

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001975

Luminaire Tested: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001975
REPORT IS A COMBINATION OF REPORTS P996600 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6290.7 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001975

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001975

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001975

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.0
10°-20°	355.9	5.7
20°-30°	523.8	8.3
30°-40°	608.9	9.7
40°-50°	608.8	9.7
50°-60°	532.5	8.5
60°-70°	395.3	6.3
70°-80°	224.3	3.6
80°-90°	65.7	1.0
90°-100°	290.0	4.6
100°-110°	589.8	9.4
110°-120°	525.7	8.4
120°-130°	441.6	7.0
130°-140°	368.5	5.9
140°-150°	281.4	4.5
150°-160°	197.8	3.1
160°-170°	116.4	1.8
170°-180°	37.8	0.6
0°-30°	1006.0	16.0
0°-40°	1614.9	25.7
0°-60°	2756.1	43.8
0°-90°	3441.5	54.7
90°-120°	1405.6	22.3
90°-150°	2497.2	39.7
90°-180°	2849.0	45.3
0°-180°	6290.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	1	6	14	15	16	6
95°	25	80	625	310	187	28
105°	90	130	503	1083	1079	96
115°	158	198	449	862	1036	157
125°	220	262	446	734	827	196
135°	262	311	443	651	739	202
145°	301	345	440	549	604	189
155°	343	370	428	485	506	158
165°	374	385	410	434	441	106
175°	390	390	394	399	397	37
180°	390	390	390	390	390	

TEST NUMBER: P1001975

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	0.8	6.1	13.8	15.3	16.1
92.5°	10.7	59.0	300.7	99.3	69.8
95°	25.3	79.8	625.1	309.5	187.2
97.5°	42.2	88.2	668.8	632.0	449.5
100°	58.3	99.7	616.7	874.4	703.4
102.5°	73.6	113.5	551.5	1026.2	924.3
105°	89.7	130.0	503.2	1083.4	1079.2
107.5°	107.4	146.9	471.7	1066.2	1152.8
110°	125.0	163.8	457.1	1004.8	1154.4

TEST NUMBER: P1001975

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	180.6	450.2	929.6	1109.1
115°	158.0	198.2	448.7	862.1	1036.2
117.5°	174.9	214.8	447.9	809.2	964.9
120°	191.8	230.8	447.9	773.6	906.6
122.5°	207.1	246.6	447.2	750.2	860.6
125°	220.1	261.6	446.4	733.7	826.8
127.5°	232.4	275.4	444.9	718.0	805.4
130°	242.4	288.8	444.1	699.2	787.0
132.5°	252.3	300.2	443.3	676.9	766.2
135°	261.6	311.4	442.6	651.2	739.4
137.5°	270.8	321.0	442.6	623.6	708.0
140°	280.7	329.8	441.8	596.7	673.4
142.5°	291.5	337.8	441.8	571.8	636.6
145°	301.4	345.2	440.3	549.2	603.6
147.5°	312.9	352.0	438.0	530.4	573.0
150°	323.7	358.6	435.7	513.1	547.6
152.5°	333.7	364.7	431.8	498.6	524.6
155°	342.9	370.0	428.0	484.8	505.5
157.5°	352.1	375.1	424.2	471.8	487.8
160°	360.5	379.3	419.6	458.6	471.7
162.5°	368.2	382.8	415.0	446.0	456.4
165°	373.5	385.0	410.4	434.5	441.0
167.5°	379.7	387.0	405.8	424.6	428.8
170°	383.5	388.5	401.1	414.6	417.3
172.5°	387.3	389.6	396.5	405.8	405.8
175°	389.6	390.4	393.5	398.8	397.3
177.5°	391.2	390.4	391.2	393.8	391.2
180°	390.4	390.4	390.4	390.4	390.4

(END OF REPORT)