

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000988

Luminaire Tested: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000988
REPORT IS A COMBINATION OF REPORTS P995604 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6937.2 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000988

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000988

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	100	95	90	86	93	89	85	81	78	75	72	68	66	64	59	58	56
2	90	82	75	69	84	77	71	66	68	63	59	59	56	52	51	49	46
3	82	72	64	57	77	67	60	54	59	54	49	52	47	44	45	42	39
4	75	63	55	48	70	59	52	46	53	46	41	46	41	37	40	36	33
5	69	56	47	41	64	53	45	39	47	40	36	41	36	32	36	32	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	55	43	35	30	38	32	27	34	28	25	30	25	22
8	54	41	33	27	51	39	32	26	35	29	24	31	26	22	27	23	20
9	51	38	30	24	47	36	28	23	32	26	22	28	23	20	25	21	18
10	47	35	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11555	11555	11555
5°	11586	11254	11274
10°	11511	11032	11000
15°	11403	10783	10692
20°	11244	10513	10393
25°	11064	10216	10070
30°	10869	9922	9740
35°	10649	9621	9447
40°	10472	9331	9144
45°	10211	9060	8875
50°	9988	8752	8592
55°	9758	8456	8266
60°	9401	8086	7959
65°	9008	7688	7590
70°	8531	7233	7163
75°	7864	6726	6757
80°	7115	6210	6331
85°	6120	5691	5986

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10211 cd/sqm

TEST NUMBER: P1000988

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	1.9
10°-20°	384.7	5.5
20°-30°	581.6	8.4
30°-40°	703.7	10.1
40°-50°	743.9	10.7
50°-60°	700.1	10.1
60°-70°	581.0	8.4
70°-80°	407.7	5.9
80°-90°	230.9	3.3
90°-100°	351.1	5.1
100°-110°	537.1	7.7
110°-120°	456.4	6.6
120°-130°	364.6	5.3
130°-140°	288.8	4.2
140°-150°	211.2	3.0
150°-160°	146.2	2.1
160°-170°	86.0	1.2
170°-180°	28.0	0.4
0°-30°	1100.6	15.9
0°-40°	1804.2	26.0
0°-60°	3248.2	46.8
0°-90°	4467.8	64.4
90°-120°	1344.6	19.4
90°-150°	2209.3	31.8
90°-180°	2469.0	35.6
0°-180°	6937.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1417	1417	1417	1417	1417	
5°	1418	1414	1403	1415	1414	135
15°	1360	1361	1357	1371	1369	383
25°	1244	1254	1258	1276	1277	573
35°	1088	1108	1123	1146	1150	682
45°	908	938	968	995	1003	701
55°	711	744	792	824	833	633
65°	492	543	597	636	649	488
75°	273	332	398	443	457	290
85°	84	151	222	270	286	88
90°	26	93	167	214	228	19
95°	39	132	600	410	334	37
105°	81	142	476	945	954	87
115°	126	170	406	746	886	126
125°	169	198	374	617	695	151
135°	196	233	341	521	596	152
145°	224	255	325	415	462	141
155°	253	273	316	358	374	117
165°	276	284	303	321	326	78
175°	288	288	291	295	294	27
180°	288	288	288	288	288	

TEST NUMBER: P1000988

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1423.3	1418.5	1405.9	1417.0	1415.4
5°	1418.5	1413.8	1402.7	1415.4	1413.8
7.5°	1409.0	1405.9	1396.3	1410.6	1409.0
10°	1396.3	1394.7	1386.8	1401.1	1399.5
12.5°	1378.9	1378.9	1374.1	1386.8	1386.8
15°	1359.8	1361.4	1356.7	1370.9	1369.4
17.5°	1334.5	1339.2	1337.6	1351.9	1350.3
20°	1307.5	1312.2	1313.8	1329.7	1329.7
22.5°	1277.3	1283.7	1286.8	1302.7	1305.9
25°	1244.0	1253.5	1258.3	1275.7	1277.3
27.5°	1207.5	1221.8	1228.1	1244.0	1245.6
30°	1171.0	1183.7	1194.8	1212.3	1215.4
32.5°	1131.3	1147.2	1159.9	1180.5	1183.7
35°	1088.5	1107.5	1123.4	1145.6	1150.4
37.5°	1045.7	1067.9	1086.9	1109.1	1113.9
40°	1004.4	1025.0	1047.2	1071.1	1077.4
42.5°	956.8	980.6	1007.6	1034.6	1039.3
45°	907.6	937.8	967.9	994.9	1002.8
47.5°	861.6	891.7	926.7	953.6	963.2
50°	810.8	845.7	880.6	912.4	921.9
52.5°	760.0	795.0	836.2	867.9	877.5
55°	710.9	744.2	791.8	823.5	833.0
57.5°	655.3	696.6	742.6	780.7	788.6
60°	601.4	642.6	695.0	731.5	744.2
62.5°	549.0	595.0	647.4	683.9	696.6
65°	491.9	542.7	596.6	636.3	649.0
67.5°	437.9	491.9	549.0	588.7	601.4
70°	382.4	436.4	496.7	539.5	550.6
72.5°	328.5	384.0	449.0	490.3	503.0
75°	272.9	331.6	398.3	442.7	457.0
77.5°	220.6	282.4	352.3	396.7	412.6
80°	173.0	236.4	306.2	353.8	366.5
82.5°	125.4	192.0	261.8	311.0	325.3
85°	84.1	150.7	222.1	269.7	285.6
87.5°	52.4	117.4	187.2	233.3	247.5
90°	26.0	93.4	167.3	214.4	227.7
92.5°	31.7	123.0	369.7	265.4	256.3
95°	39.3	131.9	599.9	409.6	333.5
97.5°	50.2	130.3	624.3	638.4	517.7
100°	60.6	132.4	576.2	809.4	694.2
102.5°	71.9	136.3	520.2	912.2	849.5
105°	80.6	142.0	476.5	944.8	954.5
107.5°	93.6	149.8	445.3	924.2	999.4
110°	105.1	155.8	428.2	869.2	992.5



TEST NUMBER: P1000988

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	115.9	163.5	415.2	804.2	949.6
115°	126.2	170.2	406.1	746.5	886.2
117.5°	138.7	177.6	397.6	697.9	825.6
120°	149.6	183.2	389.7	661.9	772.9
122.5°	160.9	190.0	381.2	636.7	729.4
125°	168.9	198.0	374.2	616.6	695.0
127.5°	178.0	208.2	365.2	595.6	671.2
130°	183.9	216.6	356.7	573.6	648.0
132.5°	191.2	225.0	349.8	549.3	624.8
135°	196.4	233.2	341.3	520.8	595.5
137.5°	203.2	238.7	334.9	492.4	562.8
140°	210.6	245.3	329.6	464.7	529.3
142.5°	216.9	251.2	326.4	440.0	494.2
145°	224.3	255.0	325.3	415.2	461.9
147.5°	232.8	260.1	323.6	393.5	431.2
150°	240.7	264.9	321.9	379.1	404.6
152.5°	246.5	269.5	319.1	368.4	387.6
155°	253.3	273.4	316.2	358.2	373.5
157.5°	260.1	277.1	313.4	348.5	360.4
160°	266.4	280.2	310.0	338.9	348.5
162.5°	272.0	282.8	306.6	329.6	337.2
165°	276.0	284.5	303.2	321.0	325.9
167.5°	280.5	285.9	299.8	313.6	316.8
170°	283.4	287.0	296.4	306.4	308.3
172.5°	286.2	287.9	293.0	299.8	299.8
175°	287.9	288.5	290.7	294.7	293.6
177.5°	289.0	288.5	289.0	291.0	289.0
180°	288.5	288.5	288.5	288.5	288.5

(END OF REPORT)