

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001980

Luminaire Tested: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001980
REPORT IS A COMBINATION OF REPORTS P996605 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5963.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001980

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001980

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	46	46	46	40
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38	38	38	33
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31	31	31	27
4	73	61	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27	27	27	23
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23	23	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20	20	20	17
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	18	18	15
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16	16	16	14
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14	14	14	12
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1001980

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.5
10°-20°	257.7	4.3
20°-30°	389.7	6.5
30°-40°	471.5	7.9
40°-50°	498.4	8.4
50°-60°	469.1	7.9
60°-70°	389.3	6.5
70°-80°	273.2	4.6
80°-90°	156.1	2.6
90°-100°	155.7	2.6
100°-110°	259.6	4.4
110°-120°	371.2	6.2
120°-130°	455.1	7.6
130°-140°	493.4	8.3
140°-150°	476.2	8.0
150°-160°	398.7	6.7
160°-170°	265.3	4.4
170°-180°	92.9	1.6
0°-30°	737.4	12.4
0°-40°	1208.9	20.3
0°-60°	2176.5	36.5
0°-90°	2995.0	50.2
90°-120°	786.4	13.2
90°-150°	2211.2	37.1
90°-180°	2968.0	49.8
0°-180°	5963.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	19	70	122	157	167	15
95°	59	101	150	181	191	60
105°	186	208	251	280	291	198
115°	337	347	380	402	409	333
125°	486	485	511	530	535	434
135°	624	628	636	652	656	483
145°	757	758	759	765	767	474
155°	866	866	865	868	865	398
165°	942	940	938	943	940	266
175°	980	976	976	981	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001980

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	19.3	70.1	122.0	157.4	167.4
92.5°	35.6	82.8	132.3	164.3	173.6
95°	59.4	101.3	150.2	181.2	190.8
97.5°	85.7	122.6	172.2	202.9	212.5
100°	118.0	148.6	197.0	227.2	234.7
102.5°	152.9	177.1	223.6	253.4	262.7
105°	186.5	208.5	250.9	279.8	290.6
107.5°	223.7	242.5	280.5	310.1	316.8
110°	260.6	277.0	313.4	336.4	347.2

TEST NUMBER: P1001980

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	299.0	311.8	345.3	368.7	377.2
115°	337.4	346.9	379.5	402.2	408.8
117.5°	374.6	381.0	412.2	432.2	438.4
120°	410.7	417.0	445.5	463.0	473.0
122.5°	449.5	450.2	478.2	497.2	500.8
125°	486.4	485.3	511.2	529.8	534.6
127.5°	520.6	521.8	541.6	559.1	565.8
130°	555.9	557.1	574.1	591.8	595.2
132.5°	593.1	593.6	605.6	622.2	627.7
135°	623.9	628.5	636.0	651.5	655.6
137.5°	659.6	660.9	666.6	680.3	686.4
140°	695.3	695.8	696.8	709.9	714.5
142.5°	726.9	728.5	726.6	738.3	742.5
145°	756.6	758.5	759.3	764.9	766.8
147.5°	786.9	789.6	788.9	789.2	792.6
150°	814.3	816.2	816.2	816.2	815.4
152.5°	839.0	840.5	841.3	843.5	841.3
155°	865.6	865.6	864.8	867.8	864.8
157.5°	888.3	886.8	886.8	889.1	886.8
160°	908.1	907.3	906.5	908.8	905.0
162.5°	926.3	924.0	923.3	927.8	924.0
165°	942.2	940.0	938.4	943.0	940.0
167.5°	955.1	952.1	952.1	956.7	952.1
170°	965.8	962.0	962.7	967.3	962.0
172.5°	973.4	970.3	970.3	975.6	970.3
175°	980.2	976.4	975.6	981.0	975.6
177.5°	983.2	979.4	979.4	984.8	978.7
180°	981.7	981.7	981.7	981.7	981.7

(END OF REPORT)