

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001984

Luminaire Tested: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001984
REPORT IS A COMBINATION OF REPORTS P996609 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6227.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001984

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001984

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001984

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.0
10°-20°	352.4	5.7
20°-30°	518.6	8.3
30°-40°	602.8	9.7
40°-50°	602.8	9.7
50°-60°	527.2	8.5
60°-70°	391.4	6.3
70°-80°	222.1	3.6
80°-90°	65.1	1.0
90°-100°	287.0	4.6
100°-110°	583.8	9.4
110°-120°	520.4	8.4
120°-130°	437.1	7.0
130°-140°	364.8	5.9
140°-150°	278.6	4.5
150°-160°	195.8	3.1
160°-170°	115.2	1.8
170°-180°	37.4	0.6
0°-30°	996.1	16.0
0°-40°	1598.9	25.7
0°-60°	2728.9	43.8
0°-90°	3407.5	54.7
90°-120°	1391.3	22.3
90°-150°	2471.7	39.7
90°-180°	2820.0	45.3
0°-180°	6227.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	1	6	14	15	16	5
95°	25	79	619	306	185	27
105°	89	129	498	1072	1068	95
115°	156	196	444	853	1026	155
125°	218	259	442	726	818	194
135°	259	308	438	645	732	200
145°	298	342	436	544	598	187
155°	339	366	424	480	500	157
165°	370	381	406	430	436	104
175°	386	386	390	395	393	37
180°	386	386	386	386	386	

TEST NUMBER: P1001984

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	0.8	6.1	13.7	15.2	15.9
92.5°	10.6	58.4	297.6	98.3	69.1
95°	25.1	79.0	618.7	306.4	185.2
97.5°	41.8	87.3	662.0	625.6	444.9
100°	57.7	98.6	610.4	865.5	696.2
102.5°	72.9	112.4	545.9	1015.8	914.8
105°	88.8	128.7	498.0	1072.4	1068.2
107.5°	106.3	145.4	466.9	1055.3	1141.1
110°	123.7	162.0	452.5	994.6	1142.6



TEST NUMBER: P1001984

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.5	178.8	445.6	920.2	1097.8
115°	156.4	196.2	444.1	853.4	1025.7
117.5°	173.1	212.6	443.4	801.0	955.1
120°	189.8	228.5	443.4	765.7	897.4
122.5°	205.0	244.0	442.6	742.5	851.8
125°	217.9	258.9	441.9	726.2	818.4
127.5°	230.0	272.5	440.3	710.6	797.2
130°	239.9	285.8	439.6	692.0	778.9
132.5°	249.8	297.2	438.8	670.0	758.4
135°	258.9	308.2	438.1	644.6	731.9
137.5°	268.0	317.7	438.1	617.2	700.7
140°	277.9	326.5	437.3	590.7	666.6
142.5°	288.5	334.4	437.3	566.0	630.1
145°	298.4	341.6	435.8	543.6	597.5
147.5°	309.8	348.5	433.5	525.0	567.1
150°	320.4	354.9	431.2	507.9	542.1
152.5°	330.3	361.0	427.4	493.5	519.3
155°	339.4	366.3	423.6	479.8	500.3
157.5°	348.5	371.2	419.8	466.9	482.8
160°	356.8	375.4	415.3	454.0	466.9
162.5°	364.4	378.8	410.7	441.4	451.7
165°	369.7	381.1	406.2	430.1	436.5
167.5°	375.8	383.0	401.6	420.2	424.4
170°	379.6	384.5	397.1	410.4	413.0
172.5°	383.4	385.6	392.5	401.6	401.6
175°	385.7	386.4	389.5	394.8	393.3
177.5°	387.2	386.4	387.2	389.8	387.2
180°	386.4	386.4	386.4	386.4	386.4

(END OF REPORT)