

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001987

Luminaire Tested: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001987
REPORT IS A COMBINATION OF REPORTS P996612 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6148.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10118	10118	10118	10118
5°	10093	11608	10152	8722
10°	10017	13543	10094	7652
15°	9897	15612	9966	6847
20°	9769	16930	9840	6139
25°	9582	16736	9674	5616
30°	9399	13833	9513	5347
35°	9143	10308	9243	5184
40°	8842	7766	8929	5104
45°	8385	6232	8490	4995
50°	7840	5251	7953	4944
55°	7197	4570	7310	4886
60°	6573	4025	6766	4805
65°	5987	3463	6043	4604
70°	5299	2849	5412	4240
75°	4622	2188	4591	3602
80°	3636	1439	3595	2734
85°	2394	646	2241	1595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 13083 cd/sqm

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	2.0
10°-20°	372.7	6.1
20°-30°	592.2	9.6
30°-40°	658.0	10.7
40°-50°	598.4	9.7
50°-60°	489.0	8.0
60°-70°	349.0	5.7
70°-80°	192.1	3.1
80°-90°	53.4	0.9
90°-100°	270.9	4.4
100°-110°	565.6	9.2
110°-120°	502.8	8.2
120°-130°	423.2	6.9
130°-140°	353.1	5.7
140°-150°	269.6	4.4
150°-160°	189.5	3.1
160°-170°	111.5	1.8
170°-180°	36.3	0.6
0°-30°	1085.7	17.7
0°-40°	1743.6	28.4
0°-60°	2831.0	46.0
0°-90°	3425.5	55.7
90°-120°	1339.3	21.8
90°-150°	2385.3	38.8
90°-180°	2723.0	44.3
0°-180°	6148.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1241	1241	1241	1241	1241	
5°	1236	1456	1243	1094	1236	117
15°	1180	2000	1188	877	1180	333
25°	1077	2123	1088	712	1077	496
35°	934	1255	945	631	934	584
45°	745	704	755	564	745	575
55°	524	461	532	492	524	472
65°	327	296	330	394	327	323
75°	160	148	159	244	160	168
85°	33	31	31	76	33	38
90°	1	15	1	15	1	4
95°	24	179	24	179	24	27
105°	86	1033	86	1033	86	92
115°	151	992	151	992	151	150
125°	211	792	211	792	211	188
135°	250	708	250	708	250	194
145°	289	578	289	578	289	181
155°	328	484	328	484	328	151
165°	358	422	358	422	358	101
175°	373	380	373	380	373	35
180°	374	374	374	374	374	

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1240.8	1253.2	1258.3	1262.4	1275.8	1279.9	1280.9	1287.1	1292.2	1293.3	1293.3
5°	1235.7	1255.2	1270.6	1285.0	1306.6	1315.9	1327.2	1339.5	1356.0	1366.3	1371.4
7.5°	1227.5	1256.3	1279.9	1304.6	1334.4	1352.9	1363.2	1396.1	1418.7	1437.2	1459.8
10°	1215.1	1252.1	1286.1	1322.1	1364.2	1386.8	1409.4	1449.5	1481.4	1517.4	1546.2
12.5°	1196.6	1244.9	1286.1	1336.4	1388.9	1415.6	1442.3	1512.2	1549.2	1581.1	1632.5
15°	1180.2	1228.5	1287.1	1338.5	1403.3	1443.4	1482.4	1527.7	1586.3	1655.1	1704.5
17.5°	1161.7	1222.3	1276.8	1348.8	1420.7	1458.8	1490.6	1560.6	1642.8	1710.6	1755.9
20°	1136.0	1197.7	1269.6	1345.7	1431.0	1460.8	1503.0	1596.5	1670.6	1737.4	1811.4
22.5°	1106.2	1178.1	1254.2	1327.2	1415.6	1478.3	1524.6	1606.8	1696.3	1773.4	1856.6
25°	1077.4	1155.5	1222.3	1322.1	1415.6	1457.8	1510.2	1607.8	1705.5	1799.1	1884.4
27.5°	1046.5	1119.5	1210.0	1289.2	1395.0	1441.3	1497.8	1604.8	1708.6	1802.1	1893.6
30°	1012.6	1090.7	1165.8	1259.3	1362.1	1421.8	1474.2	1590.4	1696.3	1793.9	1879.2
32.5°	974.6	1048.6	1128.8	1217.2	1325.1	1385.8	1451.6	1570.8	1683.9	1768.2	1834.0
35°	934.5	1009.5	1079.4	1169.9	1280.9	1341.6	1405.3	1536.9	1649.0	1717.8	1755.9
37.5°	890.3	961.2	1030.1	1119.5	1230.6	1295.3	1360.1	1487.6	1593.5	1651.0	1640.7
40°	848.1	911.9	975.6	1059.9	1176.1	1244.9	1301.5	1430.0	1522.5	1547.2	1513.3
42.5°	799.8	854.3	916.0	1002.3	1115.4	1180.2	1251.1	1368.3	1437.2	1426.9	1369.3
45°	745.3	793.6	855.3	936.5	1051.7	1118.5	1178.1	1289.2	1339.5	1313.8	1209.0
47.5°	692.9	740.2	790.6	871.8	983.8	1040.4	1101.0	1200.7	1229.5	1175.0	1070.2
50°	636.4	675.4	727.8	805.0	909.8	969.4	1019.8	1100.0	1110.3	1043.5	934.5
52.5°	581.9	614.8	665.1	741.2	838.9	886.2	935.5	1006.4	998.2	929.3	824.5
55°	524.3	555.1	601.4	671.3	757.7	802.9	845.0	907.8	890.3	819.3	727.8
57.5°	476.0	497.6	542.8	607.6	678.5	727.8	763.8	813.2	786.4	715.5	630.2
60°	420.5	447.2	485.2	537.7	607.6	640.5	672.3	705.2	686.7	618.9	542.8
62.5°	370.1	390.7	423.5	473.9	528.4	558.2	592.1	612.7	594.2	531.5	467.8
65°	326.9	343.4	369.1	410.2	462.6	487.3	506.8	526.4	510.9	452.3	406.1
67.5°	279.6	294.0	315.6	348.5	392.7	410.2	428.7	442.1	424.6	385.5	340.3
70°	237.5	247.8	268.3	293.0	323.8	340.3	355.7	369.1	353.6	320.7	286.8
72.5°	194.3	202.5	221.0	238.5	266.3	277.6	288.9	299.2	294.0	263.2	235.4
75°	160.4	163.5	175.8	190.2	207.7	220.0	228.2	234.4	230.3	205.6	188.1
77.5°	121.3	125.4	134.7	146.0	161.4	168.6	173.7	179.9	174.8	155.2	142.9
80°	88.4	89.4	94.6	104.9	115.1	116.2	121.3	129.5	126.4	113.1	103.8
82.5°	56.5	59.6	61.7	67.9	75.0	77.1	80.2	82.2	81.2	73.0	69.9
85°	32.9	32.9	35.0	39.1	41.1	44.2	45.2	46.3	48.3	43.2	40.1
87.5°	14.4	15.4	15.4	16.4	18.5	18.5	19.5	20.6	21.6	20.6	17.5
90°	0.7	2.2	4.4	5.1	5.9	5.9	5.9	10.3	10.3	11.8	13.2
92.5°	10.3	14.7	22.8	33.8	47.0	56.6	66.1	111.6	182.9	251.9	287.9
95°	24.2	26.4	33.8	43.3	61.0	76.4	91.8	155.7	276.1	451.7	598.5
97.5°	40.4	40.4	47.0	55.8	71.2	84.4	97.7	148.3	251.9	432.6	640.4
100°	55.8	55.8	61.0	69.8	83.7	95.4	107.2	150.6	233.5	383.4	590.5
102.5°	70.5	72.0	76.4	84.5	97.7	108.7	119.7	157.9	228.4	350.3	528.0
105°	85.9	88.1	91.8	100.6	113.8	124.4	135.1	170.4	231.3	334.1	481.8
107.5°	102.8	104.3	108.0	117.5	130.0	140.6	151.3	183.6	240.1	329.7	451.7
110°	119.7	121.2	124.8	133.7	146.9	156.8	166.7	199.0	250.4	331.2	437.7



TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.9	137.3	141.7	149.8	163.0	173.0	182.9	213.7	261.4	335.6	431.1
115°	151.3	153.5	158.6	166.0	179.9	189.9	199.8	229.1	273.2	341.5	429.6
117.5°	167.4	169.6	174.1	182.1	195.3	205.6	215.9	243.8	284.9	347.4	428.9
120°	183.6	185.1	190.2	198.3	210.8	221.0	231.3	259.2	297.4	354.0	428.9
122.5°	198.3	199.8	204.9	212.2	226.2	236.1	246.0	273.9	309.2	360.6	428.2
125°	210.8	213.7	218.1	226.2	240.1	250.4	260.7	287.1	320.9	367.2	427.4
127.5°	222.5	224.7	229.9	238.7	253.4	263.6	273.9	299.6	331.2	372.3	425.9
130°	232.1	235.0	240.9	251.9	265.9	276.5	287.1	312.1	340.8	378.2	425.2
132.5°	241.6	243.8	251.9	262.2	277.6	287.5	297.4	322.4	350.3	383.4	424.5
135°	250.4	253.4	260.7	273.2	288.6	298.2	307.7	331.9	358.4	388.5	423.7
137.5°	259.2	262.2	270.3	282.0	298.2	307.4	316.5	339.3	364.3	391.4	423.7
140°	268.8	271.0	279.1	291.6	307.0	315.8	324.6	346.6	370.1	395.1	423.0
142.5°	279.1	281.3	288.6	300.4	315.1	323.5	331.9	353.2	374.5	398.0	423.0
145°	288.6	290.8	298.2	308.4	322.4	330.5	338.6	357.7	377.5	398.8	421.5
147.5°	299.6	300.4	307.0	318.0	329.7	337.0	344.4	362.8	380.4	399.5	419.3
150°	309.9	310.6	316.5	325.3	336.4	343.4	350.3	366.5	382.6	399.5	417.1
152.5°	319.5	319.5	325.3	333.4	343.0	349.2	355.4	369.4	384.1	398.0	413.5
155°	328.3	329.0	333.4	340.8	348.8	354.4	359.9	372.3	384.8	396.6	409.8
157.5°	337.1	337.1	341.5	347.4	354.7	359.1	363.5	374.5	384.8	395.1	406.1
160°	345.2	345.2	348.1	353.2	359.1	363.2	367.2	376.0	384.8	392.9	401.7
162.5°	352.5	351.8	354.0	358.4	363.5	366.4	369.4	377.5	384.8	390.7	397.3
165°	357.7	357.7	359.1	362.8	366.5	368.7	370.9	377.5	383.4	387.8	392.9
167.5°	363.5	362.8	363.5	366.5	368.7	370.5	372.3	377.5	381.9	384.8	388.5
170°	367.2	366.5	367.2	369.4	370.9	372.0	373.1	376.7	380.4	381.9	384.1
172.5°	370.9	370.1	370.1	371.6	372.3	373.0	373.8	376.0	378.9	378.9	379.7
175°	373.1	372.3	372.3	373.1	373.8	373.8	373.8	375.3	377.5	376.7	376.7
177.5°	374.5	373.8	373.1	373.8	373.8	373.8	373.8	374.5	376.0	374.5	374.5
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1296.4	1314.9	1323.1	1325.1	1336.4	1329.2	1332.3	1331.3	1339.5	1340.6	1340.6
5°	1390.9	1412.5	1419.7	1430.0	1445.4	1449.5	1446.4	1452.6	1463.9	1455.7	1468.0
7.5°	1490.6	1514.3	1530.7	1553.4	1558.5	1571.9	1580.1	1587.3	1589.3	1590.4	1592.4
10°	1583.2	1613.0	1635.6	1673.6	1681.9	1689.1	1725.0	1710.6	1729.2	1723.0	1725.0
12.5°	1658.2	1716.8	1735.3	1799.1	1805.2	1829.9	1827.8	1850.5	1854.6	1862.8	1854.6
15°	1756.9	1824.8	1854.6	1890.6	1911.1	1939.9	1945.0	1975.9	1988.2	1999.5	1988.2
17.5°	1847.4	1883.4	1959.4	1988.2	2001.6	2017.0	2056.1	2067.4	2085.9	2078.7	2099.2
20°	1892.6	1944.0	2024.2	2073.5	2094.1	2108.5	2141.4	2158.9	2166.1	2166.1	2168.1
22.5°	1932.7	2006.7	2066.3	2122.9	2141.4	2151.7	2171.2	2184.6	2187.7	2189.7	2191.8
25°	1968.7	2035.5	2083.8	2115.7	2122.9	2122.9	2134.2	2126.0	2112.6	2122.9	2129.1
27.5°	1968.7	2016.0	2037.6	2048.9	2048.9	2021.1	2004.7	1970.7	1942.0	1933.7	1952.2
30°	1935.8	1957.4	1927.6	1899.8	1878.2	1859.7	1794.9	1743.5	1733.3	1726.1	1753.8
32.5°	1859.7	1832.0	1773.4	1693.2	1661.3	1619.2	1568.8	1529.7	1506.1	1497.8	1491.7
35°	1725.0	1653.1	1577.0	1469.1	1446.4	1393.0	1324.1	1295.3	1256.3	1255.2	1268.6
37.5°	1578.0	1467.0	1384.8	1282.0	1250.1	1193.5	1128.8	1099.0	1072.2	1051.7	1076.4
40°	1406.4	1309.7	1184.3	1100.0	1054.8	1024.9	970.5	937.6	925.2	915.0	930.4
42.5°	1246.0	1140.1	1042.4	956.1	919.1	885.1	849.2	817.3	808.0	807.0	818.3
45°	1086.6	982.8	892.3	818.3	794.7	774.1	739.2	729.9	714.5	704.2	709.3
47.5°	959.2	852.2	777.2	720.7	700.1	682.6	660.0	644.6	631.2	627.1	633.3
50°	833.7	761.8	684.7	637.4	622.0	605.5	588.0	573.6	567.5	563.4	567.5
52.5°	733.0	655.9	603.5	565.4	550.0	537.7	525.3	519.2	510.9	513.0	517.1
55°	642.5	574.7	530.5	502.7	493.5	488.3	472.9	465.7	462.6	460.6	462.6
57.5°	557.2	507.8	475.0	451.3	439.0	435.9	423.5	423.5	420.5	417.4	418.4
60°	489.3	447.2	415.3	396.8	394.8	389.6	381.4	380.4	373.2	376.3	377.3
62.5°	420.5	386.5	365.0	353.6	346.4	344.4	339.3	338.2	335.1	336.2	334.1
65°	366.0	338.2	316.6	307.4	304.3	303.3	299.2	296.1	294.0	296.1	294.0
67.5°	311.5	293.0	276.5	267.3	263.2	262.1	259.1	257.0	258.0	255.0	257.0
70°	260.1	241.6	231.3	226.2	224.1	221.0	221.0	221.0	221.0	219.0	217.9
72.5°	219.0	200.5	193.3	190.2	188.1	187.1	184.0	185.0	184.0	183.0	187.1
75°	173.7	162.4	155.2	152.1	154.2	151.1	148.0	150.1	147.0	148.0	152.1
77.5°	131.6	126.4	122.3	120.3	118.2	116.2	116.2	114.1	114.1	114.1	114.1
80°	95.6	94.6	87.4	86.4	86.4	84.3	84.3	84.3	84.3	83.3	84.3
82.5°	63.7	62.7	60.7	59.6	57.6	58.6	58.6	56.5	56.5	55.5	56.5
85°	37.0	37.0	35.0	33.9	32.9	33.9	31.9	30.8	31.9	30.8	31.9
87.5°	17.5	15.4	16.4	15.4	13.4	14.4	12.3	13.4	12.3	11.3	13.4
90°	12.5	13.2	14.0	14.7	14.7	14.7	15.4	16.2	15.4	15.4	15.4
92.5°	239.4	177.0	132.2	104.3	95.1	85.9	74.9	69.8	66.8	66.8	66.8
95°	615.4	544.2	430.4	331.9	296.3	260.7	224.7	202.0	188.7	179.2	188.7
97.5°	771.8	783.6	727.1	646.3	605.2	564.0	514.1	470.0	448.0	430.4	448.0
100°	778.5	885.7	900.4	864.4	837.2	810.0	746.1	701.3	679.3	673.4	679.3
102.5°	723.4	880.5	967.9	990.0	982.6	975.3	942.2	912.9	889.4	884.9	889.4
105°	654.3	822.5	949.6	1022.3	1037.4	1052.4	1053.9	1048.0	1037.7	1033.3	1037.7
107.5°	597.8	751.3	888.6	990.0	1020.8	1051.7	1084.0	1097.2	1103.1	1103.8	1103.1
110°	557.4	688.1	815.2	921.7	962.0	1002.4	1054.6	1085.4	1098.7	1105.3	1098.7

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	534.6	641.9	750.6	849.7	890.1	930.5	991.4	1030.4	1050.2	1061.9	1050.2
115°	522.2	614.0	704.3	790.2	825.4	860.7	918.7	962.8	986.3	992.2	986.3
117.5°	515.5	597.8	674.2	743.9	774.8	805.6	857.0	895.2	920.2	923.9	920.2
120°	510.4	587.5	655.8	714.6	740.7	766.7	808.6	840.9	860.0	868.1	860.0
122.5°	504.5	578.7	644.1	696.2	718.2	740.3	774.1	800.5	815.9	824.0	815.9
125°	497.9	568.4	631.6	682.3	702.4	722.6	752.0	773.3	787.3	791.7	787.3
127.5°	489.1	556.7	617.6	668.3	687.4	706.5	735.9	755.0	766.7	771.1	766.7
130°	481.0	542.0	600.0	649.9	669.4	688.9	719.0	737.3	749.1	753.5	749.1
132.5°	473.7	526.6	580.2	628.6	648.1	667.6	696.9	718.2	729.3	733.7	729.3
135°	466.3	512.6	560.3	605.1	623.5	641.9	671.2	691.8	703.5	708.0	703.5
137.5°	459.7	499.4	541.2	580.2	597.1	614.0	641.9	663.2	672.7	677.8	672.7
140°	454.6	488.4	522.9	555.9	571.3	586.8	612.5	628.6	638.9	644.8	638.9
142.5°	450.2	478.1	507.5	534.6	547.4	560.3	582.4	597.1	605.9	609.5	605.9
145°	445.0	468.5	493.5	515.5	525.8	536.1	554.5	567.0	574.3	578.0	574.3
147.5°	440.6	460.5	481.0	499.4	507.8	516.3	530.2	541.2	547.1	548.6	547.1
150°	435.5	453.1	470.0	484.7	491.3	497.9	509.7	519.2	523.6	524.4	523.6
152.5°	429.6	445.0	459.0	472.2	477.4	482.5	492.0	499.4	501.6	502.3	501.6
155°	423.7	437.0	448.7	459.7	464.1	468.5	475.9	481.8	484.0	484.0	484.0
157.5°	417.9	428.2	438.4	448.0	451.6	455.3	461.2	465.6	467.1	467.1	467.1
160°	411.3	420.1	428.2	436.2	439.2	442.1	446.5	450.9	451.7	451.7	451.7
162.5°	405.4	412.0	418.6	424.5	427.0	429.6	432.6	437.0	437.7	437.0	437.7
165°	398.8	404.7	409.1	414.2	416.0	417.9	420.8	423.7	423.0	422.3	423.0
167.5°	392.9	397.3	401.0	405.4	406.5	407.6	409.1	411.3	411.3	410.5	411.3
170°	387.0	390.7	392.9	395.8	396.9	398.0	399.5	400.2	399.5	399.5	399.5
172.5°	381.9	384.8	386.3	387.8	388.5	389.2	390.0	390.7	390.0	388.5	390.0
175°	378.2	379.7	380.4	381.9	381.9	381.9	381.9	383.4	381.9	380.4	381.9
177.5°	375.3	376.0	376.7	376.7	377.1	377.5	376.7	377.5	376.0	374.5	376.0
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1338.5	1335.4	1331.3	1331.3	1326.2	1326.2	1317.9	1303.5	1291.2	1287.1	1289.2
5°	1452.6	1453.6	1447.5	1442.3	1433.1	1425.9	1412.5	1386.8	1378.6	1362.1	1350.8
7.5°	1583.2	1579.1	1567.8	1559.5	1557.5	1541.0	1512.2	1481.4	1456.7	1440.3	1416.6
10°	1730.2	1713.7	1697.3	1692.1	1679.8	1652.1	1619.2	1585.2	1551.3	1515.3	1475.2
12.5°	1853.5	1821.7	1820.6	1808.3	1784.7	1769.2	1730.2	1681.9	1623.3	1583.2	1537.9
15°	1986.2	1956.3	1931.7	1909.1	1897.8	1852.5	1819.6	1759.0	1689.1	1645.9	1615.0
17.5°	2080.7	2067.4	2025.2	2014.9	1999.5	1947.1	1894.7	1835.0	1774.4	1713.7	1630.5
20°	2156.8	2148.6	2120.8	2106.4	2081.8	2040.6	1976.9	1908.0	1838.1	1751.8	1673.6
22.5°	2189.7	2179.4	2156.8	2144.5	2129.1	2094.1	2039.6	1961.5	1870.0	1792.9	1709.6
25°	2124.9	2143.5	2137.3	2132.1	2126.0	2105.4	2064.3	1995.4	1906.0	1818.6	1714.8
27.5°	1979.0	2010.8	2041.7	2045.8	2056.1	2064.3	2047.8	1998.5	1923.5	1830.9	1716.8
30°	1782.6	1797.0	1859.7	1878.2	1892.6	1945.0	1975.9	1963.5	1906.0	1822.7	1717.8
32.5°	1530.7	1568.8	1632.5	1676.7	1715.8	1774.4	1854.6	1886.4	1865.9	1798.0	1694.2
35°	1292.2	1337.5	1411.5	1468.0	1507.1	1590.4	1684.9	1753.8	1779.5	1745.6	1653.1
37.5°	1096.9	1151.4	1217.2	1238.8	1284.0	1386.8	1517.4	1613.0	1675.7	1678.8	1606.8
40°	949.9	977.7	1030.1	1063.0	1107.2	1193.5	1321.0	1447.5	1542.1	1573.9	1535.9
42.5°	825.5	847.1	886.2	926.3	966.4	1032.1	1149.3	1267.6	1395.0	1458.8	1457.8
45°	726.8	749.4	776.2	809.1	836.8	907.8	1000.3	1121.6	1231.6	1330.3	1354.9
47.5°	640.5	660.0	692.9	707.3	725.8	792.6	872.8	985.9	1100.0	1213.1	1241.9
50°	576.7	593.2	615.8	625.0	645.6	695.0	760.7	852.2	978.7	1082.5	1136.0
52.5°	519.2	531.5	549.0	556.2	570.6	607.6	667.2	739.2	844.0	950.9	1026.0
55°	469.8	478.0	490.4	498.6	508.9	541.8	586.0	650.7	741.2	833.7	906.7
57.5°	423.5	429.7	442.1	446.2	454.4	480.1	510.9	565.4	648.7	730.9	801.9
60°	380.4	384.5	391.7	400.9	407.1	424.6	453.4	498.6	565.4	640.5	698.0
62.5°	339.3	345.4	347.5	351.6	356.7	373.2	395.8	428.7	487.3	549.0	609.6
65°	297.1	302.2	306.4	307.4	312.5	324.9	345.4	374.2	412.2	465.7	522.2
67.5°	258.0	261.1	263.2	267.3	272.4	278.6	295.0	316.6	351.6	394.8	440.0
70°	222.1	222.1	225.1	226.2	232.3	239.5	246.7	267.3	298.1	333.1	363.9
72.5°	183.0	188.1	187.1	192.2	191.2	196.4	205.6	219.0	241.6	269.3	299.2
75°	149.1	152.1	152.1	152.1	154.2	158.3	163.5	175.8	193.3	215.9	233.4
77.5°	116.2	118.2	118.2	118.2	119.3	123.4	128.5	136.7	149.1	162.4	172.7
80°	83.3	85.3	85.3	87.4	87.4	88.4	93.6	97.7	103.8	114.1	124.4
82.5°	56.5	57.6	59.6	59.6	58.6	60.7	61.7	65.8	72.0	74.0	81.2
85°	30.8	31.9	32.9	32.9	33.9	36.0	35.0	39.1	39.1	43.2	45.2
87.5°	12.3	14.4	14.4	13.4	14.4	14.4	14.4	16.4	17.5	18.5	17.5
90°	16.2	15.4	14.7	14.7	14.7	14.0	13.2	12.5	13.2	11.8	10.3
92.5°	69.8	74.9	85.9	95.1	104.3	132.2	177.0	239.4	287.9	251.9	182.9
95°	202.0	224.7	260.7	296.3	331.9	430.4	544.2	615.4	598.5	451.7	276.1
97.5°	470.0	514.1	564.0	605.2	646.3	727.1	783.6	771.8	640.4	432.6	251.9
100°	701.3	746.1	810.0	837.2	864.4	900.4	885.7	778.5	590.5	383.4	233.5
102.5°	912.9	942.2	975.3	982.6	990.0	967.9	880.5	723.4	528.0	350.3	228.4
105°	1048.0	1053.9	1052.4	1037.4	1022.3	949.6	822.5	654.3	481.8	334.1	231.3
107.5°	1097.2	1084.0	1051.7	1020.8	990.0	888.6	751.3	597.8	451.7	329.7	240.1
110°	1085.4	1054.6	1002.4	962.0	921.7	815.2	688.1	557.4	437.7	331.2	250.4

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1030.4	991.4	930.5	890.1	849.7	750.6	641.9	534.6	431.1	335.6	261.4
115°	962.8	918.7	860.7	825.4	790.2	704.3	614.0	522.2	429.6	341.5	273.2
117.5°	895.2	857.0	805.6	774.8	743.9	674.2	597.8	515.5	428.9	347.4	284.9
120°	840.9	808.6	766.7	740.7	714.6	655.8	587.5	510.4	428.9	354.0	297.4
122.5°	800.5	774.1	740.3	718.2	696.2	644.1	578.7	504.5	428.2	360.6	309.2
125°	773.3	752.0	722.6	702.4	682.3	631.6	568.4	497.9	427.4	367.2	320.9
127.5°	755.0	735.9	706.5	687.4	668.3	617.6	556.7	489.1	425.9	372.3	331.2
130°	737.3	719.0	688.9	669.4	649.9	600.0	542.0	481.0	425.2	378.2	340.8
132.5°	718.2	696.9	667.6	648.1	628.6	580.2	526.6	473.7	424.5	383.4	350.3
135°	691.8	671.2	641.9	623.5	605.1	560.3	512.6	466.3	423.7	388.5	358.4
137.5°	663.2	641.9	614.0	597.1	580.2	541.2	499.4	459.7	423.7	391.4	364.3
140°	628.6	612.5	586.8	571.3	555.9	522.9	488.4	454.6	423.0	395.1	370.1
142.5°	597.1	582.4	560.3	547.4	534.6	507.5	478.1	450.2	423.0	398.0	374.5
145°	567.0	554.5	536.1	525.8	515.5	493.5	468.5	445.0	421.5	398.8	377.5
147.5°	541.2	530.2	516.3	507.8	499.4	481.0	460.5	440.6	419.3	399.5	380.4
150°	519.2	509.7	497.9	491.3	484.7	470.0	453.1	435.5	417.1	399.5	382.6
152.5°	499.4	492.0	482.5	477.4	472.2	459.0	445.0	429.6	413.5	398.0	384.1
155°	481.8	475.9	468.5	464.1	459.7	448.7	437.0	423.7	409.8	396.6	384.8
157.5°	465.6	461.2	455.3	451.6	448.0	438.4	428.2	417.9	406.1	395.1	384.8
160°	450.9	446.5	442.1	439.2	436.2	428.2	420.1	411.3	401.7	392.9	384.8
162.5°	437.0	432.6	429.6	427.0	424.5	418.6	412.0	405.4	397.3	390.7	384.8
165°	423.7	420.8	417.9	416.0	414.2	409.1	404.7	398.8	392.9	387.8	383.4
167.5°	411.3	409.1	407.6	406.5	405.4	401.0	397.3	392.9	388.5	384.8	381.9
170°	400.2	399.5	398.0	396.9	395.8	392.9	390.7	387.0	384.1	381.9	380.4
172.5°	390.7	390.0	389.2	388.5	387.8	386.3	384.8	381.9	379.7	378.9	378.9
175°	383.4	381.9	381.9	381.9	381.9	380.4	379.7	378.2	376.7	376.7	377.5
177.5°	377.5	376.7	377.5	377.1	376.7	376.7	376.0	375.3	374.5	374.5	376.0
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1279.9	1275.8	1272.7	1272.7	1263.5	1254.2	1249.1	1247.0	1244.9	1236.7	1225.4
5°	1332.3	1319.0	1309.7	1300.5	1285.0	1268.6	1252.1	1242.9	1229.5	1211.0	1197.7
7.5°	1390.9	1359.1	1348.8	1337.5	1306.6	1278.9	1256.3	1236.7	1215.1	1191.5	1167.8
10°	1440.3	1406.4	1383.7	1364.2	1324.1	1287.1	1253.2	1224.4	1196.6	1165.8	1137.0
12.5°	1487.6	1439.2	1415.6	1386.8	1344.7	1291.2	1247.0	1211.0	1169.9	1138.0	1103.1
15°	1553.4	1472.1	1433.1	1414.6	1358.0	1295.3	1241.9	1188.4	1154.5	1106.2	1075.3
17.5°	1563.6	1497.8	1472.1	1424.9	1357.0	1286.1	1224.4	1170.9	1119.5	1076.4	1036.3
20°	1599.6	1513.3	1472.1	1442.3	1352.9	1280.9	1213.1	1144.2	1094.9	1048.6	1003.4
22.5°	1622.2	1524.6	1481.4	1434.1	1348.8	1262.4	1182.2	1122.6	1062.0	1014.7	978.7
25°	1616.1	1518.4	1470.1	1425.9	1322.1	1235.7	1163.7	1087.7	1031.1	979.7	932.4
27.5°	1613.0	1503.0	1451.6	1402.2	1304.6	1214.1	1123.6	1062.0	999.2	939.6	904.7
30°	1604.8	1483.5	1423.8	1370.4	1268.6	1174.0	1096.9	1024.9	962.2	907.8	861.5
32.5°	1577.0	1450.6	1393.0	1335.4	1229.5	1134.9	1056.8	990.0	927.3	870.7	826.5
35°	1540.0	1411.5	1348.8	1288.1	1182.2	1086.6	1014.7	944.8	886.2	831.7	789.5
37.5°	1503.0	1366.3	1307.7	1237.8	1140.1	1040.4	966.4	903.6	849.2	792.6	746.4
40°	1449.5	1312.8	1248.0	1188.4	1074.3	980.7	912.9	856.4	802.9	749.4	710.4
42.5°	1376.5	1254.2	1187.4	1121.6	1014.7	922.1	856.4	806.0	755.6	711.4	668.2
45°	1302.5	1183.3	1123.6	1065.0	948.9	861.5	800.8	754.6	712.4	664.1	629.2
47.5°	1213.1	1112.3	1052.7	995.1	885.1	797.8	742.2	699.1	660.0	619.9	587.0
50°	1121.6	1034.2	979.7	920.1	815.2	736.1	681.6	645.6	613.7	575.7	549.0
52.5°	1022.9	946.8	900.6	843.0	750.5	677.5	622.0	586.0	559.3	531.5	507.8
55°	918.0	862.5	813.2	766.9	679.5	613.7	564.4	532.5	514.0	488.3	467.8
57.5°	823.5	770.0	740.2	687.8	611.7	546.9	507.8	481.1	459.5	444.1	427.7
60°	724.8	681.6	648.7	610.7	543.8	489.3	448.2	432.8	410.2	398.9	391.7
62.5°	630.2	599.3	568.5	539.7	480.1	428.7	397.8	378.3	365.0	353.6	347.5
65°	540.7	512.0	490.4	464.7	415.3	374.2	345.4	330.0	316.6	313.6	306.4
67.5°	453.4	441.0	417.4	396.8	354.7	322.8	301.2	281.7	274.5	271.4	265.2
70°	379.3	365.0	346.4	329.0	297.1	269.3	249.8	242.6	232.3	231.3	224.1
72.5°	312.5	295.0	281.7	268.3	244.7	220.0	209.7	199.4	194.3	190.2	187.1
75°	247.8	235.4	226.2	214.9	194.3	177.8	163.5	159.3	156.3	155.2	153.2
77.5°	185.0	176.8	172.7	161.4	147.0	132.6	126.4	120.3	120.3	118.2	119.3
80°	131.6	126.4	121.3	115.1	102.8	96.6	91.5	87.4	85.3	84.3	85.3
82.5°	83.3	80.2	79.2	75.0	66.8	63.7	59.6	56.5	56.5	56.5	56.5
85°	46.3	46.3	46.3	40.1	37.0	33.9	31.9	30.8	30.8	30.8	31.9
87.5°	19.5	19.5	16.4	16.4	15.4	13.4	12.3	12.3	13.4	13.4	14.4
90°	10.3	5.9	5.9	5.9	5.1	4.4	2.2	0.7	2.2	4.4	5.1
92.5°	111.6	66.1	56.6	47.0	33.8	22.8	14.7	10.3	14.7	22.8	33.8
95°	155.7	91.8	76.4	61.0	43.3	33.8	26.4	24.2	26.4	33.8	43.3
97.5°	148.3	97.7	84.4	71.2	55.8	47.0	40.4	40.4	40.4	47.0	55.8
100°	150.6	107.2	95.4	83.7	69.8	61.0	55.8	55.8	55.8	61.0	69.8
102.5°	157.9	119.7	108.7	97.7	84.5	76.4	72.0	70.5	72.0	76.4	84.5
105°	170.4	135.1	124.4	113.8	100.6	91.8	88.1	85.9	88.1	91.8	100.6
107.5°	183.6	151.3	140.6	130.0	117.5	108.0	104.3	102.8	104.3	108.0	117.5
110°	199.0	166.7	156.8	146.9	133.7	124.8	121.2	119.7	121.2	124.8	133.7

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	213.7	182.9	173.0	163.0	149.8	141.7	137.3	135.9	137.3	141.7	149.8
115°	229.1	199.8	189.9	179.9	166.0	158.6	153.5	151.3	153.5	158.6	166.0
117.5°	243.8	215.9	205.6	195.3	182.1	174.1	169.6	167.4	169.6	174.1	182.1
120°	259.2	231.3	221.0	210.8	198.3	190.2	185.1	183.6	185.1	190.2	198.3
122.5°	273.9	246.0	236.1	226.2	212.2	204.9	199.8	198.3	199.8	204.9	212.2
125°	287.1	260.7	250.4	240.1	226.2	218.1	213.7	210.8	213.7	218.1	226.2
127.5°	299.6	273.9	263.6	253.4	238.7	229.9	224.7	222.5	224.7	229.9	238.7
130°	312.1	287.1	276.5	265.9	251.9	240.9	235.0	232.1	235.0	240.9	251.9
132.5°	322.4	297.4	287.5	277.6	262.2	251.9	243.8	241.6	243.8	251.9	262.2
135°	331.9	307.7	298.2	288.6	273.2	260.7	253.4	250.4	253.4	260.7	273.2
137.5°	339.3	316.5	307.4	298.2	282.0	270.3	262.2	259.2	262.2	270.3	282.0
140°	346.6	324.6	315.8	307.0	291.6	279.1	271.0	268.8	271.0	279.1	291.6
142.5°	353.2	331.9	323.5	315.1	300.4	288.6	281.3	279.1	281.3	288.6	300.4
145°	357.7	338.6	330.5	322.4	308.4	298.2	290.8	288.6	290.8	298.2	308.4
147.5°	362.8	344.4	337.0	329.7	318.0	307.0	300.4	299.6	300.4	307.0	318.0
150°	366.5	350.3	343.4	336.4	325.3	316.5	310.6	309.9	310.6	316.5	325.3
152.5°	369.4	355.4	349.2	343.0	333.4	325.3	319.5	319.5	319.5	325.3	333.4
155°	372.3	359.9	354.4	348.8	340.8	333.4	329.0	328.3	329.0	333.4	340.8
157.5°	374.5	363.5	359.1	354.7	347.4	341.5	337.1	337.1	337.1	341.5	347.4
160°	376.0	367.2	363.2	359.1	353.2	348.1	345.2	345.2	345.2	348.1	353.2
162.5°	377.5	369.4	366.4	363.5	358.4	354.0	351.8	352.5	351.8	354.0	358.4
165°	377.5	370.9	368.7	366.5	362.8	359.1	357.7	357.7	357.7	359.1	362.8
167.5°	377.5	372.3	370.5	368.7	366.5	363.5	362.8	363.5	362.8	363.5	366.5
170°	376.7	373.1	372.0	370.9	369.4	367.2	366.5	367.2	366.5	367.2	369.4
172.5°	376.0	373.8	373.0	372.3	371.6	370.1	370.1	370.9	370.1	370.1	371.6
175°	375.3	373.8	373.8	373.8	373.1	372.3	372.3	373.1	372.3	372.3	373.1
177.5°	374.5	373.8	373.8	373.8	373.8	373.1	373.8	374.5	373.8	373.1	373.8
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1222.3	1218.2	1220.3	1210.0	1200.7	1187.4	1176.1	1174.0	1172.0	1178.1	1174.0
5°	1187.4	1182.2	1177.1	1164.8	1146.3	1134.9	1118.5	1117.5	1111.3	1102.1	1104.1
7.5°	1149.3	1146.3	1139.1	1119.5	1103.1	1083.5	1070.2	1058.9	1053.7	1045.5	1042.4
10°	1118.5	1107.2	1101.0	1079.4	1059.9	1039.3	1021.9	1013.6	1004.4	997.2	992.1
12.5°	1076.4	1073.3	1055.8	1038.3	1021.9	998.2	984.9	961.2	948.9	955.0	953.0
15°	1048.6	1034.2	1030.1	1005.4	977.7	962.2	937.6	922.1	917.0	907.8	896.4
17.5°	1011.6	1002.3	987.9	965.3	933.5	911.9	894.4	880.0	873.8	861.5	852.2
20°	976.6	961.2	949.9	929.3	898.5	870.7	849.2	839.9	824.5	814.2	809.1
22.5°	944.8	933.5	917.0	886.2	859.4	832.7	807.0	793.6	779.2	773.1	764.9
25°	905.7	887.2	875.9	842.0	813.2	791.6	767.9	750.5	742.2	732.0	729.9
27.5°	867.7	850.2	836.8	807.0	772.1	744.3	729.9	717.6	703.2	703.2	698.0
30°	829.6	817.3	796.7	767.9	735.0	708.3	691.9	680.6	675.4	671.3	670.3
32.5°	791.6	775.1	762.8	723.7	699.1	674.4	662.1	652.8	646.6	645.6	646.6
35°	752.5	734.0	721.7	686.7	662.1	639.4	634.3	626.1	623.0	622.0	627.1
37.5°	711.4	697.0	681.6	652.8	625.0	611.7	601.4	598.3	597.3	603.5	605.5
40°	673.4	661.0	646.6	615.8	595.2	580.8	575.7	572.6	576.7	582.9	586.0
42.5°	637.4	619.9	608.6	580.8	562.3	554.1	547.9	547.9	552.1	559.3	564.4
45°	599.3	586.0	574.7	550.0	533.5	524.3	523.3	524.3	529.4	534.6	540.7
47.5°	562.3	549.0	536.6	516.1	501.7	496.5	495.5	496.5	504.8	512.0	519.2
50°	528.4	514.0	502.7	483.2	471.9	465.7	466.7	471.9	478.0	488.3	497.6
52.5°	488.3	478.0	467.8	450.3	440.0	435.9	439.0	443.1	454.4	461.6	472.9
55°	449.3	440.0	431.8	418.4	410.2	407.1	409.2	415.3	424.6	436.9	450.3
57.5°	413.3	403.0	394.8	385.5	376.3	377.3	378.3	386.5	397.8	409.2	424.6
60°	373.2	367.0	359.8	348.5	344.4	344.4	347.5	356.7	367.0	385.5	398.9
62.5°	337.2	329.0	323.8	316.6	310.5	311.5	318.7	326.9	339.3	354.7	372.1
65°	300.2	290.9	286.8	280.7	278.6	279.6	284.8	297.1	310.5	323.8	340.3
67.5°	259.1	256.0	251.9	245.7	247.8	248.8	253.9	264.2	278.6	292.0	310.5
70°	224.1	217.9	216.9	211.8	211.8	214.9	225.1	232.3	245.7	260.1	279.6
72.5°	187.1	182.0	182.0	177.8	180.9	184.0	189.2	199.4	211.8	226.2	242.6
75°	149.1	147.0	149.1	147.0	147.0	152.1	158.3	166.5	179.9	195.3	208.7
77.5°	115.1	115.1	114.1	117.2	117.2	120.3	128.5	136.7	147.0	159.3	173.7
80°	84.3	84.3	84.3	87.4	90.5	90.5	95.6	105.9	115.1	123.4	136.7
82.5°	57.6	57.6	57.6	59.6	63.7	63.7	69.9	76.1	86.4	93.6	99.7
85°	35.0	35.0	33.9	36.0	37.0	40.1	45.2	49.3	54.5	60.7	66.8
87.5°	15.4	15.4	16.4	17.5	18.5	20.6	22.6	24.7	29.8	31.9	35.0
90°	5.9	5.9	5.9	10.3	10.3	11.8	13.2	12.5	13.2	14.0	14.7
92.5°	47.0	56.6	66.1	111.6	182.9	251.9	287.9	239.4	177.0	132.2	104.3
95°	61.0	76.4	91.8	155.7	276.1	451.7	598.5	615.4	544.2	430.4	331.9
97.5°	71.2	84.4	97.7	148.3	251.9	432.6	640.4	771.8	783.6	727.1	646.3
100°	83.7	95.4	107.2	150.6	233.5	383.4	590.5	778.5	885.7	900.4	864.4
102.5°	97.7	108.7	119.7	157.9	228.4	350.3	528.0	723.4	880.5	967.9	990.0
105°	113.8	124.4	135.1	170.4	231.3	334.1	481.8	654.3	822.5	949.6	1022.3
107.5°	130.0	140.6	151.3	183.6	240.1	329.7	451.7	597.8	751.3	888.6	990.0
110°	146.9	156.8	166.7	199.0	250.4	331.2	437.7	557.4	688.1	815.2	921.7

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	163.0	173.0	182.9	213.7	261.4	335.6	431.1	534.6	641.9	750.6	849.7
115°	179.9	189.9	199.8	229.1	273.2	341.5	429.6	522.2	614.0	704.3	790.2
117.5°	195.3	205.6	215.9	243.8	284.9	347.4	428.9	515.5	597.8	674.2	743.9
120°	210.8	221.0	231.3	259.2	297.4	354.0	428.9	510.4	587.5	655.8	714.6
122.5°	226.2	236.1	246.0	273.9	309.2	360.6	428.2	504.5	578.7	644.1	696.2
125°	240.1	250.4	260.7	287.1	320.9	367.2	427.4	497.9	568.4	631.6	682.3
127.5°	253.4	263.6	273.9	299.6	331.2	372.3	425.9	489.1	556.7	617.6	668.3
130°	265.9	276.5	287.1	312.1	340.8	378.2	425.2	481.0	542.0	600.0	649.9
132.5°	277.6	287.5	297.4	322.4	350.3	383.4	424.5	473.7	526.6	580.2	628.6
135°	288.6	298.2	307.7	331.9	358.4	388.5	423.7	466.3	512.6	560.3	605.1
137.5°	298.2	307.4	316.5	339.3	364.3	391.4	423.7	459.7	499.4	541.2	580.2
140°	307.0	315.8	324.6	346.6	370.1	395.1	423.0	454.6	488.4	522.9	555.9
142.5°	315.1	323.5	331.9	353.2	374.5	398.0	423.0	450.2	478.1	507.5	534.6
145°	322.4	330.5	338.6	357.7	377.5	398.8	421.5	445.0	468.5	493.5	515.5
147.5°	329.7	337.0	344.4	362.8	380.4	399.5	419.3	440.6	460.5	481.0	499.4
150°	336.4	343.4	350.3	366.5	382.6	399.5	417.1	435.5	453.1	470.0	484.7
152.5°	343.0	349.2	355.4	369.4	384.1	398.0	413.5	429.6	445.0	459.0	472.2
155°	348.8	354.4	359.9	372.3	384.8	396.6	409.8	423.7	437.0	448.7	459.7
157.5°	354.7	359.1	363.5	374.5	384.8	395.1	406.1	417.9	428.2	438.4	448.0
160°	359.1	363.2	367.2	376.0	384.8	392.9	401.7	411.3	420.1	428.2	436.2
162.5°	363.5	366.4	369.4	377.5	384.8	390.7	397.3	405.4	412.0	418.6	424.5
165°	366.5	368.7	370.9	377.5	383.4	387.8	392.9	398.8	404.7	409.1	414.2
167.5°	368.7	370.5	372.3	377.5	381.9	384.8	388.5	392.9	397.3	401.0	405.4
170°	370.9	372.0	373.1	376.7	380.4	381.9	384.1	387.0	390.7	392.9	395.8
172.5°	372.3	373.0	373.8	376.0	378.9	378.9	379.7	381.9	384.8	386.3	387.8
175°	373.8	373.8	373.8	375.3	377.5	376.7	376.7	378.2	379.7	380.4	381.9
177.5°	373.8	373.8	373.8	374.5	376.0	374.5	374.5	375.3	376.0	376.7	376.7
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1170.9	1169.9	1164.8	1166.8	1160.7	1162.7	1165.8	1166.8	1170.9	1167.8	1166.8
5°	1099.0	1096.9	1093.8	1090.7	1089.7	1093.8	1086.6	1088.7	1090.7	1093.8	1097.9
7.5°	1040.4	1039.3	1036.3	1031.1	1029.1	1027.0	1028.0	1035.2	1034.2	1033.2	1040.4
10°	986.9	987.9	981.8	980.7	974.6	973.5	974.6	976.6	979.7	983.8	984.9
12.5°	931.4	944.8	933.5	929.3	920.1	925.2	927.3	918.0	923.2	926.3	941.7
15°	896.4	890.3	883.1	883.1	879.0	876.9	871.8	879.0	883.1	889.2	887.2
17.5°	848.1	837.8	833.7	829.6	830.7	834.8	823.5	839.9	839.9	843.0	837.8
20°	806.0	797.8	792.6	790.6	787.5	785.4	784.4	788.5	794.7	796.7	801.9
22.5°	761.8	761.8	753.5	750.5	748.4	745.3	750.5	747.4	751.5	755.6	763.8
25°	724.8	724.8	721.7	717.6	714.5	712.4	715.5	714.5	717.6	722.7	724.8
27.5°	695.0	691.9	690.8	689.8	688.8	689.8	688.8	691.9	695.0	696.0	693.9
30°	669.3	666.2	667.2	667.2	668.2	667.2	666.2	669.3	670.3	668.2	669.3
32.5°	645.6	645.6	647.7	648.7	648.7	649.7	650.7	648.7	649.7	646.6	647.7
35°	626.1	628.1	630.2	631.2	632.2	631.2	633.3	632.2	630.2	628.1	627.1
37.5°	606.5	608.6	612.7	613.7	616.8	617.8	615.8	615.8	614.8	610.7	608.6
40°	586.0	588.0	593.2	596.3	598.3	601.4	599.3	599.3	595.2	591.1	588.0
42.5°	566.4	570.6	575.7	578.8	582.9	582.9	582.9	580.8	575.7	571.6	568.5
45°	546.9	547.9	555.1	560.3	564.4	564.4	564.4	561.3	558.2	550.0	545.9
47.5°	525.3	528.4	536.6	541.8	545.9	546.9	546.9	543.8	537.7	530.5	525.3
50°	501.7	506.8	516.1	523.3	528.4	530.5	527.4	525.3	518.1	509.9	503.7
52.5°	479.1	485.2	496.5	502.7	509.9	510.9	509.9	506.8	498.6	487.3	482.1
55°	456.4	461.6	473.9	484.2	490.4	492.4	490.4	485.2	475.0	463.6	458.5
57.5°	431.8	439.0	452.3	462.6	469.8	470.8	468.8	463.6	455.4	441.0	433.8
60°	406.1	415.3	428.7	439.0	448.2	449.3	447.2	440.0	429.7	415.3	409.2
62.5°	380.4	387.6	403.0	414.3	421.5	426.6	422.5	415.3	405.0	390.7	381.4
65°	350.6	360.8	374.2	384.5	392.7	393.7	391.7	385.5	374.2	358.8	351.6
67.5°	321.8	329.0	342.3	355.7	358.8	361.9	358.8	352.6	343.4	330.0	319.7
70°	286.8	293.0	309.4	318.7	322.8	325.9	323.8	317.7	309.4	297.1	288.9
72.5°	251.9	257.0	272.4	279.6	287.8	286.8	285.8	281.7	270.4	262.1	257.0
75°	214.9	221.0	231.3	240.6	243.6	243.6	243.6	240.6	233.4	220.0	214.9
77.5°	180.9	184.0	192.2	197.4	200.5	201.5	200.5	195.3	191.2	182.0	178.9
80°	138.8	147.0	153.2	154.2	158.3	158.3	158.3	156.3	152.1	142.9	141.9
82.5°	104.9	106.9	113.1	116.2	118.2	117.2	117.2	113.1	112.1	106.9	104.9
85°	70.9	74.0	73.0	77.1	78.1	76.1	76.1	78.1	73.0	74.0	70.9
87.5°	39.1	39.1	41.1	40.1	44.2	44.2	42.1	43.2	41.1	40.1	39.1
90°	14.7	14.7	15.4	16.2	15.4	15.4	15.4	16.2	15.4	14.7	14.7
92.5°	95.1	85.9	74.9	69.8	66.8	66.8	66.8	69.8	74.9	85.9	95.1
95°	296.3	260.7	224.7	202.0	188.7	179.2	188.7	202.0	224.7	260.7	296.3
97.5°	605.2	564.0	514.1	470.0	448.0	430.4	448.0	470.0	514.1	564.0	605.2
100°	837.2	810.0	746.1	701.3	679.3	673.4	679.3	701.3	746.1	810.0	837.2
102.5°	982.6	975.3	942.2	912.9	889.4	884.9	889.4	912.9	942.2	975.3	982.6
105°	1037.4	1052.4	1053.9	1048.0	1037.7	1033.3	1037.7	1048.0	1053.9	1052.4	1037.4
107.5°	1020.8	1051.7	1084.0	1097.2	1103.1	1103.8	1103.1	1097.2	1084.0	1051.7	1020.8
110°	962.0	1002.4	1054.6	1085.4	1098.7	1105.3	1098.7	1085.4	1054.6	1002.4	962.0

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	890.1	930.5	991.4	1030.4	1050.2	1061.9	1050.2	1030.4	991.4	930.5	890.1
115°	825.4	860.7	918.7	962.8	986.3	992.2	986.3	962.8	918.7	860.7	825.4
117.5°	774.8	805.6	857.0	895.2	920.2	923.9	920.2	895.2	857.0	805.6	774.8
120°	740.7	766.7	808.6	840.9	860.0	868.1	860.0	840.9	808.6	766.7	740.7
122.5°	718.2	740.3	774.1	800.5	815.9	824.0	815.9	800.5	774.1	740.3	718.2
125°	702.4	722.6	752.0	773.3	787.3	791.7	787.3	773.3	752.0	722.6	702.4
127.5°	687.4	706.5	735.9	755.0	766.7	771.1	766.7	755.0	735.9	706.5	687.4
130°	669.4	688.9	719.0	737.3	749.1	753.5	749.1	737.3	719.0	688.9	669.4
132.5°	648.1	667.6	696.9	718.2	729.3	733.7	729.3	718.2	696.9	667.6	648.1
135°	623.5	641.9	671.2	691.8	703.5	708.0	703.5	691.8	671.2	641.9	623.5
137.5°	597.1	614.0	641.9	663.2	672.7	677.8	672.7	663.2	641.9	614.0	597.1
140°	571.3	586.8	612.5	628.6	638.9	644.8	638.9	628.6	612.5	586.8	571.3
142.5°	547.4	560.3	582.4	597.1	605.9	609.5	605.9	597.1	582.4	560.3	547.4
145°	525.8	536.1	554.5	567.0	574.3	578.0	574.3	567.0	554.5	536.1	525.8
147.5°	507.8	516.3	530.2	541.2	547.1	548.6	547.1	541.2	530.2	516.3	507.8
150°	491.3	497.9	509.7	519.2	523.6	524.4	523.6	519.2	509.7	497.9	491.3
152.5°	477.4	482.5	492.0	499.4	501.6	502.3	501.6	499.4	492.0	482.5	477.4
155°	464.1	468.5	475.9	481.8	484.0	484.0	484.0	481.8	475.9	468.5	464.1
157.5°	451.6	455.3	461.2	465.6	467.1	467.1	467.1	465.6	461.2	455.3	451.6
160°	439.2	442.1	446.5	450.9	451.7	451.7	451.7	450.9	446.5	442.1	439.2
162.5°	427.0	429.6	432.6	437.0	437.7	437.0	437.7	437.0	432.6	429.6	427.0
165°	416.0	417.9	420.8	423.7	423.0	422.3	423.0	423.7	420.8	417.9	416.0
167.5°	406.5	407.6	409.1	411.3	411.3	410.5	411.3	411.3	409.1	407.6	406.5
170°	396.9	398.0	399.5	400.2	399.5	399.5	399.5	400.2	399.5	398.0	396.9
172.5°	388.5	389.2	390.0	390.7	390.0	388.5	390.0	390.7	390.0	389.2	388.5
175°	381.9	381.9	381.9	383.4	381.9	380.4	381.9	383.4	381.9	381.9	381.9
177.5°	377.1	377.5	376.7	377.5	376.0	374.5	376.0	377.5	376.7	377.5	377.1
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1166.8	1173.0	1166.8	1170.9	1173.0	1178.1	1180.2	1189.4	1192.5	1199.7	1199.7
5°	1096.9	1100.0	1101.0	1105.1	1109.2	1119.5	1126.7	1140.1	1155.5	1157.6	1166.8
7.5°	1040.4	1045.5	1053.7	1050.7	1057.8	1073.3	1082.5	1099.0	1114.4	1122.6	1133.9
10°	990.0	996.2	999.2	1002.3	1015.7	1029.1	1043.5	1054.8	1075.3	1087.7	1096.9
12.5°	948.9	943.7	949.9	961.2	976.6	984.9	1004.4	1021.9	1037.3	1050.7	1058.9
15°	895.4	899.5	905.7	925.2	929.3	949.9	957.1	976.6	1005.4	1017.8	1028.0
17.5°	844.0	857.4	869.7	876.9	889.2	905.7	926.3	947.8	966.4	980.7	993.1
20°	802.9	816.3	823.5	828.6	840.9	863.5	883.1	909.8	933.5	944.8	961.2
22.5°	770.0	770.0	780.3	795.7	802.9	824.5	840.9	869.7	895.4	909.8	925.2
25°	728.9	735.0	743.3	756.6	766.9	784.4	808.0	832.7	860.5	872.8	892.3
27.5°	695.0	702.1	713.5	716.5	726.8	742.2	766.9	793.6	822.4	835.8	852.2
30°	669.3	673.4	677.5	683.6	692.9	706.3	726.8	750.5	785.4	795.7	816.3
32.5°	646.6	648.7	650.7	655.9	661.0	674.4	690.8	716.5	745.3	760.7	779.2
35°	626.1	624.0	625.0	628.1	633.3	638.4	655.9	677.5	704.2	722.7	737.1
37.5°	606.5	602.4	601.4	601.4	603.5	609.6	623.0	641.5	670.3	685.7	700.1
40°	585.0	580.8	578.8	577.8	576.7	580.8	591.1	609.6	632.2	646.6	663.1
42.5°	564.4	560.3	555.1	554.1	552.1	554.1	561.3	578.8	598.3	612.7	626.1
45°	543.8	536.6	530.5	526.4	527.4	524.3	529.4	542.8	565.4	574.7	588.0
47.5°	521.2	513.0	504.8	500.7	496.5	498.6	500.7	512.0	531.5	540.7	554.1
50°	499.6	488.3	479.1	473.9	470.8	468.8	470.8	482.1	496.5	504.8	516.1
52.5°	475.0	463.6	454.4	446.2	442.1	439.0	440.0	450.3	463.6	471.9	483.2
55°	452.3	437.9	425.6	415.3	412.2	411.2	410.2	417.4	428.7	436.9	446.2
57.5°	426.6	412.2	398.9	386.5	380.4	379.3	379.3	381.4	395.8	402.0	407.1
60°	400.9	385.5	371.1	359.8	350.6	347.5	346.4	350.6	357.8	363.9	371.1
62.5°	372.1	356.7	339.3	329.0	319.7	311.5	314.6	315.6	325.9	329.0	335.1
65°	344.4	326.9	312.5	296.1	285.8	280.7	278.6	280.7	288.9	289.9	294.0
67.5°	312.5	296.1	278.6	267.3	258.0	248.8	246.7	246.7	250.8	253.9	259.1
70°	281.7	265.2	245.7	233.4	224.1	215.9	212.8	211.8	214.9	216.9	222.1
72.5°	245.7	229.3	214.9	201.5	190.2	184.0	180.9	178.9	182.0	184.0	185.0
75°	207.7	194.3	179.9	166.5	159.3	153.2	149.1	146.0	148.0	148.0	148.0
77.5°	171.7	158.3	147.0	137.8	128.5	121.3	118.2	115.1	116.2	116.2	118.2
80°	133.6	124.4	115.1	106.9	98.7	92.5	90.5	87.4	85.3	84.3	84.3
82.5°	98.7	91.5	83.3	76.1	72.0	65.8	63.7	59.6	59.6	58.6	58.6
85°	65.8	61.7	53.5	48.3	45.2	42.1	40.1	38.0	35.0	35.0	33.9
87.5°	35.0	32.9	30.8	24.7	24.7	21.6	20.6	19.5	16.4	17.5	17.5
90°	14.7	14.0	13.2	12.5	13.2	11.8	10.3	10.3	5.9	5.9	5.9
92.5°	104.3	132.2	177.0	239.4	287.9	251.9	182.9	111.6	66.1	56.6	47.0
95°	331.9	430.4	544.2	615.4	598.5	451.7	276.1	155.7	91.8	76.4	61.0
97.5°	646.3	727.1	783.6	771.8	640.4	432.6	251.9	148.3	97.7	84.4	71.2
100°	864.4	900.4	885.7	778.5	590.5	383.4	233.5	150.6	107.2	95.4	83.7
102.5°	990.0	967.9	880.5	723.4	528.0	350.3	228.4	157.9	119.7	108.7	97.7
105°	1022.3	949.6	822.5	654.3	481.8	334.1	231.3	170.4	135.1	124.4	113.8
107.5°	990.0	888.6	751.3	597.8	451.7	329.7	240.1	183.6	151.3	140.6	130.0
110°	921.7	815.2	688.1	557.4	437.7	331.2	250.4	199.0	166.7	156.8	146.9

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	849.7	750.6	641.9	534.6	431.1	335.6	261.4	213.7	182.9	173.0	163.0
115°	790.2	704.3	614.0	522.2	429.6	341.5	273.2	229.1	199.8	189.9	179.9
117.5°	743.9	674.2	597.8	515.5	428.9	347.4	284.9	243.8	215.9	205.6	195.3
120°	714.6	655.8	587.5	510.4	428.9	354.0	297.4	259.2	231.3	221.0	210.8
122.5°	696.2	644.1	578.7	504.5	428.2	360.6	309.2	273.9	246.0	236.1	226.2
125°	682.3	631.6	568.4	497.9	427.4	367.2	320.9	287.1	260.7	250.4	240.1
127.5°	668.3	617.6	556.7	489.1	425.9	372.3	331.2	299.6	273.9	263.6	253.4
130°	649.9	600.0	542.0	481.0	425.2	378.2	340.8	312.1	287.1	276.5	265.9
132.5°	628.6	580.2	526.6	473.7	424.5	383.4	350.3	322.4	297.4	287.5	277.6
135°	605.1	560.3	512.6	466.3	423.7	388.5	358.4	331.9	307.7	298.2	288.6
137.5°	580.2	541.2	499.4	459.7	423.7	391.4	364.3	339.3	316.5	307.4	298.2
140°	555.9	522.9	488.4	454.6	423.0	395.1	370.1	346.6	324.6	315.8	307.0
142.5°	534.6	507.5	478.1	450.2	423.0	398.0	374.5	353.2	331.9	323.5	315.1
145°	515.5	493.5	468.5	445.0	421.5	398.8	377.5	357.7	338.6	330.5	322.4
147.5°	499.4	481.0	460.5	440.6	419.3	399.5	380.4	362.8	344.4	337.0	329.7
150°	484.7	470.0	453.1	435.5	417.1	399.5	382.6	366.5	350.3	343.4	336.4
152.5°	472.2	459.0	445.0	429.6	413.5	398.0	384.1	369.4	355.4	349.2	343.0
155°	459.7	448.7	437.0	423.7	409.8	396.6	384.8	372.3	359.9	354.4	348.8
157.5°	448.0	438.4	428.2	417.9	406.1	395.1	384.8	374.5	363.5	359.1	354.7
160°	436.2	428.2	420.1	411.3	401.7	392.9	384.8	376.0	367.2	363.2	359.1
162.5°	424.5	418.6	412.0	405.4	397.3	390.7	384.8	377.5	369.4	366.4	363.5
165°	414.2	409.1	404.7	398.8	392.9	387.8	383.4	377.5	370.9	368.7	366.5
167.5°	405.4	401.0	397.3	392.9	388.5	384.8	381.9	377.5	372.3	370.5	368.7
170°	395.8	392.9	390.7	387.0	384.1	381.9	380.4	376.7	373.1	372.0	370.9
172.5°	387.8	386.3	384.8	381.9	379.7	378.9	378.9	376.0	373.8	373.0	372.3
175°	381.9	380.4	379.7	378.2	376.7	376.7	377.5	375.3	373.8	373.8	373.8
177.5°	376.7	376.7	376.0	375.3	374.5	374.5	376.0	374.5	373.8	373.8	373.8
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1240.8	1240.8	1240.8	1240.8
2.5°	1206.9	1217.2	1226.4	1240.8
5°	1180.2	1194.6	1214.1	1235.7
7.5°	1149.3	1172.0	1197.7	1227.5
10°	1120.6	1146.3	1179.2	1215.1
12.5°	1090.7	1121.6	1157.6	1196.6
15°	1056.8	1087.7	1127.8	1180.2
17.5°	1026.0	1063.0	1106.2	1161.7
20°	990.0	1024.9	1072.2	1136.0
22.5°	958.1	998.2	1050.7	1106.2
25°	923.2	958.1	1010.6	1077.4
27.5°	888.2	931.4	981.8	1046.5
30°	854.3	890.3	944.8	1012.6
32.5°	817.3	860.5	910.8	974.6
35°	777.2	818.3	865.6	934.5
37.5°	741.2	781.3	829.6	890.3
40°	701.1	743.3	787.5	848.1
42.5°	662.1	700.1	744.3	799.8
45°	624.0	656.9	697.0	745.3
47.5°	585.0	612.7	649.7	692.9
50°	542.8	572.6	600.4	636.4
52.5°	503.7	529.4	552.1	581.9
55°	465.7	483.2	501.7	524.3
57.5°	425.6	439.0	452.3	476.0
60°	385.5	397.8	405.0	420.5
62.5°	346.4	351.6	360.8	370.1
65°	303.3	310.5	315.6	326.9
67.5°	264.2	267.3	272.4	279.6
70°	223.1	230.3	232.3	237.5
72.5°	188.1	191.2	193.3	194.3
75°	149.1	152.1	154.2	160.4
77.5°	117.2	116.2	120.3	121.3
80°	86.4	83.3	84.3	88.4
82.5°	56.5	57.6	56.5	56.5
85°	35.0	33.9	31.9	32.9
87.5°	15.4	15.4	14.4	14.4
90°	5.1	4.4	2.2	0.7
92.5°	33.8	22.8	14.7	10.3
95°	43.3	33.8	26.4	24.2
97.5°	55.8	47.0	40.4	40.4
100°	69.8	61.0	55.8	55.8
102.5°	84.5	76.4	72.0	70.5
105°	100.6	91.8	88.1	85.9
107.5°	117.5	108.0	104.3	102.8
110°	133.7	124.8	121.2	119.7



TEST NUMBER: P1001987

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	149.8	141.7	137.3	135.9
115°	166.0	158.6	153.5	151.3
117.5°	182.1	174.1	169.6	167.4
120°	198.3	190.2	185.1	183.6
122.5°	212.2	204.9	199.8	198.3
125°	226.2	218.1	213.7	210.8
127.5°	238.7	229.9	224.7	222.5
130°	251.9	240.9	235.0	232.1
132.5°	262.2	251.9	243.8	241.6
135°	273.2	260.7	253.4	250.4
137.5°	282.0	270.3	262.2	259.2
140°	291.6	279.1	271.0	268.8
142.5°	300.4	288.6	281.3	279.1
145°	308.4	298.2	290.8	288.6
147.5°	318.0	307.0	300.4	299.6
150°	325.3	316.5	310.6	309.9
152.5°	333.4	325.3	319.5	319.5
155°	340.8	333.4	329.0	328.3
157.5°	347.4	341.5	337.1	337.1
160°	353.2	348.1	345.2	345.2
162.5°	358.4	354.0	351.8	352.5
165°	362.8	359.1	357.7	357.7
167.5°	366.5	363.5	362.8	363.5
170°	369.4	367.2	366.5	367.2
172.5°	371.6	370.1	370.1	370.9
175°	373.1	372.3	372.3	373.1
177.5°	373.8	373.1	373.8	374.5
180°	373.8	373.8	373.8	373.8

(END OF REPORT)