

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001993

Luminaire Tested: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001993
REPORT IS A COMBINATION OF REPORTS P996618 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6022.4 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001993

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001993

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001993

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.0
10°-20°	340.7	5.7
20°-30°	501.4	8.3
30°-40°	582.8	9.7
40°-50°	582.8	9.7
50°-60°	509.7	8.5
60°-70°	378.4	6.3
70°-80°	214.7	3.6
80°-90°	62.9	1.0
90°-100°	277.7	4.6
100°-110°	564.7	9.4
110°-120°	503.4	8.4
120°-130°	422.8	7.0
130°-140°	352.9	5.9
140°-150°	269.5	4.5
150°-160°	189.4	3.1
160°-170°	111.4	1.8
170°-180°	36.2	0.6
0°-30°	963.0	16.0
0°-40°	1545.9	25.7
0°-60°	2638.4	43.8
0°-90°	3294.4	54.7
90°-120°	1345.8	22.3
90°-150°	2390.9	39.7
90°-180°	2728.0	45.3
0°-180°	6022.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	1	6	13	15	15	5
95°	24	76	598	296	179	27
105°	86	124	482	1037	1033	92
115°	151	190	430	825	992	150
125°	211	250	427	702	792	188
135°	250	298	424	624	708	194
145°	289	330	422	526	578	181
155°	328	354	410	464	484	151
165°	358	369	393	416	422	101
175°	373	374	377	382	380	35
180°	374	374	374	374	374	

TEST NUMBER: P1001993

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	0.7	5.9	13.2	14.7	15.4
92.5°	10.3	56.6	287.9	95.1	66.8
95°	24.2	76.4	598.5	296.3	179.2
97.5°	40.4	84.4	640.4	605.2	430.4
100°	55.8	95.4	590.5	837.2	673.4
102.5°	70.5	108.7	528.0	982.6	884.9
105°	85.9	124.4	481.8	1037.4	1033.3
107.5°	102.8	140.6	451.7	1020.8	1103.8
110°	119.7	156.8	437.7	962.0	1105.3



TEST NUMBER: P1001993

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.9	173.0	431.1	890.1	1061.9
115°	151.3	189.9	429.6	825.4	992.2
117.5°	167.4	205.6	428.9	774.8	923.9
120°	183.6	221.0	428.9	740.7	868.1
122.5°	198.3	236.1	428.2	718.2	824.0
125°	210.8	250.4	427.4	702.4	791.7
127.5°	222.5	263.6	425.9	687.4	771.1
130°	232.1	276.5	425.2	669.4	753.5
132.5°	241.6	287.5	424.5	648.1	733.7
135°	250.4	298.2	423.7	623.5	708.0
137.5°	259.2	307.4	423.7	597.1	677.8
140°	268.8	315.8	423.0	571.3	644.8
142.5°	279.1	323.5	423.0	547.4	609.5
145°	288.6	330.5	421.5	525.8	578.0
147.5°	299.6	337.0	419.3	507.8	548.6
150°	309.9	343.4	417.1	491.3	524.4
152.5°	319.5	349.2	413.5	477.4	502.3
155°	328.3	354.4	409.8	464.1	484.0
157.5°	337.1	359.1	406.1	451.6	467.1
160°	345.2	363.2	401.7	439.2	451.7
162.5°	352.5	366.4	397.3	427.0	437.0
165°	357.7	368.7	392.9	416.0	422.3
167.5°	363.5	370.5	388.5	406.5	410.5
170°	367.2	372.0	384.1	396.9	399.5
172.5°	370.9	373.0	379.7	388.5	388.5
175°	373.1	373.8	376.7	381.9	380.4
177.5°	374.5	373.8	374.5	377.1	374.5
180°	373.8	373.8	373.8	373.8	373.8

(END OF REPORT)