

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000305

Luminaire Tested: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5097.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000305

CATALOG NUMBER: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000305

CATALOG NUMBER: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70
4	83	71	63	56	81	70	62	56	67	60	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	52	43	37	50	43	37		49	42	37		47
8	61	48	39	34	60	47	39	34	46	39	33		45	38	33		43
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16193	16193	16193
5°	16242	16047	16164
10°	16140	15916	15995
15°	15946	15690	15730
20°	15686	15410	15424
25°	15390	15090	15047
30°	15028	14713	14578
35°	14652	14319	14130
40°	14262	13872	13618
45°	13855	13433	13176
50°	13404	13040	12637
55°	12917	12532	12126
60°	12431	11963	11601
65°	11882	11421	10962
70°	11268	10698	10281
75°	10328	9827	9575
80°	9190	8819	8594
85°	8037	7738	7597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13855 cd/sqm

TEST NUMBER: P1000305

CATALOG NUMBER: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	3.7
10°-20°	527.3	10.3
20°-30°	776.1	15.2
30°-40°	902.1	17.7
40°-50°	902.1	17.7
50°-60°	789.0	15.5
60°-70°	585.7	11.5
70°-80°	332.3	6.5
80°-90°	95.2	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1490.6	29.2
0°-40°	2392.7	46.9
0°-60°	4083.7	80.1
0°-90°	5097.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5097.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1986	1986	1986	1986	1986	
5°	1984	1978	1960	1978	1975	188
15°	1889	1882	1858	1868	1863	532
25°	1710	1699	1677	1679	1672	787
35°	1472	1461	1438	1427	1419	920
45°	1201	1190	1165	1147	1142	926
55°	909	904	882	862	853	814
65°	616	608	592	576	568	609
75°	328	320	312	306	304	348
85°	86	86	83	83	81	98
90°	0	0	0	0	0	

TEST NUMBER: P1000305

CATALOG NUMBER: SA4XXDP-B1195DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1985.8	1985.8	1985.8	1985.8	1985.8
2.5°	1992.2	1987.4	1969.9	1985.8	1984.2
5°	1984.2	1977.9	1960.4	1977.9	1974.7
7.5°	1969.9	1963.5	1944.5	1958.8	1957.2
10°	1949.2	1942.9	1922.2	1934.9	1931.7
12.5°	1922.2	1915.8	1893.5	1907.9	1903.1
15°	1888.8	1882.4	1858.5	1868.1	1863.3
17.5°	1850.6	1842.6	1820.3	1826.7	1823.5
20°	1807.6	1799.7	1775.8	1780.6	1777.4
22.5°	1761.5	1750.3	1726.5	1736.0	1729.6
25°	1710.5	1699.4	1677.1	1678.7	1672.4
27.5°	1653.3	1642.1	1621.4	1618.3	1610.3
30°	1596.0	1583.2	1562.6	1556.2	1548.2
32.5°	1535.5	1524.4	1502.1	1494.1	1486.2
35°	1471.9	1460.7	1438.4	1427.3	1419.4
37.5°	1405.0	1395.5	1371.6	1360.5	1349.3
40°	1339.8	1327.1	1303.2	1287.3	1279.3
42.5°	1269.8	1263.4	1236.4	1217.3	1212.5
45°	1201.4	1190.2	1164.8	1147.3	1142.5
47.5°	1129.8	1121.8	1097.9	1078.8	1066.1
50°	1056.6	1050.2	1027.9	1005.6	996.1
52.5°	985.0	977.0	953.1	934.0	921.3
55°	908.6	903.8	881.5	862.4	852.9
57.5°	837.0	832.2	809.9	790.8	781.3
60°	762.2	754.2	733.5	719.2	711.3
62.5°	689.0	682.6	660.3	647.6	639.7
65°	615.8	607.8	591.9	576.0	568.1
67.5°	541.0	534.6	518.7	502.8	501.2
70°	472.6	461.4	448.7	436.0	431.2
72.5°	399.4	388.3	378.7	369.2	364.4
75°	327.8	319.8	311.9	305.5	303.9
77.5°	257.8	254.6	246.6	245.0	240.3
80°	195.7	190.9	187.8	184.6	183.0
82.5°	135.3	133.7	133.7	132.1	130.5
85°	85.9	85.9	82.7	82.7	81.2
87.5°	41.4	39.8	38.2	38.2	38.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)