

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001051

Luminaire Tested: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001051
REPORT IS A COMBINATION OF REPORTS P995667 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7895.7 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001051

CATALOG NUMBER: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001051

CATALOG NUMBER: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	89	95	91	87	84	80	77	75	70	68	67	61	60	59
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49
3	84	74	67	61	78	70	63	58	62	57	52	55	50	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1001051

CATALOG NUMBER: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.4
10°-20°	525.8	6.7
20°-30°	773.8	9.8
30°-40°	899.5	11.4
40°-50°	899.4	11.4
50°-60°	786.6	10.0
60°-70°	584.0	7.4
70°-80°	331.4	4.2
80°-90°	96.4	1.2
90°-100°	286.2	3.6
100°-110°	582.2	7.4
110°-120°	518.9	6.6
120°-130°	435.9	5.5
130°-140°	363.7	4.6
140°-150°	277.8	3.5
150°-160°	195.3	2.5
160°-170°	114.8	1.5
170°-180°	37.3	0.5
0°-30°	1486.2	18.8
0°-40°	2385.7	30.2
0°-60°	4071.7	51.6
0°-90°	5083.5	64.4
90°-120°	1387.3	17.6
90°-150°	2464.7	31.2
90°-180°	2812.0	35.6
0°-180°	7895.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	1	6	14	15	16	7
95°	25	79	617	305	185	27
105°	89	128	497	1069	1065	94
115°	156	196	443	851	1023	155
125°	217	258	441	724	816	194
135°	258	307	437	643	730	200
145°	298	341	434	542	596	187
155°	338	365	422	478	499	156
165°	369	380	405	429	435	104
175°	385	385	388	394	392	37
180°	385	385	385	385	385	

TEST NUMBER: P1001051

CATALOG NUMBER: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	0.8	6.1	13.6	15.1	15.9
92.5°	10.6	58.3	296.8	98.0	68.9
95°	25.0	78.7	617.0	305.4	184.7
97.5°	41.6	87.1	660.1	623.8	443.6
100°	57.5	98.4	608.7	863.0	694.2
102.5°	72.7	112.0	544.3	1013.0	912.2
105°	88.6	128.3	496.6	1069.3	1065.2
107.5°	106.0	145.0	465.6	1052.3	1137.8
110°	123.4	161.6	451.2	991.8	1139.3



TEST NUMBER: P1001051

CATALOG NUMBER: SA4XXDIP-B1195D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.1	178.3	444.4	917.6	1094.7
115°	156.0	195.7	442.9	851.0	1022.8
117.5°	172.6	212.0	442.1	798.7	952.4
120°	189.3	227.9	442.1	763.5	894.8
122.5°	204.4	243.4	441.4	740.4	849.4
125°	217.3	258.2	440.6	724.1	816.1
127.5°	229.4	271.8	439.1	708.6	794.9
130°	239.2	285.0	438.3	690.0	776.7
132.5°	249.1	296.4	437.6	668.1	756.3
135°	258.2	307.4	436.8	642.8	729.8
137.5°	267.2	316.8	436.8	615.5	698.7
140°	277.1	325.5	436.1	589.0	664.7
142.5°	287.7	333.5	436.1	564.4	628.3
145°	297.5	340.6	434.5	542.0	595.8
147.5°	308.9	347.5	432.3	523.5	565.5
150°	319.5	353.9	430.0	506.4	540.5
152.5°	329.3	360.0	426.2	492.1	517.8
155°	338.4	365.3	422.4	478.4	498.9
157.5°	347.5	370.2	418.6	465.6	481.5
160°	355.8	374.4	414.1	452.7	465.6
162.5°	363.4	377.8	409.6	440.2	450.4
165°	368.7	380.0	405.0	428.9	435.3
167.5°	374.7	381.9	400.5	419.0	423.2
170°	378.5	383.5	395.9	409.2	411.8
172.5°	382.3	384.6	391.4	400.4	400.5
175°	384.6	385.3	388.4	393.7	392.1
177.5°	386.1	385.3	386.1	388.8	386.1
180°	385.3	385.3	385.3	385.3	385.3

(END OF REPORT)