

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001101

Luminaire Tested: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001101
REPORT IS A COMBINATION OF REPORTS P995717 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7565.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001101

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001101

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1001101

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.4
10°-20°	509.9	6.7
20°-30°	750.5	9.9
30°-40°	872.4	11.5
40°-50°	872.3	11.5
50°-60°	763.0	10.1
60°-70°	566.4	7.5
70°-80°	321.4	4.2
80°-90°	94.1	1.2
90°-100°	61.9	0.8
100°-110°	185.3	2.4
110°-120°	314.8	4.2
120°-130°	415.2	5.5
130°-140°	466.4	6.2
140°-150°	458.4	6.1
150°-160°	385.5	5.1
160°-170°	256.5	3.4
170°-180°	89.8	1.2
0°-30°	1441.4	19.1
0°-40°	2313.8	30.6
0°-60°	3949.1	52.2
0°-90°	4931.0	65.2
90°-120°	562.1	7.4
90°-150°	1902.1	25.1
90°-180°	2634.0	34.8
0°-180°	7565.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	2	10	16	21	22	9
95°	44	51	56	58	58	48
105°	171	172	175	177	179	181
115°	320	320	319	318	317	316
125°	466	466	466	464	462	416
135°	601	606	606	604	602	465
145°	730	734	734	734	731	457
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1001101

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	2.2	10.3	16.2	20.6	22.0
92.5°	19.1	28.6	32.3	34.5	35.2
95°	44.1	50.7	55.8	58.0	58.0
97.5°	70.5	76.4	82.2	85.2	85.2
100°	102.8	105.7	112.3	113.8	113.8
102.5°	136.6	137.3	143.2	145.4	146.1
105°	171.1	171.8	174.7	176.9	179.1
107.5°	207.0	207.8	208.5	211.4	210.7
110°	243.8	245.2	244.5	243.0	245.2

TEST NUMBER: P1001101

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	281.9	280.5	280.5	280.5
115°	320.1	320.1	318.6	317.9	317.2
117.5°	356.1	356.1	355.3	353.1	350.9
120°	392.1	395.0	392.8	389.1	390.6
122.5°	429.5	430.2	429.5	427.3	423.6
125°	466.2	466.2	465.5	464.0	462.5
127.5°	499.2	501.5	500.0	498.5	497.8
130°	534.5	536.7	536.7	535.2	532.3
132.5°	570.5	571.9	571.2	569.7	569.0
135°	601.3	605.7	605.7	604.2	602.0
137.5°	635.8	638.0	639.5	637.3	638.0
140°	670.3	671.8	671.8	671.0	670.3
142.5°	701.9	703.4	702.6	702.6	702.6
145°	730.5	733.5	734.2	733.5	731.3
147.5°	759.9	763.6	762.8	762.1	761.4
150°	786.3	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)