

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001134

Luminaire Tested: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001134
REPORT IS A COMBINATION OF REPORTS P995750 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5024.0 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001134

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001134

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	53	46	40	58	48	42	36	38	33	30	29	26	23	21	18	17
6	59	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4690	4690	4690
5°	4693	4555	4560
10°	4654	4428	4397
15°	4587	4278	4213
20°	4502	4115	4023
25°	4405	3944	3818
30°	4290	3758	3593
35°	4170	3567	3375
40°	4045	3363	3144
45°	3914	3157	2928
50°	3770	2959	2689
55°	3612	2726	2451
60°	3450	2471	2203
65°	3265	2209	1924
70°	3054	1892	1625
75°	2735	1525	1301
80°	2332	1103	916
85°	1812	615	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3914 cd/sqm

TEST NUMBER: P1001134

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.1
10°-20°	152.7	3.0
20°-30°	224.7	4.5
30°-40°	261.2	5.2
40°-50°	261.2	5.2
50°-60°	228.5	4.5
60°-70°	169.6	3.4
70°-80°	96.2	1.9
80°-90°	30.3	0.6
90°-100°	83.3	1.7
100°-110°	249.5	5.0
110°-120°	423.8	8.4
120°-130°	558.9	11.1
130°-140°	627.7	12.5
140°-150°	617.0	12.3
150°-160°	518.9	10.3
160°-170°	345.3	6.9
170°-180°	120.9	2.4
0°-30°	431.6	8.6
0°-40°	692.9	13.8
0°-60°	1182.6	23.5
0°-90°	1478.7	29.4
90°-120°	756.6	15.1
90°-150°	2560.2	51.0
90°-180°	3545.0	70.6
0°-180°	5024.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	575	573	568	573	572	55
15°	547	545	538	541	540	154
25°	495	492	486	486	484	228
35°	426	423	416	413	411	267
45°	348	345	337	332	331	268
55°	263	262	255	250	247	236
65°	178	176	171	167	164	176
75°	95	93	90	88	88	101
85°	25	25	24	24	24	27
90°	3	14	22	28	30	6
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	628	628	626	624	623	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1126	1130	1126	518
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1001134

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.1	575.1	575.1	575.1	575.1
2.5°	576.9	575.5	570.5	575.1	574.6
5°	574.6	572.8	567.7	572.8	571.8
7.5°	570.5	568.6	563.1	567.2	566.8
10°	564.5	562.6	556.6	560.3	559.4
12.5°	556.6	554.8	548.3	552.5	551.1
15°	547.0	545.1	538.2	541.0	539.6
17.5°	535.9	533.6	527.1	529.0	528.1
20°	523.5	521.1	514.2	515.6	514.7
22.5°	510.1	506.9	500.0	502.7	500.9
25°	495.3	492.1	485.7	486.1	484.3
27.5°	478.8	475.5	469.5	468.6	466.3
30°	462.2	458.5	452.5	450.6	448.3
32.5°	444.7	441.4	435.0	432.7	430.4
35°	426.2	423.0	416.5	413.3	411.0
37.5°	406.9	404.1	397.2	394.0	390.7
40°	388.0	384.3	377.4	372.8	370.5
42.5°	367.7	365.9	358.0	352.5	351.1
45°	347.9	344.7	337.3	332.2	330.8
47.5°	327.2	324.9	317.9	312.4	308.7
50°	306.0	304.1	297.7	291.2	288.5
52.5°	285.2	282.9	276.0	270.5	266.8
55°	263.1	261.7	255.3	249.7	247.0
57.5°	242.4	241.0	234.5	229.0	226.2
60°	220.7	218.4	212.4	208.3	206.0
62.5°	199.5	197.7	191.2	187.5	185.2
65°	178.3	176.0	171.4	166.8	164.5
67.5°	156.7	154.8	150.2	145.6	145.1
70°	136.9	133.6	129.9	126.3	124.9
72.5°	115.7	112.4	109.7	106.9	105.5
75°	94.9	92.6	90.3	88.5	88.0
77.5°	74.6	73.7	71.4	71.0	69.6
80°	56.7	55.3	54.4	53.5	53.0
82.5°	39.2	38.7	38.7	38.2	37.8
85°	24.9	24.9	24.0	24.0	23.5
87.5°	12.0	11.5	11.1	11.1	11.1
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.1	78.1
97.5°	94.9	102.8	110.7	114.6	114.6
100°	138.3	142.3	151.2	153.2	153.2
102.5°	183.8	184.8	192.7	195.7	196.7
105°	230.3	231.2	235.2	238.2	241.1
107.5°	278.7	279.7	280.6	284.6	283.6
110°	328.1	330.1	329.1	327.1	330.1

TEST NUMBER: P1001134

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.5	379.5	377.5	377.5	377.5
115°	430.9	430.9	428.9	427.9	426.9
117.5°	479.3	479.3	478.3	475.3	472.4
120°	527.7	531.7	528.7	523.7	525.7
122.5°	578.1	579.1	578.1	575.1	570.2
125°	627.5	627.5	626.5	624.5	622.6
127.5°	672.0	674.9	673.0	671.0	670.0
130°	719.4	722.4	722.4	720.4	716.4
132.5°	767.8	769.8	768.8	766.8	765.9
135°	809.3	815.3	815.3	813.3	810.3
137.5°	855.8	858.7	860.7	857.8	858.7
140°	902.2	904.2	904.2	903.2	902.2
142.5°	944.7	946.7	945.7	945.7	945.7
145°	983.3	987.2	988.2	987.2	984.2
147.5°	1022.8	1027.7	1026.7	1025.8	1024.8
150°	1058.4	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)