

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001143

Luminaire Tested: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001143
REPORT IS A COMBINATION OF REPORTS P995759 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5045.0 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001143

CATALOG NUMBER: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001143

CATALOG NUMBER: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	53	46	40	58	48	42	36	38	33	30	29	26	23	21	18	17
6	59	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4708	4708	4708
5°	4712	4573	4579
10°	4673	4446	4415
15°	4606	4295	4230
20°	4520	4132	4039
25°	4424	3959	3834
30°	4307	3772	3608
35°	4187	3581	3389
40°	4062	3376	3157
45°	3930	3171	2940
50°	3784	2971	2699
55°	3627	2737	2461
60°	3464	2482	2212
65°	3278	2218	1932
70°	3065	1900	1631
75°	2746	1532	1307
80°	2340	1107	919
85°	1819	618	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3930 cd/sqm

TEST NUMBER: P1001143

CATALOG NUMBER: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.1
10°-20°	153.3	3.0
20°-30°	225.7	4.5
30°-40°	262.3	5.2
40°-50°	262.3	5.2
50°-60°	229.4	4.5
60°-70°	170.3	3.4
70°-80°	96.6	1.9
80°-90°	30.4	0.6
90°-100°	83.6	1.7
100°-110°	250.5	5.0
110°-120°	425.6	8.4
120°-130°	561.3	11.1
130°-140°	630.4	12.5
140°-150°	619.6	12.3
150°-160°	521.1	10.3
160°-170°	346.7	6.9
170°-180°	121.4	2.4
0°-30°	433.4	8.6
0°-40°	695.7	13.8
0°-60°	1187.4	23.5
0°-90°	1484.8	29.4
90°-120°	759.7	15.1
90°-150°	2571.0	51.0
90°-180°	3560.0	70.6
0°-180°	5045.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	577	575	570	575	574	55
15°	549	547	540	543	542	155
25°	497	494	488	488	486	229
35°	428	425	418	415	413	268
45°	349	346	339	334	332	269
55°	264	263	256	251	248	237
65°	179	177	172	168	165	177
75°	95	93	91	89	88	101
85°	25	25	24	24	24	27
90°	3	14	22	28	30	6
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1001143

CATALOG NUMBER: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	577.4	577.4	577.4	577.4	577.4
2.5°	579.2	577.9	572.8	577.4	576.9
5°	576.9	575.1	570.0	575.1	574.2
7.5°	572.8	570.9	565.4	569.5	569.1
10°	566.8	564.9	558.9	562.6	561.7
12.5°	558.9	557.0	550.6	554.7	553.3
15°	549.2	547.3	540.4	543.2	541.8
17.5°	538.1	535.8	529.3	531.1	530.2
20°	525.6	523.3	516.3	517.7	516.8
22.5°	512.2	508.9	502.0	504.8	502.9
25°	497.4	494.1	487.6	488.1	486.3
27.5°	480.7	477.5	471.4	470.5	468.2
30°	464.0	460.3	454.3	452.5	450.2
32.5°	446.5	443.2	436.7	434.4	432.1
35°	428.0	424.7	418.2	415.0	412.7
37.5°	408.5	405.8	398.8	395.6	392.3
40°	389.6	385.9	378.9	374.3	372.0
42.5°	369.2	367.3	359.5	353.9	352.5
45°	349.3	346.1	338.7	333.6	332.2
47.5°	328.5	326.2	319.2	313.7	310.0
50°	307.2	305.4	298.9	292.4	289.6
52.5°	286.4	284.1	277.1	271.6	267.9
55°	264.2	262.8	256.3	250.8	248.0
57.5°	243.4	242.0	235.5	229.9	227.2
60°	221.6	219.3	213.3	209.1	206.8
62.5°	200.3	198.5	192.0	188.3	186.0
65°	179.0	176.7	172.1	167.5	165.2
67.5°	157.3	155.5	150.8	146.2	145.7
70°	137.4	134.2	130.5	126.8	125.4
72.5°	116.1	112.9	110.1	107.3	105.9
75°	95.3	93.0	90.7	88.8	88.4
77.5°	75.0	74.0	71.7	71.2	69.9
80°	56.9	55.5	54.6	53.7	53.2
82.5°	39.3	38.9	38.9	38.4	37.9
85°	25.0	25.0	24.1	24.1	23.6
87.5°	12.0	11.6	11.1	11.1	11.1
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1001143

CATALOG NUMBER: SA4XXDIP-B350D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)