

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001152

Luminaire Tested: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001152
REPORT IS A COMBINATION OF REPORTS P995768 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4996.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001152

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001152

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	53	46	40	58	48	42	36	38	33	30	29	26	23	21	18	17
6	59	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3893 cd/sqm

TEST NUMBER: P1001152

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.1
10°-20°	151.9	3.0
20°-30°	223.5	4.5
30°-40°	259.8	5.2
40°-50°	259.8	5.2
50°-60°	227.2	4.5
60°-70°	168.7	3.4
70°-80°	95.7	1.9
80°-90°	30.1	0.6
90°-100°	82.8	1.7
100°-110°	248.1	5.0
110°-120°	421.4	8.4
120°-130°	555.8	11.1
130°-140°	624.2	12.5
140°-150°	613.5	12.3
150°-160°	516.0	10.3
160°-170°	343.3	6.9
170°-180°	120.2	2.4
0°-30°	429.3	8.6
0°-40°	689.1	13.8
0°-60°	1176.2	23.5
0°-90°	1470.7	29.4
90°-120°	752.3	15.1
90°-150°	2545.8	51.0
90°-180°	3525.0	70.6
0°-180°	4996.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	3	14	22	28	30	6
95°	59	68	75	78	78	64
105°	229	230	234	237	240	243
115°	428	428	426	426	424	423
125°	624	624	623	621	619	556
135°	805	811	811	809	806	623
145°	978	982	983	982	979	612
155°	1120	1120	1119	1123	1119	516
165°	1219	1216	1214	1220	1216	344
175°	1269	1264	1263	1270	1263	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1001152

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	2.9	13.8	21.6	27.5	29.5
92.5°	25.5	38.3	43.2	46.2	47.2
95°	59.0	67.8	74.7	77.6	77.6
97.5°	94.3	102.2	110.1	114.0	114.0
100°	137.6	141.5	150.3	152.3	152.3
102.5°	182.8	183.8	191.6	194.6	195.5
105°	229.0	229.9	233.9	236.8	239.8
107.5°	277.1	278.1	279.1	283.0	282.0
110°	326.2	328.2	327.2	325.3	328.2

TEST NUMBER: P1001152

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.3	377.3	375.4	375.4	375.4
115°	428.4	428.4	426.5	425.5	424.5
117.5°	476.6	476.6	475.6	472.6	469.7
120°	524.7	528.7	525.7	520.8	522.8
122.5°	574.8	575.8	574.8	571.9	567.0
125°	624.0	624.0	623.0	621.0	619.1
127.5°	668.2	671.1	669.2	667.2	666.2
130°	715.4	718.3	718.3	716.3	712.4
132.5°	763.5	765.5	764.5	762.5	761.5
135°	804.8	810.7	810.7	808.7	805.8
137.5°	851.0	853.9	855.9	852.9	853.9
140°	897.1	899.1	899.1	898.1	897.1
142.5°	939.4	941.4	940.4	940.4	940.4
145°	977.7	981.6	982.6	981.6	978.7
147.5°	1017.0	1021.9	1021.0	1020.0	1019.0
150°	1052.4	1056.3	1056.3	1056.3	1055.3
152.5°	1085.8	1087.8	1088.8	1091.7	1088.8
155°	1120.2	1120.2	1119.2	1123.1	1119.2
157.5°	1149.7	1147.7	1147.7	1150.7	1147.7
160°	1175.2	1174.2	1173.3	1176.2	1171.3
162.5°	1198.8	1195.9	1194.9	1200.8	1195.9
165°	1219.4	1216.5	1214.5	1220.4	1216.5
167.5°	1236.1	1232.2	1232.2	1238.1	1232.2
170°	1249.9	1245.0	1246.0	1251.9	1245.0
172.5°	1259.7	1255.8	1255.8	1262.7	1255.8
175°	1268.6	1263.7	1262.7	1269.6	1262.7
177.5°	1272.5	1267.6	1267.6	1274.5	1266.6
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)