

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001153

Luminaire Tested: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001153
REPORT IS A COMBINATION OF REPORTS P995769 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5120.3 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001153

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001153

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	37	37	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	31	31	24
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26	26	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	22	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	21	19	19	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16	16	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	14	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	13	13	10
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11	11	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	10	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3893 cd/sqm

TEST NUMBER: P1001153

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.1
10°-20°	151.9	3.0
20°-30°	223.5	4.4
30°-40°	259.8	5.1
40°-50°	259.8	5.1
50°-60°	227.2	4.4
60°-70°	168.7	3.3
70°-80°	95.7	1.9
80°-90°	29.3	0.6
90°-100°	371.5	7.3
100°-110°	755.7	14.8
110°-120°	673.6	13.2
120°-130°	565.8	11.1
130°-140°	472.2	9.2
140°-150°	360.6	7.0
150°-160°	253.5	5.0
160°-170°	149.1	2.9
170°-180°	48.5	0.9
0°-30°	429.3	8.4
0°-40°	689.1	13.5
0°-60°	1176.2	23.0
0°-90°	1469.9	28.7
90°-120°	1800.8	35.2
90°-150°	3199.4	62.5
90°-180°	3650.0	71.3
0°-180°	5120.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	1	8	18	20	21	4
95°	32	102	801	396	240	36
105°	115	167	645	1388	1383	122
115°	202	254	575	1105	1328	201
125°	282	335	572	940	1059	251
135°	335	399	567	834	947	259
145°	386	442	564	704	773	242
155°	439	474	548	621	648	203
165°	479	493	526	557	565	135
175°	499	500	504	511	509	47
180°	500	500	500	500	500	

TEST NUMBER: P1001153

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	1.0	7.9	17.7	19.7	20.6
92.5°	13.8	75.6	385.2	127.2	89.4
95°	32.4	102.2	800.9	396.5	239.8
97.5°	54.0	113.0	856.9	809.8	575.9
100°	74.7	127.8	790.1	1120.2	901.1
102.5°	94.3	145.4	706.6	1314.8	1184.2
105°	115.0	166.6	644.6	1388.1	1382.7
107.5°	137.6	188.2	604.4	1366.0	1477.0
110°	160.2	209.8	585.7	1287.4	1479.0

TEST NUMBER: P1001153

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	231.4	576.8	1191.0	1421.0
115°	202.4	254.0	574.9	1104.6	1327.6
117.5°	224.1	275.2	573.9	1036.8	1236.2
120°	245.7	295.8	573.9	991.0	1161.5
122.5°	265.3	316.0	572.9	961.1	1102.6
125°	282.0	335.1	571.9	940.0	1059.3
127.5°	297.8	352.8	570.0	919.8	1031.8
130°	310.5	370.0	569.0	895.8	1008.2
132.5°	323.3	384.8	568.0	867.2	981.7
135°	335.1	399.0	567.0	834.3	947.3
137.5°	346.9	411.2	567.0	798.9	907.0
140°	359.7	422.6	566.0	764.6	862.8
142.5°	373.4	432.9	566.0	732.6	815.6
145°	386.2	442.2	564.1	703.6	773.4
147.5°	400.9	451.0	561.1	679.5	734.1
150°	414.7	459.4	558.2	657.4	701.6
152.5°	427.5	467.2	553.3	638.8	672.2
155°	439.3	474.2	548.3	621.1	647.6
157.5°	451.1	480.5	543.4	604.3	625.0
160°	461.9	485.9	537.5	587.7	604.4
162.5°	471.7	490.4	531.6	571.4	584.7
165°	478.6	493.4	525.7	556.7	565.1
167.5°	486.4	495.8	519.8	543.9	549.3
170°	491.3	497.8	514.0	531.2	534.6
172.5°	496.3	499.2	508.1	519.8	519.8
175°	499.2	500.2	504.1	511.0	509.0
177.5°	501.2	500.2	501.2	504.6	501.2
180°	500.2	500.2	500.2	500.2	500.2

(END OF REPORT)