

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331374-927

Luminaire Tested: **SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331374-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5474.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331374-927
CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	27	26	23	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.4
10°-20°	222.5	4.1
20°-30°	327.1	6.0
30°-40°	379.9	6.9
40°-50°	379.5	6.9
50°-60°	331.0	6.0
60°-70°	244.7	4.5
70°-80°	138.6	2.5
80°-90°	41.6	0.8
90°-100°	191.3	3.5
100°-110°	649.3	11.9
110°-120°	689.8	12.6
120°-130°	567.8	10.4
130°-140°	456.0	8.3
140°-150°	344.6	6.3
150°-160°	242.2	4.4
160°-170°	142.6	2.6
170°-180°	46.4	0.8
0°-30°	628.7	11.5
0°-40°	1008.6	18.4
0°-60°	1719.1	31.4
0°-90°	2144.1	39.2
90°-120°	1530.4	28.0
90°-150°	2898.8	53.0
90°-180°	3330.0	60.8
0°-180°	5474.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	12	31	30	30	3
95°	32	79	361	136	105	34
105°	112	169	682	1219	1037	119
115°	198	250	570	1177	1365	196
125°	276	327	548	954	1107	245
135°	324	386	542	802	918	250
145°	370	425	539	670	732	232
155°	421	454	524	592	616	193
165°	458	472	502	532	540	129
175°	478	478	482	488	487	45
180°	479	479	479	479	479	



TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.8	12.1	12.5	12.6	12.7	13.0	13.6	14.6	15.4	15.3	14.7
90°	1.0	3.6	7.4	9.2	11.0	13.8	18.4	24.9	30.3	31.3	30.3
92.5°	11.2	16.2	22.8	26.9	33.1	41.7	62.6	91.8	118.0	119.6	101.1
95°	32.2	35.9	45.1	53.4	68.1	90.2	132.5	212.5	319.3	360.8	315.7
97.5°	52.4	57.4	67.2	79.7	96.6	121.7	174.8	286.4	463.8	615.8	646.0
100°	70.8	73.6	81.9	96.6	115.0	140.8	189.6	301.8	500.6	727.0	859.5
102.5°	87.8	89.8	98.1	112.8	132.0	157.7	202.8	302.6	486.6	730.7	939.1
105°	112.3	116.0	122.4	136.2	156.5	182.2	225.5	307.4	459.2	681.9	926.7
107.5°	138.8	141.7	148.0	160.7	180.8	206.7	248.7	320.0	445.6	629.6	845.9
110°	156.5	160.1	165.6	177.6	196.9	223.6	264.1	330.3	442.7	604.6	795.1



TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.6	176.3	182.6	193.8	212.4	239.8	278.8	341.4	443.4	588.4	759.8
115°	197.9	202.5	207.9	219.0	237.4	262.3	301.8	358.0	447.3	570.5	716.0
117.5°	224.0	227.7	233.2	243.0	260.6	286.4	323.0	375.7	453.8	561.9	688.3
120°	240.2	243.8	249.4	257.7	276.1	301.8	337.7	387.5	458.3	556.7	673.6
122.5°	255.6	258.6	264.1	273.1	291.5	318.1	351.7	397.8	463.4	553.8	661.1
125°	276.1	278.8	284.4	295.4	313.8	339.6	372.7	414.2	471.2	548.5	643.3
127.5°	292.2	296.0	303.7	315.8	333.5	360.0	392.2	429.4	479.1	545.3	626.7
130°	301.8	305.5	314.7	327.6	346.0	371.8	404.0	438.9	485.0	543.8	615.7
132.5°	310.7	315.1	325.0	338.7	357.8	383.6	414.3	448.5	490.8	543.1	606.8
135°	323.9	327.6	338.7	352.4	373.6	399.4	428.8	461.1	497.9	542.0	594.5
137.5°	336.4	340.9	351.9	366.6	387.6	411.5	440.6	470.6	504.1	541.9	585.8
140°	346.0	349.7	360.8	375.5	395.7	419.6	447.3	475.8	507.1	541.1	580.7
142.5°	355.6	358.5	368.8	383.6	403.1	425.6	452.4	480.2	509.3	541.1	575.5
145°	369.9	373.6	382.9	396.6	415.0	435.3	460.1	485.9	511.7	539.2	568.7
147.5°	385.4	388.2	397.0	409.7	425.0	443.0	466.4	489.0	512.4	536.0	561.7
150°	395.7	398.5	405.8	417.8	431.6	448.1	469.4	490.5	511.7	533.8	555.8
152.5°	406.0	407.3	414.6	425.2	438.2	453.3	472.3	491.2	510.2	530.0	550.6
155°	420.6	421.4	427.0	437.1	447.3	461.1	476.7	492.3	507.9	523.6	541.1
157.5°	432.7	433.6	438.1	446.9	455.0	466.6	479.8	492.3	503.7	517.0	532.1
160°	440.8	441.7	445.4	452.7	460.1	470.2	481.3	492.3	501.5	512.6	525.5
162.5°	448.9	448.4	452.0	457.9	464.5	472.5	482.0	491.6	499.3	508.9	519.6
165°	458.3	457.4	459.2	464.7	469.4	474.8	483.2	489.6	495.1	501.5	509.8
167.5°	466.0	464.9	466.6	470.1	473.4	476.9	482.9	488.3	490.8	495.1	500.3
170°	471.2	469.4	470.2	473.0	474.8	477.6	482.2	486.8	488.6	491.4	495.1
172.5°	474.1	473.0	472.5	475.2	476.3	478.3	481.5	484.6	485.7	487.0	490.0
175°	477.6	476.7	475.8	477.6	477.6	478.6	480.4	482.2	481.3	482.2	483.2
177.5°	479.3	477.8	477.1	478.6	478.6	478.6	479.3	480.8	479.3	478.6	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	14.1	13.3	13.2	13.2	13.0	12.8	12.7	12.5
90°	29.5	27.6	29.5	30.3	30.3	30.3	30.3	30.3
92.5°	80.2	68.8	61.1	55.4	54.7	51.7	52.4	51.0
95°	241.1	185.0	146.3	126.0	114.1	106.8	104.0	104.9
97.5°	562.6	460.3	360.8	294.3	250.3	227.7	214.2	206.5
100°	840.2	726.1	600.0	488.6	412.3	372.7	346.0	329.5
102.5°	1022.1	996.2	904.0	786.1	703.1	635.6	602.2	579.8
105°	1118.1	1222.1	1234.1	1203.7	1146.6	1089.6	1050.0	1037.1
107.5°	1048.9	1205.5	1301.2	1345.8	1353.0	1349.8	1341.9	1324.8
110°	989.3	1154.0	1271.8	1347.3	1386.8	1404.3	1412.6	1411.7



TEST NUMBER: P331374-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	934.8	1092.9	1218.8	1305.3	1360.3	1389.6	1405.3	1410.2
115°	867.8	1009.6	1130.0	1224.9	1290.2	1332.5	1356.5	1364.8
117.5°	817.4	941.8	1051.1	1140.0	1206.7	1251.3	1276.6	1283.6
120°	792.3	906.4	1004.0	1087.7	1152.1	1195.4	1222.1	1231.3
122.5°	772.5	877.0	969.4	1045.0	1102.8	1145.3	1169.1	1176.8
125°	743.5	838.4	919.3	988.3	1041.7	1076.7	1099.7	1107.1
127.5°	715.0	800.8	877.2	940.9	987.5	1020.2	1040.1	1046.0
130°	696.6	775.8	848.5	909.2	954.3	985.6	1004.0	1011.4
132.5°	679.0	752.3	819.0	876.1	920.4	951.7	968.7	975.3
135°	654.3	715.0	775.8	827.3	866.9	897.2	913.8	917.5
137.5°	634.6	685.4	733.6	778.6	814.6	840.7	855.3	860.8
140°	622.1	666.3	708.6	749.1	778.6	802.5	816.3	821.8
142.5°	611.8	649.4	685.8	719.6	747.6	769.4	781.6	782.8
145°	597.2	627.6	656.2	682.9	704.9	720.6	729.8	732.5
147.5°	586.1	610.0	632.2	651.7	669.9	682.5	688.7	690.4
150°	577.9	598.2	617.5	634.1	647.8	658.9	664.4	665.4
152.5°	569.8	588.6	605.0	619.3	630.2	639.8	643.8	644.0
155°	558.6	573.3	587.1	597.2	607.4	613.8	617.5	615.7
157.5°	545.5	557.9	569.4	577.3	584.6	589.9	591.5	591.5
160°	537.4	547.6	557.7	564.1	570.5	575.1	576.1	576.1
162.5°	529.3	538.0	546.6	551.6	558.0	561.2	562.1	561.3
165°	517.2	523.6	530.0	533.8	537.4	541.1	541.1	540.2
167.5°	505.6	510.6	515.0	518.3	519.9	522.0	521.8	520.7
170°	499.7	502.5	506.1	507.9	508.9	511.7	510.7	508.9
172.5°	493.1	495.1	498.0	499.2	500.1	501.4	500.4	499.3
175°	485.9	486.8	487.7	488.6	488.6	489.6	488.6	486.8
177.5°	480.8	480.8	481.5	481.5	481.5	481.5	480.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)