

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331642-927

Luminaire Tested: **SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331642-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4231.4 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17				
2	83	76	70	66	73	67	63	59	51	48	45	36	34	33	22	21	20	14				
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	18	12				
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	16	15	11				
5	64	53	45	39	56	47	40	36	36	31	28	26	23	21	16	15	13	9				
6	58	47	40	34	51	42	36	31	32	28	24	23	20	18	15	13	12	8				
7	54	42	35	30	47	38	31	27	29	25	21	21	18	16	13	12	10	7				
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	11	9	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6				
10	43	32	25	21	38	28	23	19	22	18	15	16	13	11	10	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	0.9
10°-20°	102.2	2.4
20°-30°	143.5	3.4
30°-40°	156.5	3.7
40°-50°	143.9	3.4
50°-60°	113.0	2.7
60°-70°	73.7	1.7
70°-80°	38.0	0.9
80°-90°	12.7	0.3
90°-100°	38.8	0.9
100°-110°	142.4	3.4
110°-120°	380.6	9.0
120°-130°	628.2	14.8
130°-140°	668.1	15.8
140°-150°	620.9	14.7
150°-160°	499.2	11.8
160°-170°	321.7	7.6
170°-180°	110.7	2.6
0°-30°	282.9	6.7
0°-40°	439.4	10.4
0°-60°	696.4	16.5
0°-90°	820.7	19.4
90°-120°	561.7	13.3
90°-150°	2478.9	58.6
90°-180°	3411.0	80.6
0°-180°	4231.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	10	17	21	23	3
95°	55	29	33	37	36	67
105°	256	267	51	60	64	274
115°	484	499	520	148	69	477
125°	685	696	712	717	720	610
135°	847	860	868	876	875	654
145°	983	983	996	1002	998	614
155°	1082	1076	1085	1089	1083	498
165°	1140	1136	1138	1143	1138	322
175°	1166	1161	1162	1167	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.7	4.6	4.4	4.4	4.4	4.8	5.1	5.4	5.7	5.8
90°	0.9	2.9	5.0	7.1	9.1	10.9	12.4	13.9	15.4	16.9	17.7
92.5°	17.0	16.8	16.6	16.5	16.2	16.6	17.3	18.1	18.8	19.6	20.0
95°	54.7	48.6	42.4	36.2	30.0	27.6	28.9	30.3	31.5	32.9	33.7
97.5°	108.6	91.3	73.8	56.4	39.1	31.8	34.9	37.9	41.0	44.0	44.7
100°	149.1	123.4	97.8	72.2	46.5	35.3	38.4	41.7	44.8	48.0	49.5
102.5°	193.5	188.1	182.7	177.2	171.8	155.8	129.2	102.6	76.0	49.4	51.3
105°	256.0	261.7	267.2	272.8	278.5	255.7	204.6	153.5	102.4	51.3	53.4
107.5°	327.3	331.8	336.3	340.8	345.4	317.0	255.7	194.5	133.2	71.9	69.8
110°	373.0	377.0	381.0	384.8	388.8	363.7	309.6	255.6	201.5	147.3	128.7



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	416.2	419.7	423.1	426.6	430.1	425.2	411.8	398.5	385.1	371.7	303.5
115°	484.3	487.4	490.6	493.8	496.9	500.9	505.6	510.2	514.9	519.6	432.9
117.5°	545.0	548.6	552.2	555.7	559.3	562.6	565.9	569.1	572.3	575.5	554.5
120°	589.5	592.3	595.1	597.9	600.7	603.8	607.2	610.5	613.9	617.3	619.5
122.5°	627.2	630.2	633.1	636.1	639.1	642.4	646.0	649.7	653.4	657.0	658.4
125°	684.7	687.1	689.5	692.0	694.3	697.4	700.9	704.5	708.1	711.6	712.9
127.5°	736.7	739.4	742.1	744.8	747.5	750.1	752.8	755.4	758.1	760.8	762.7
130°	769.7	772.7	775.7	778.7	781.6	784.2	786.2	788.3	790.4	792.4	794.5
132.5°	803.4	806.0	808.5	811.0	813.6	815.9	817.9	820.0	822.0	824.1	825.9
135°	847.2	850.2	853.2	856.2	859.1	861.5	863.2	864.8	866.6	868.2	870.1
137.5°	891.4	893.6	895.6	897.8	899.8	901.8	903.8	905.7	907.6	909.5	911.3
140°	920.4	921.9	923.4	925.0	926.5	928.2	930.3	932.3	934.4	936.4	938.1
142.5°	944.7	946.0	947.4	948.7	950.1	952.0	954.3	956.6	959.0	961.4	962.9
145°	982.8	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	997.5
147.5°	1016.0	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9
150°	1037.5	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2
152.5°	1055.7	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0
155°	1082.1	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8
157.5°	1102.9	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8
160°	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1
162.5°	1125.8	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3
165°	1140.3	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0
167.5°	1151.0	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6
170°	1157.1	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0
172.5°	1161.1	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0
175°	1166.3	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5
177.5°	1167.2	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	5.9	6.0	6.2	6.3	6.3	6.4	6.5	6.6
90°	18.7	19.6	20.6	21.2	21.6	22.0	22.3	22.7
92.5°	20.5	21.0	21.5	21.9	22.1	22.3	22.5	22.7
95°	34.7	35.6	36.6	37.0	36.8	36.6	36.4	36.2
97.5°	45.5	46.2	47.0	47.5	47.7	47.9	48.1	48.3
100°	51.0	52.5	54.0	54.9	55.3	55.7	56.1	56.4
102.5°	53.2	55.2	57.1	58.4	58.9	59.4	60.0	60.4
105°	55.5	57.5	59.6	61.0	61.8	62.5	63.2	64.0
107.5°	67.7	65.6	63.5	62.9	63.6	64.3	65.1	65.8
110°	110.0	91.3	72.5	63.5	64.2	65.0	65.8	66.5



TEST NUMBER: P331642-927

CATALOG NUMBER: SA2XXRDIP-C290D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.2	166.9	98.6	64.8	65.4	66.0	66.6	67.2
115°	346.3	259.7	173.0	122.9	109.5	96.0	82.5	69.1
117.5°	533.6	512.6	491.7	459.1	414.8	370.5	326.2	281.9
120°	621.8	624.0	626.3	614.7	589.5	564.2	538.9	513.7
122.5°	659.7	661.1	662.4	660.6	655.8	650.9	645.9	641.0
125°	714.2	715.5	716.8	717.8	718.4	718.9	719.5	720.0
127.5°	764.6	766.5	768.4	769.4	769.5	769.7	769.8	769.8
130°	796.5	798.6	800.7	801.6	801.5	801.2	801.1	800.9
132.5°	827.6	829.4	831.2	831.9	831.7	831.6	831.4	831.2
135°	872.0	873.9	875.7	876.5	876.1	875.7	875.4	875.0
137.5°	913.1	915.0	916.8	917.4	916.8	916.2	915.5	914.9
140°	939.8	941.5	943.2	943.6	942.6	941.7	940.7	939.8
142.5°	964.4	966.0	967.5	967.8	966.9	965.9	965.0	964.1
145°	998.9	1000.1	1001.5	1001.6	1000.8	999.8	998.9	997.9
147.5°	1028.8	1029.8	1030.8	1030.9	1030.1	1029.3	1028.5	1027.7
150°	1047.3	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1064.1	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1086.9	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1106.0	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1117.2	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1127.6	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1151.0	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1156.3	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1160.4	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1164.7	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1165.2	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)