

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331696-930

Luminaire Tested: **SA2XXRDIP-C675D925U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331696-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4909.7 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331696-930  
CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	71	64	58	72	65	59	54	53	49	45	42	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19
6	62	50	43	37	56	46	39	35	38	33	30	31	27	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.1	1.8
10°-20°	236.4	4.8
20°-30°	331.9	6.8
30°-40°	361.9	7.4
40°-50°	332.8	6.8
50°-60°	261.4	5.3
60°-70°	170.4	3.5
70°-80°	87.9	1.8
80°-90°	25.3	0.5
90°-100°	34.3	0.7
100°-110°	125.9	2.6
110°-120°	336.5	6.9
120°-130°	555.4	11.3
130°-140°	590.7	12.0
140°-150°	549.0	11.2
150°-160°	441.4	9.0
160°-170°	284.5	5.8
170°-180°	97.9	2.0
0°-30°	654.4	13.3
0°-40°	1016.3	20.7
0°-60°	1610.5	32.8
0°-90°	1894.1	38.6
90°-120°	496.7	10.1
90°-150°	2191.9	44.6
90°-180°	3016.0	61.4
0°-180°	4909.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	9	15	18	20	4
95°	48	26	29	33	32	59
105°	226	236	45	53	57	242
115°	428	441	459	131	61	421
125°	605	615	629	634	637	540
135°	749	761	768	775	774	578
145°	869	869	881	886	882	543
155°	957	951	959	963	958	441
165°	1008	1004	1006	1011	1006	285
175°	1031	1026	1028	1032	1025	98
180°	1029	1029	1029	1029	1029	



TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.1	8.3	7.5	7.3	7.5	7.7	8.1	8.3	8.3
90°	0.7	2.5	4.4	6.2	8.0	9.6	10.9	12.2	13.5	14.9	15.7
92.5°	15.0	14.8	14.7	14.5	14.3	14.6	15.3	16.0	16.6	17.3	17.7
95°	48.4	43.0	37.5	32.0	26.6	24.4	25.6	26.7	27.9	29.0	29.8
97.5°	96.0	80.6	65.3	49.9	34.5	28.1	30.8	33.5	36.2	38.9	39.5
100°	131.8	109.1	86.4	63.8	41.1	31.2	34.0	36.9	39.6	42.5	43.8
102.5°	171.1	166.3	161.5	156.7	151.9	137.8	114.2	90.7	67.2	43.6	45.3
105°	226.3	231.3	236.3	241.2	246.2	226.1	180.9	135.7	90.6	45.4	47.2
107.5°	289.3	293.3	297.3	301.3	305.4	280.3	226.1	171.9	117.7	63.6	61.7
110°	329.9	333.4	336.8	340.3	343.7	321.6	273.8	225.9	178.1	130.3	113.7



TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	371.0	374.1	377.2	380.3	375.9	364.1	352.3	340.5	328.6	268.3
115°	428.1	431.0	433.7	436.6	439.4	442.9	447.0	451.2	455.3	459.4	382.8
117.5°	481.9	485.0	488.2	491.4	494.5	497.5	500.3	503.2	506.1	508.8	490.3
120°	521.2	523.7	526.2	528.6	531.2	533.9	536.9	539.8	542.8	545.8	547.8
122.5°	554.6	557.2	559.8	562.4	565.0	567.9	571.2	574.5	577.7	581.0	582.1
125°	605.4	607.5	609.7	611.8	614.0	616.6	619.8	622.9	626.1	629.2	630.4
127.5°	651.3	653.8	656.2	658.5	660.9	663.2	665.6	668.0	670.3	672.7	674.3
130°	680.6	683.2	685.8	688.5	691.1	693.4	695.2	697.0	698.9	700.7	702.5
132.5°	710.4	712.6	714.9	717.1	719.3	721.4	723.3	725.0	726.8	728.6	730.3
135°	749.1	751.7	754.4	757.0	759.7	761.7	763.2	764.8	766.2	767.7	769.3
137.5°	788.2	790.1	792.0	793.8	795.7	797.4	799.1	800.8	802.5	804.2	805.8
140°	813.8	815.2	816.5	817.8	819.1	820.8	822.6	824.3	826.2	828.0	829.5
142.5°	835.3	836.5	837.7	838.9	840.1	841.7	843.8	845.9	848.0	850.0	851.4
145°	868.9	868.8	868.6	868.5	868.3	869.6	872.5	875.2	878.1	880.8	882.0
147.5°	898.3	897.6	897.1	896.4	895.8	896.8	899.6	902.5	905.2	908.0	908.8
150°	917.4	916.2	915.0	913.9	912.7	913.5	916.2	918.8	921.5	924.1	925.0
152.5°	933.4	932.1	930.8	929.6	928.3	928.9	931.4	933.9	936.5	939.0	940.0
155°	956.8	955.4	953.8	952.4	950.9	951.1	953.1	955.1	957.1	959.0	960.0
157.5°	975.1	973.9	972.7	971.3	970.1	970.2	971.6	973.0	974.4	975.8	976.9
160°	985.9	984.9	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9	986.8
162.5°	995.4	994.4	993.4	992.4	991.4	991.3	992.2	993.0	993.9	994.8	995.9
165°	1008.2	1007.2	1006.2	1005.2	1004.2	1004.0	1004.4	1004.9	1005.5	1006.0	1007.1
167.5°	1017.7	1016.8	1015.8	1014.7	1013.7	1013.5	1014.0	1014.4	1014.9	1015.4	1016.5
170°	1023.1	1022.1	1021.1	1020.1	1019.1	1018.8	1019.1	1019.5	1019.8	1020.1	1021.2
172.5°	1026.6	1025.6	1024.7	1023.7	1022.7	1022.4	1022.7	1023.0	1023.4	1023.7	1024.8
175°	1031.3	1030.1	1029.0	1027.8	1026.6	1026.2	1026.5	1026.9	1027.2	1027.5	1028.7
177.5°	1032.0	1031.1	1030.2	1029.2	1028.3	1027.9	1028.1	1028.2	1028.3	1028.4	1029.4
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	8.3	8.4	8.4	8.4	8.5	8.6	8.6	8.6
90°	16.6	17.4	18.2	18.8	19.1	19.4	19.8	20.1
92.5°	18.1	18.6	19.0	19.3	19.5	19.7	19.9	20.1
95°	30.7	31.6	32.4	32.7	32.5	32.4	32.2	32.0
97.5°	40.2	40.8	41.5	41.9	42.2	42.3	42.6	42.7
100°	45.1	46.4	47.8	48.6	48.9	49.2	49.6	49.9
102.5°	47.0	48.8	50.5	51.6	52.1	52.5	53.0	53.5
105°	49.1	50.9	52.7	54.0	54.6	55.3	55.9	56.6
107.5°	59.8	58.0	56.2	55.6	56.3	56.9	57.6	58.2
110°	97.2	80.6	64.1	56.2	56.8	57.5	58.1	58.9





TEST NUMBER: P331696-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	208.0	147.6	87.2	57.3	57.8	58.4	58.9	59.4
115°	306.2	229.6	153.0	108.7	96.8	84.9	73.0	61.1
117.5°	471.8	453.3	434.7	405.9	366.7	327.6	288.5	249.3
120°	549.8	551.8	553.8	543.6	521.2	498.9	476.5	454.2
122.5°	583.3	584.5	585.7	584.2	579.8	575.4	571.1	566.8
125°	631.5	632.7	633.8	634.6	635.1	635.6	636.2	636.7
127.5°	676.0	677.8	679.5	680.3	680.4	680.5	680.6	680.7
130°	704.3	706.1	707.9	708.8	708.7	708.4	708.3	708.1
132.5°	731.8	733.4	734.9	735.6	735.4	735.2	735.1	734.9
135°	771.0	772.7	774.3	774.9	774.6	774.3	774.0	773.6
137.5°	807.4	809.0	810.7	811.2	810.7	810.1	809.5	808.9
140°	831.0	832.5	834.0	834.3	833.5	832.7	831.8	831.0
142.5°	852.7	854.1	855.5	855.7	854.9	854.1	853.3	852.4
145°	883.2	884.4	885.5	885.7	884.8	884.0	883.2	882.4
147.5°	909.7	910.5	911.4	911.5	910.8	910.1	909.4	908.7
150°	926.0	927.1	928.1	928.1	927.3	926.4	925.6	924.8
152.5°	940.9	941.9	942.9	942.9	941.8	940.7	939.6	938.5
155°	961.1	962.1	963.0	962.9	961.6	960.2	958.9	957.6
157.5°	978.0	979.1	980.2	980.2	978.8	977.5	976.2	975.0
160°	987.8	988.9	989.9	989.8	988.6	987.4	986.3	985.1
162.5°	997.0	998.2	999.3	999.1	997.8	996.3	994.9	993.4
165°	1008.3	1009.4	1010.6	1010.6	1009.4	1008.3	1007.1	1006.0
167.5°	1017.7	1018.8	1020.0	1019.8	1018.3	1016.8	1015.4	1013.8
170°	1022.5	1023.6	1024.7	1024.6	1023.1	1021.6	1020.1	1018.6
172.5°	1026.0	1027.2	1028.3	1028.2	1026.6	1025.2	1023.7	1022.2
175°	1029.9	1031.0	1032.2	1031.9	1030.3	1028.7	1027.0	1025.3
177.5°	1030.3	1031.3	1032.2	1032.0	1030.9	1029.6	1028.4	1027.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1

(END OF REPORT)