

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331690-935

Luminaire Tested: **SA2XXRDIP-C675D725U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331690-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4494.1 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44				38	
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38				33	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28				25	
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25				22	
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22				19	
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18				16	
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.0
10°-20°	249.6	5.6
20°-30°	350.5	7.8
30°-40°	382.2	8.5
40°-50°	351.5	7.8
50°-60°	276.0	6.1
60°-70°	180.0	4.0
70°-80°	92.8	2.1
80°-90°	26.2	0.6
90°-100°	28.4	0.6
100°-110°	104.1	2.3
110°-120°	278.3	6.2
120°-130°	459.4	10.2
130°-140°	488.6	10.9
140°-150°	454.1	10.1
150°-160°	365.1	8.1
160°-170°	235.3	5.2
170°-180°	81.0	1.8
0°-30°	691.1	15.4
0°-40°	1073.3	23.9
0°-60°	1700.8	37.8
0°-90°	1999.7	44.5
90°-120°	410.8	9.1
90°-150°	1813.0	40.3
90°-180°	2494.0	55.5
0°-180°	4494.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	1	7	12	15	17	3
95°	40	21	24	27	26	49
105°	187	195	38	44	47	200
115°	354	365	380	108	50	349
125°	501	509	520	525	527	446
135°	620	629	635	641	640	478
145°	719	719	729	732	730	449
155°	791	787	793	796	792	365
165°	834	830	832	836	832	236
175°	853	849	850	854	848	81
180°	851	851	851	851	851	



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.4	10.4	9.5	8.5	7.6	7.2	7.4	7.7	7.8	8.1	8.1
90°	0.6	2.2	3.6	5.2	6.6	7.9	9.0	10.2	11.2	12.3	13.0
92.5°	12.4	12.3	12.1	12.1	11.9	12.1	12.7	13.2	13.8	14.3	14.6
95°	40.0	35.6	31.0	26.5	22.0	20.1	21.2	22.1	23.1	24.0	24.7
97.5°	79.5	66.7	54.0	41.2	28.5	23.2	25.5	27.7	30.0	32.1	32.7
100°	109.0	90.2	71.5	52.8	34.0	25.8	28.2	30.5	32.8	35.1	36.2
102.5°	141.5	137.6	133.6	129.7	125.6	113.9	94.5	75.0	55.5	36.1	37.5
105°	187.3	191.3	195.4	199.6	203.6	187.0	149.6	112.3	74.9	37.5	39.1
107.5°	239.4	242.6	246.0	249.3	252.6	231.9	187.0	142.2	97.4	52.6	51.1
110°	272.9	275.7	278.6	281.5	284.3	266.0	226.4	186.9	147.3	107.8	94.1



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.4	306.9	309.4	312.0	314.5	310.9	301.2	291.4	281.6	271.8	222.0
115°	354.1	356.5	358.8	361.1	363.4	366.4	369.7	373.2	376.6	380.0	316.7
117.5°	398.6	401.2	403.8	406.4	409.0	411.5	413.9	416.2	418.5	420.9	405.6
120°	431.1	433.2	435.2	437.3	439.4	441.6	444.1	446.5	449.0	451.4	453.1
122.5°	458.7	460.9	463.0	465.2	467.4	469.8	472.5	475.2	477.9	480.5	481.5
125°	500.8	502.5	504.3	506.1	507.8	510.1	512.6	515.2	517.8	520.5	521.4
127.5°	538.8	540.8	542.8	544.7	546.6	548.6	550.6	552.5	554.5	556.4	557.8
130°	562.9	565.2	567.3	569.5	571.7	573.5	575.1	576.5	578.1	579.5	581.1
132.5°	587.5	589.4	591.3	593.1	595.0	596.7	598.2	599.7	601.2	602.7	604.0
135°	619.6	621.8	624.0	626.2	628.4	630.1	631.3	632.5	633.8	635.0	636.4
137.5°	652.0	653.5	655.0	656.6	658.1	659.6	661.0	662.4	663.7	665.2	666.5
140°	673.2	674.2	675.4	676.5	677.5	678.9	680.4	681.9	683.4	684.9	686.1
142.5°	691.0	691.9	692.9	693.9	694.8	696.2	697.9	699.6	701.4	703.1	704.2
145°	718.8	718.6	718.5	718.3	718.2	719.3	721.6	723.9	726.3	728.6	729.6
147.5°	743.0	742.5	742.0	741.5	741.0	741.8	744.2	746.4	748.7	751.1	751.7
150°	758.8	757.9	756.9	756.0	754.9	755.6	757.8	759.9	762.2	764.3	765.2
152.5°	772.1	771.0	770.0	768.9	767.8	768.4	770.4	772.5	774.6	776.6	777.5
155°	791.4	790.2	788.9	787.7	786.5	786.7	788.3	790.0	791.6	793.2	794.1
157.5°	806.6	805.6	804.5	803.5	802.5	802.5	803.7	804.8	805.9	807.1	808.0
160°	815.5	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	816.3
162.5°	823.4	822.5	821.7	820.9	820.0	820.0	820.7	821.4	822.2	822.9	823.8
165°	834.0	833.1	832.3	831.5	830.6	830.4	830.9	831.3	831.6	832.1	833.0
167.5°	841.8	841.0	840.2	839.4	838.5	838.3	838.7	839.0	839.5	839.8	840.8
170°	846.3	845.4	844.6	843.8	843.0	842.7	843.0	843.3	843.5	843.8	844.7
172.5°	849.2	848.3	847.6	846.7	845.9	845.7	845.9	846.2	846.4	846.7	847.7
175°	853.0	852.0	851.1	850.2	849.2	848.9	849.1	849.4	849.6	850.0	850.9
177.5°	853.7	852.9	852.1	851.4	850.6	850.2	850.3	850.5	850.6	850.7	851.4
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	8.0	8.0	8.0	8.0	8.1	8.2	8.2	8.3
90°	13.7	14.4	15.1	15.5	15.8	16.1	16.4	16.6
92.5°	15.0	15.3	15.7	16.0	16.1	16.3	16.4	16.6
95°	25.4	26.1	26.8	27.0	26.9	26.8	26.6	26.5
97.5°	33.2	33.8	34.4	34.7	34.9	35.0	35.2	35.4
100°	37.3	38.4	39.5	40.2	40.5	40.7	41.0	41.2
102.5°	38.9	40.4	41.8	42.7	43.0	43.5	43.8	44.3
105°	40.6	42.1	43.6	44.6	45.2	45.7	46.2	46.8
107.5°	49.5	48.0	46.5	46.0	46.5	47.1	47.6	48.1
110°	80.4	66.7	53.0	46.5	47.0	47.5	48.1	48.6



TEST NUMBER: P331690-935

CATALOG NUMBER: SA2XXRDIP-C675D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.0	122.1	72.2	47.4	47.9	48.3	48.7	49.2
115°	253.3	189.9	126.6	89.9	80.1	70.2	60.4	50.5
117.5°	390.3	374.9	359.6	335.7	303.3	271.0	238.6	206.2
120°	454.8	456.4	458.1	449.6	431.1	412.7	394.2	375.7
122.5°	482.5	483.5	484.5	483.2	479.6	476.0	472.4	468.8
125°	522.4	523.3	524.3	525.0	525.4	525.8	526.2	526.6
127.5°	559.2	560.6	562.0	562.7	562.8	562.9	563.0	563.1
130°	582.6	584.1	585.6	586.3	586.2	586.0	585.8	585.7
132.5°	605.3	606.6	607.9	608.5	608.3	608.2	608.0	607.9
135°	637.7	639.1	640.5	641.0	640.8	640.5	640.2	639.9
137.5°	667.9	669.2	670.5	671.0	670.5	670.0	669.6	669.1
140°	687.3	688.5	689.8	690.1	689.4	688.7	688.0	687.3
142.5°	705.3	706.5	707.6	707.8	707.1	706.5	705.8	705.1
145°	730.6	731.5	732.5	732.5	731.9	731.2	730.6	729.9
147.5°	752.4	753.2	753.9	754.0	753.4	752.8	752.3	751.7
150°	765.9	766.8	767.6	767.7	767.0	766.3	765.6	764.9
152.5°	778.3	779.1	780.0	779.9	779.0	778.1	777.2	776.3
155°	795.0	795.7	796.6	796.4	795.3	794.3	793.2	792.0
157.5°	808.9	809.9	810.8	810.7	809.7	808.6	807.5	806.5
160°	817.1	817.9	818.7	818.6	817.7	816.7	815.8	814.9
162.5°	824.7	825.6	826.6	826.5	825.3	824.1	822.9	821.7
165°	834.0	835.0	835.9	835.9	835.0	834.0	833.0	832.1
167.5°	841.8	842.7	843.7	843.5	842.3	841.1	839.8	838.6
170°	845.7	846.6	847.7	847.5	846.3	845.0	843.8	842.6
172.5°	848.7	849.6	850.6	850.4	849.2	848.0	846.7	845.5
175°	851.9	852.8	853.8	853.6	852.2	850.8	849.5	848.1
177.5°	852.2	853.0	853.8	853.7	852.6	851.7	850.7	849.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2

(END OF REPORT)