

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333012-830

Luminaire Tested: **SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333012-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9075.0 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	43	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.0
10°-20°	514.9	5.7
20°-30°	743.5	8.2
30°-40°	842.8	9.3
40°-50°	813.8	9.0
50°-60°	676.7	7.5
60°-70°	467.3	5.1
70°-80°	236.9	2.6
80°-90°	65.0	0.7
90°-100°	50.1	0.6
100°-110°	319.3	3.5
110°-120°	610.8	6.7
120°-130°	775.4	8.5
130°-140°	829.7	9.1
140°-150°	775.8	8.5
150°-160°	625.7	6.9
160°-170°	403.5	4.4
170°-180°	139.1	1.5
0°-30°	1443.1	15.9
0°-40°	2285.8	25.2
0°-60°	3776.4	41.6
0°-90°	4545.6	50.1
90°-120°	980.2	10.8
90°-150°	3361.2	37.0
90°-180°	4529.0	49.9
0°-180°	9075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	3	15	24	30	33	7
95°	60	25	24	30	32	77
105°	330	336	342	349	312	345
115°	616	619	618	620	620	605
125°	865	869	867	871	872	772
135°	1073	1072	1077	1079	1081	827
145°	1238	1241	1241	1242	1244	773
155°	1357	1358	1355	1359	1356	625
165°	1431	1426	1426	1434	1425	404
175°	1464	1458	1459	1467	1456	139
180°	1464	1464	1464	1464	1464	



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.4	26.8	25.2	23.6	22.0	21.2	21.3	21.4	21.6	21.7	21.7
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	13.8	13.9	14.1	14.2	14.4	15.5	17.3	19.3	21.3	23.2	24.7
95°	60.2	51.9	43.6	35.4	27.1	23.1	23.4	23.6	23.8	24.1	25.5
97.5°	127.9	133.1	138.3	143.4	148.5	137.5	110.4	83.2	56.1	28.9	29.0
100°	179.6	184.0	188.4	192.7	197.2	182.6	148.9	115.4	81.8	48.2	44.0
102.5°	237.4	240.6	243.8	247.0	250.2	249.7	245.3	240.9	236.6	232.1	187.6
105°	329.6	331.1	332.5	334.0	335.5	336.9	338.1	339.2	340.4	341.7	343.9
107.5°	415.3	416.0	416.8	417.5	418.2	419.4	421.0	422.7	424.3	426.0	427.1
110°	473.2	473.8	474.6	475.3	476.1	477.1	478.6	480.0	481.5	483.0	483.4



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	530.6	531.8	533.1	534.4	535.5	536.1	536.8	537.5	538.2	538.1
115°	615.5	616.2	617.0	617.6	618.4	618.7	618.4	618.2	617.9	617.6	618.2
117.5°	693.2	694.2	695.2	696.2	697.1	697.9	698.4	699.0	699.6	700.0	699.9
120°	745.8	746.8	747.8	748.8	749.7	750.1	749.9	749.6	749.3	749.1	749.6
122.5°	794.8	795.5	796.1	796.6	797.2	797.7	798.1	798.3	798.7	799.1	799.4
125°	865.2	866.2	867.1	868.1	869.1	869.3	868.8	868.4	867.9	867.4	868.1
127.5°	931.8	932.0	932.3	932.6	932.7	933.4	934.5	935.7	936.8	937.9	937.7
130°	974.7	975.0	975.2	975.4	975.7	976.2	976.9	977.6	978.4	979.1	979.3
132.5°	1014.2	1014.6	1015.0	1015.5	1015.9	1016.6	1017.5	1018.4	1019.4	1020.3	1020.5
135°	1073.3	1073.1	1072.8	1072.5	1072.3	1072.7	1073.7	1074.6	1075.6	1076.6	1077.0
137.5°	1125.7	1125.8	1125.9	1126.0	1126.1	1126.6	1127.7	1128.8	1129.8	1130.9	1131.4
140°	1159.8	1160.3	1160.7	1161.3	1161.8	1162.2	1162.7	1163.2	1163.7	1164.2	1164.9
142.5°	1190.4	1191.4	1192.2	1193.1	1194.0	1194.6	1194.9	1195.1	1195.4	1195.7	1196.3
145°	1237.6	1238.3	1239.1	1239.7	1240.5	1240.9	1240.9	1240.9	1240.9	1240.9	1241.1
147.5°	1275.0	1276.4	1277.7	1279.1	1280.4	1281.0	1280.8	1280.5	1280.3	1280.1	1280.3
150°	1302.2	1303.2	1304.1	1305.1	1306.1	1306.5	1306.2	1306.0	1305.7	1305.4	1305.4
152.5°	1324.9	1325.8	1326.5	1327.3	1328.0	1328.2	1327.9	1327.4	1326.9	1326.5	1326.9
155°	1357.0	1357.2	1357.4	1357.6	1357.9	1357.6	1357.0	1356.2	1355.5	1354.7	1355.8
157.5°	1383.8	1383.7	1383.6	1383.5	1383.3	1382.8	1382.0	1381.2	1380.4	1379.5	1380.7
160°	1399.7	1398.9	1398.2	1397.5	1396.8	1396.3	1396.0	1395.7	1395.5	1395.2	1396.8
162.5°	1413.6	1412.8	1411.8	1410.9	1409.9	1409.4	1409.1	1408.9	1408.6	1408.4	1409.9
165°	1431.4	1430.2	1429.0	1427.8	1426.5	1426.0	1426.0	1426.0	1426.0	1426.0	1427.9
167.5°	1445.4	1444.2	1442.9	1441.6	1440.4	1439.6	1439.5	1439.4	1439.3	1439.1	1441.2
170°	1453.3	1451.9	1450.4	1449.0	1447.5	1446.9	1447.1	1447.4	1447.6	1447.8	1449.8
172.5°	1458.6	1457.1	1455.7	1454.2	1452.7	1452.1	1452.4	1452.6	1452.8	1453.1	1455.0
175°	1464.2	1462.8	1461.3	1459.9	1458.4	1457.8	1458.0	1458.3	1458.6	1458.8	1460.9
177.5°	1466.9	1465.6	1464.1	1462.8	1461.4	1460.9	1461.3	1461.7	1462.2	1462.5	1464.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	21.7	21.8	21.8	22.0	22.3	22.7	23.1	23.5
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	26.1	27.6	29.0	29.9	30.0	30.1	30.2	30.3
95°	27.1	28.5	30.0	30.8	31.0	31.3	31.5	31.8
97.5°	29.2	29.3	29.5	29.7	30.0	30.2	30.4	30.6
100°	39.9	35.8	31.7	29.7	30.0	30.2	30.4	30.6
102.5°	142.9	98.3	53.6	31.4	31.4	31.5	31.5	31.6
105°	346.1	348.3	350.4	347.1	338.4	329.6	320.9	312.2
107.5°	428.2	429.2	430.3	431.3	432.3	433.2	434.0	435.0
110°	484.0	484.5	484.9	485.5	486.3	487.0	487.8	488.4



TEST NUMBER: P333012-830

CATALOG NUMBER: SA4XXRDIP-C1195D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	538.0	537.9	537.8	538.2	539.1	540.1	541.0	541.9
115°	618.7	619.2	619.6	619.9	619.9	619.9	619.9	619.9
117.5°	699.8	699.7	699.6	699.6	699.5	699.4	699.3	699.2
120°	750.1	750.5	751.0	751.0	750.5	750.1	749.6	749.1
122.5°	799.7	799.9	800.2	800.1	799.7	799.2	798.6	798.1
125°	868.8	869.6	870.3	870.8	871.0	871.3	871.6	871.8
127.5°	937.6	937.5	937.4	937.2	937.0	936.8	936.6	936.4
130°	979.6	979.9	980.1	980.1	980.1	980.1	980.1	980.1
132.5°	1020.8	1021.1	1021.2	1021.2	1021.1	1020.9	1020.7	1020.5
135°	1077.5	1078.0	1078.6	1079.0	1079.5	1080.0	1080.4	1080.9
137.5°	1132.0	1132.5	1133.0	1133.2	1133.1	1132.9	1132.7	1132.7
140°	1165.6	1166.4	1167.2	1167.6	1167.8	1168.1	1168.3	1168.6
142.5°	1196.8	1197.3	1197.9	1198.2	1198.3	1198.3	1198.3	1198.3
145°	1241.3	1241.6	1241.8	1242.2	1242.6	1243.1	1243.7	1244.2
147.5°	1280.4	1280.6	1280.8	1281.0	1281.3	1281.6	1281.8	1282.0
150°	1305.4	1305.4	1305.4	1305.6	1305.8	1306.1	1306.4	1306.6
152.5°	1327.3	1327.7	1328.0	1328.1	1328.0	1327.9	1327.8	1327.6
155°	1356.7	1357.6	1358.7	1358.8	1358.0	1357.3	1356.6	1355.8
157.5°	1382.1	1383.3	1384.6	1384.6	1383.3	1382.1	1380.7	1379.5
160°	1398.2	1399.7	1401.1	1401.1	1399.7	1398.2	1396.8	1395.2
162.5°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.9	1409.2	1407.5
165°	1429.8	1431.8	1433.7	1433.6	1431.4	1429.2	1427.0	1424.8
167.5°	1443.4	1445.5	1447.7	1447.5	1445.1	1442.7	1440.2	1437.8
170°	1451.7	1453.7	1455.7	1455.4	1452.9	1450.5	1448.1	1445.7
172.5°	1457.0	1459.0	1460.8	1460.6	1457.9	1455.3	1452.6	1450.0
175°	1463.2	1465.4	1467.5	1467.2	1464.2	1461.3	1458.4	1455.5
177.5°	1465.7	1467.2	1468.8	1468.4	1466.0	1463.7	1461.3	1459.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2

(END OF REPORT)