

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001170

Luminaire Tested: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001170
REPORT IS A COMBINATION OF REPORTS P995786 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5596.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001170

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001170

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	47	40	37	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	15
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3879 cd/sqm

TEST NUMBER: P1001170

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.4	2.7
20°-30°	222.8	4.0
30°-40°	258.9	4.6
40°-50°	258.9	4.6
50°-60°	226.5	4.0
60°-70°	168.1	3.0
70°-80°	95.4	1.7
80°-90°	30.5	0.5
90°-100°	97.0	1.7
100°-110°	290.6	5.2
110°-120°	493.7	8.8
120°-130°	651.1	11.6
130°-140°	731.2	13.1
140°-150°	718.7	12.8
150°-160°	604.5	10.8
160°-170°	402.2	7.2
170°-180°	140.8	2.5
0°-30°	427.8	7.6
0°-40°	686.8	12.3
0°-60°	1172.2	20.9
0°-90°	1466.2	26.2
90°-120°	881.3	15.7
90°-150°	2982.3	53.3
90°-180°	4130.0	73.8
0°-180°	5596.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	4	16	25	32	34	7
95°	69	79	88	91	91	75
105°	268	269	274	277	281	284
115°	502	502	500	498	497	495
125°	731	731	730	728	725	652
135°	943	950	950	947	944	729
145°	1145	1150	1151	1150	1146	717
155°	1312	1312	1311	1316	1311	604
165°	1429	1425	1423	1430	1425	403
175°	1486	1480	1479	1487	1479	141
180°	1488	1488	1488	1488	1488	

TEST NUMBER: P1001170

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	3.5	16.1	25.3	32.2	34.5
92.5°	29.9	44.9	50.7	54.1	55.3
95°	69.1	79.4	87.5	90.9	90.9
97.5°	110.5	119.7	128.9	133.5	133.5
100°	161.2	165.8	176.1	178.4	178.4
102.5°	214.1	215.3	224.5	227.9	229.1
105°	268.2	269.4	274.0	277.4	280.9
107.5°	324.6	325.8	326.9	331.5	330.4
110°	382.2	384.5	383.3	381.0	384.5

TEST NUMBER: P1001170

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.0	442.0	439.7	439.7	439.7
115°	501.9	501.9	499.6	498.4	497.3
117.5°	558.3	558.3	557.2	553.7	550.2
120°	614.7	619.3	615.9	610.1	612.4
122.5°	673.4	674.6	673.4	670.0	664.2
125°	731.0	731.0	729.8	727.5	725.2
127.5°	782.8	786.2	783.9	781.6	780.5
130°	838.0	841.5	841.5	839.2	834.6
132.5°	894.4	896.7	895.6	893.3	892.1
135°	942.8	949.7	949.7	947.4	943.9
137.5°	996.9	1000.3	1002.6	999.2	1000.3
140°	1051.0	1053.3	1053.3	1052.1	1051.0
142.5°	1100.5	1102.8	1101.6	1101.6	1101.6
145°	1145.4	1150.0	1151.1	1150.0	1146.5
147.5°	1191.4	1197.2	1196.0	1194.9	1193.7
150°	1232.9	1237.5	1237.5	1237.5	1236.3
152.5°	1272.0	1274.3	1275.5	1278.9	1275.5
155°	1312.3	1312.3	1311.1	1315.7	1311.1
157.5°	1346.8	1344.5	1344.5	1348.0	1344.5
160°	1376.8	1375.6	1374.5	1377.9	1372.2
162.5°	1404.4	1400.9	1399.8	1406.7	1400.9
165°	1428.6	1425.1	1422.8	1429.7	1425.1
167.5°	1448.1	1443.5	1443.5	1450.4	1443.5
170°	1464.2	1458.5	1459.6	1466.5	1458.5
172.5°	1475.8	1471.2	1471.2	1479.2	1471.2
175°	1486.1	1480.4	1479.2	1487.3	1479.2
177.5°	1490.7	1485.0	1485.0	1493.0	1483.8
180°	1488.4	1488.4	1488.4	1488.4	1488.4

(END OF REPORT)