

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001200

Luminaire Tested: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001200
REPORT IS A COMBINATION OF REPORTS P995816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5596.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001200

CATALOG NUMBER: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001200

CATALOG NUMBER: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	42	41	40	27	26	26
2	83	76	70	64	73	67	62	58	51	48	45	37	35	33	24	22	21
3	75	66	59	53	67	59	53	48	45	41	38	32	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	18	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	22	20	16	15	13
6	58	46	38	33	51	41	34	30	32	27	23	23	20	17	15	13	11
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	13	12	10
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	30	24	20	24	19	16	17	14	12	11	9	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3370	3370	3370
5°	3379	3282	3288
10°	3358	3218	3209
15°	3326	3145	3119
20°	3279	3066	3031
25°	3227	2980	2937
30°	3170	2894	2841
35°	3106	2806	2755
40°	3054	2721	2667
45°	2978	2643	2589
50°	2913	2552	2506
55°	2846	2466	2411
60°	2742	2358	2321
65°	2628	2242	2214
70°	2488	2110	2089
75°	2294	1962	1971
80°	2073	1811	1847
85°	1783	1660	1746

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3555 cd/sqm

TEST NUMBER: P1001200

CATALOG NUMBER: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	0.7
10°-20°	112.2	2.0
20°-30°	169.6	3.0
30°-40°	205.2	3.7
40°-50°	217.0	3.9
50°-60°	204.2	3.6
60°-70°	169.4	3.0
70°-80°	118.9	2.1
80°-90°	70.3	1.3
90°-100°	138.2	2.5
100°-110°	324.0	5.8
110°-120°	519.9	9.3
120°-130°	670.7	12.0
130°-140°	745.6	13.3
140°-150°	729.1	13.0
150°-160°	612.4	10.9
160°-170°	407.5	7.3
170°-180°	142.7	2.5
0°-30°	321.0	5.7
0°-40°	526.2	9.4
0°-60°	947.4	16.9
0°-90°	1306.0	23.3
90°-120°	982.1	17.5
90°-150°	3127.5	55.9
90°-180°	4290.0	76.7
0°-180°	5596.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	413	413	413	413	413	
5°	414	412	409	413	412	39
15°	397	397	396	400	399	112
25°	363	366	367	372	372	167
35°	318	323	328	334	336	199
45°	265	274	282	290	292	205
55°	207	217	231	240	243	185
65°	144	158	174	186	189	142
75°	80	97	116	129	133	85
85°	24	44	65	79	83	26
90°	11	42	72	92	98	10
95°	76	102	129	145	149	81
105°	276	286	308	323	330	293
115°	511	515	528	537	539	504
125°	742	742	752	759	759	662
135°	956	963	966	971	971	740
145°	1161	1165	1166	1168	1166	727
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1001200

CATALOG NUMBER: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.3	413.3	413.3	413.3	413.3
2.5°	415.1	413.7	410.0	413.3	412.8
5°	413.7	412.3	409.1	412.8	412.3
7.5°	411.0	410.0	407.3	411.4	411.0
10°	407.3	406.8	404.5	408.6	408.2
12.5°	402.2	402.2	400.8	404.5	404.5
15°	396.6	397.1	395.7	399.8	399.4
17.5°	389.2	390.6	390.1	394.3	393.8
20°	381.3	382.7	383.2	387.8	387.8
22.5°	372.5	374.4	375.3	379.9	380.9
25°	362.8	365.6	367.0	372.1	372.5
27.5°	352.2	356.3	358.2	362.8	363.3
30°	341.5	345.2	348.5	353.6	354.5
32.5°	330.0	334.6	338.3	344.3	345.2
35°	317.5	323.0	327.7	334.1	335.5
37.5°	305.0	311.5	317.0	323.5	324.9
40°	292.9	299.0	305.4	312.4	314.2
42.5°	279.1	286.0	293.9	301.7	303.1
45°	264.7	273.5	282.3	290.2	292.5
47.5°	251.3	260.1	270.3	278.1	280.9
50°	236.5	246.7	256.8	266.1	268.9
52.5°	221.7	231.9	243.9	253.1	255.9
55°	207.3	217.0	230.9	240.2	243.0
57.5°	191.1	203.2	216.6	227.7	230.0
60°	175.4	187.4	202.7	213.3	217.0
62.5°	160.1	173.5	188.8	199.5	203.2
65°	143.5	158.3	174.0	185.6	189.3
67.5°	127.7	143.5	160.1	171.7	175.4
70°	111.5	127.3	144.9	157.3	160.6
72.5°	95.8	112.0	131.0	143.0	146.7
75°	79.6	96.7	116.2	129.1	133.3
77.5°	64.3	82.4	102.7	115.7	120.3
80°	50.4	69.0	89.3	103.2	106.9
82.5°	36.6	56.0	76.4	90.7	94.9
85°	24.5	44.0	64.8	78.7	83.3
87.5°	15.3	34.2	54.6	68.0	72.2
90°	10.9	42.2	71.5	91.9	97.9
92.5°	37.2	68.6	94.3	110.8	115.7
95°	76.0	101.8	128.9	144.9	149.0
97.5°	117.6	140.3	168.5	185.3	189.4
100°	168.4	185.0	213.6	228.5	231.7
102.5°	222.0	233.4	260.3	275.8	280.7
105°	275.9	286.3	308.1	323.1	330.3
107.5°	333.1	342.0	359.4	375.7	377.7
110°	390.9	399.7	414.7	423.0	430.2

TEST NUMBER: P1001200

CATALOG NUMBER: SA4XXDIP-B350D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	451.0	456.6	469.6	479.7	483.4
115°	511.3	515.4	527.9	536.9	539.0
117.5°	568.4	571.2	583.8	590.1	590.3
120°	625.0	631.1	641.0	644.5	650.5
122.5°	684.5	685.7	697.0	702.8	700.2
125°	742.4	741.9	752.4	758.8	759.2
127.5°	794.9	797.9	804.8	810.8	812.9
130°	850.4	853.4	860.8	866.8	864.9
132.5°	907.5	909.4	913.8	919.3	920.9
135°	956.0	963.0	966.3	971.4	970.6
137.5°	1010.8	1013.9	1018.0	1021.5	1025.0
140°	1065.6	1067.6	1068.0	1072.8	1074.0
142.5°	1115.4	1117.7	1116.0	1121.1	1122.9
145°	1160.8	1165.0	1166.2	1167.8	1166.1
147.5°	1207.5	1212.8	1211.7	1211.0	1211.6
150°	1249.5	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)