

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332951-930

Luminaire Tested: **SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332951-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6230.2 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38				
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	53	46	40	44	39	35	36	33	30	29	27	24	21				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17				
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8688	8688	8688	8688
5°	10078	8715	7703	8715
10°	11922	8676	6874	8676
15°	13771	8596	5907	8596
20°	15332	8485	5342	8485
25°	15828	8378	4960	8378
30°	13856	8245	4729	8245
35°	10787	8051	4590	8051
40°	8088	7827	4515	7827
45°	6387	7470	4475	7470
50°	5392	7058	4346	7058
55°	4700	6602	4114	6602
60°	4229	6132	3641	6132
65°	3727	5624	3131	5624
70°	3356	5098	2825	5098
75°	2813	4517	2408	4517
80°	2380	3849	2259	3849
85°	2010	3010	2010	3010



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	1.7
10°-20°	314.5	5.0
20°-30°	492.0	7.9
30°-40°	546.9	8.8
40°-50°	485.2	7.8
50°-60°	378.1	6.1
60°-70°	247.6	4.0
70°-80°	121.7	2.0
80°-90°	32.7	0.5
90°-100°	348.3	5.6
100°-110°	724.9	11.6
110°-120°	649.3	10.4
120°-130°	546.2	8.8
130°-140°	455.4	7.3
140°-150°	347.9	5.6
150°-160°	244.5	3.9
160°-170°	143.8	2.3
170°-180°	46.8	0.8
0°-30°	910.8	14.6
0°-40°	1457.7	23.4
0°-60°	2321.1	37.3
0°-90°	2723.1	43.7
90°-120°	1722.5	27.6
90°-150°	3071.9	49.3
90°-180°	3507.0	56.3
0°-180°	6230.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1076	1076	1076	1076	1076	
5°	1244	1075	950	1075	1244	126
15°	1648	1028	707	1028	1648	469
25°	1777	940	557	940	1777	788
35°	1094	817	466	817	1094	686
45°	559	654	392	654	559	443
55°	334	469	292	469	334	304
65°	195	294	164	294	195	196
75°	90	145	77	145	90	99
85°	22	32	22	32	22	25
90°	20	1	20	1	20	17
95°	231	31	231	31	231	359
105°	1333	111	1333	111	1333	1318
115°	1280	195	1280	195	1280	1271
125°	1021	272	1021	272	1021	928
135°	913	323	913	323	913	705
145°	746	372	746	372	746	473
155°	624	424	624	424	624	291
165°	545	461	545	461	545	156
175°	491	481	491	481	491	48
180°	482	482	482	482	482	



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1135.1	1138.3	1135.1	1134.8	1131.4	1130.3	1128.9	1124.5	1116.1	1111.3	1112.3
5°	1243.6	1254.4	1248.4	1247.5	1238.0	1228.4	1222.3	1208.4	1193.7	1183.7	1175.5
7.5°	1369.0	1375.2	1371.4	1365.3	1349.9	1341.2	1327.1	1308.8	1282.4	1262.2	1243.7
10°	1454.3	1459.5	1457.8	1446.5	1435.3	1412.3	1399.2	1373.7	1340.3	1313.9	1289.2
12.5°	1538.2	1543.9	1528.5	1529.1	1507.7	1489.6	1469.0	1436.8	1398.2	1364.2	1333.2
15°	1647.7	1640.8	1640.8	1632.1	1608.3	1583.1	1561.9	1528.0	1479.4	1438.7	1395.8
17.5°	1733.4	1735.8	1732.3	1711.8	1693.1	1667.0	1628.1	1588.6	1543.5	1488.8	1445.0
20°	1784.7	1784.7	1780.9	1766.9	1742.7	1714.9	1672.8	1629.9	1572.7	1517.6	1468.2
22.5°	1805.6	1806.9	1802.3	1790.9	1769.0	1742.0	1706.2	1662.6	1603.5	1541.6	1480.3
25°	1776.9	1785.2	1786.0	1783.0	1776.5	1760.0	1729.2	1684.6	1631.7	1564.5	1498.5
27.5°	1631.4	1641.8	1650.9	1665.9	1685.9	1696.2	1697.6	1675.0	1628.8	1564.1	1497.8
30°	1486.4	1495.1	1523.2	1560.1	1588.8	1614.8	1637.3	1643.4	1617.4	1559.3	1489.5
32.5°	1325.4	1337.3	1365.5	1405.1	1452.8	1496.8	1547.4	1573.3	1572.6	1537.7	1473.2
35°	1094.5	1103.1	1129.1	1170.8	1228.0	1293.5	1373.7	1436.1	1478.6	1475.5	1436.1
37.5°	882.6	892.4	918.8	953.2	1008.8	1089.8	1167.4	1253.4	1332.0	1376.1	1363.0
40°	767.5	767.9	793.5	829.1	881.1	951.8	1036.3	1131.7	1219.3	1290.9	1304.7
42.5°	676.6	676.7	693.6	731.9	769.4	835.9	916.6	1011.4	1113.9	1196.5	1233.3
45°	559.4	563.3	577.2	600.1	629.6	686.0	750.6	838.6	953.5	1051.5	1112.6
47.5°	473.7	479.4	488.2	507.0	530.4	568.0	621.4	700.5	794.0	901.8	988.8
50°	429.3	430.2	441.4	451.8	472.2	502.1	548.9	614.8	700.7	804.4	901.1
52.5°	391.1	390.9	397.7	410.9	427.5	450.8	488.6	548.6	624.8	717.6	817.4
55°	333.9	336.1	341.3	351.6	364.2	380.7	410.6	455.8	515.6	594.9	685.5
57.5°	290.3	291.5	295.5	299.9	311.5	323.5	345.9	377.2	427.7	492.7	577.2
60°	261.9	262.4	263.7	270.1	279.2	290.5	305.7	332.2	374.6	434.1	500.8
62.5°	234.2	234.9	236.9	241.7	248.7	256.5	272.4	293.7	328.8	379.6	439.8
65°	195.1	195.6	198.6	200.3	205.9	212.9	224.6	238.9	263.2	305.7	351.2
67.5°	163.1	163.1	163.2	165.6	169.4	174.1	181.1	192.5	210.8	236.9	277.0
70°	142.2	142.2	143.1	144.4	146.6	150.4	154.3	163.1	176.5	197.7	228.5
72.5°	122.8	123.1	124.0	124.3	125.4	128.6	131.5	137.1	147.0	163.1	187.9
75°	90.2	91.5	93.7	95.4	97.6	97.1	100.2	103.6	106.6	116.2	130.5
77.5°	67.1	66.4	66.7	68.2	68.4	68.9	71.0	73.7	76.0	80.5	85.6
80°	51.2	51.2	52.5	52.9	52.5	52.9	55.0	56.3	57.2	58.9	63.8
82.5°	38.6	39.4	39.0	39.4	39.6	40.0	41.9	42.2	43.0	43.7	45.7
85°	21.7	22.1	22.6	21.7	21.7	21.7	22.6	23.0	23.9	23.4	24.3
87.5°	11.6	11.3	11.8	11.6	11.7	11.4	11.6	12.1	11.2	11.7	11.3
90°	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0	16.1	17.0	15.2
92.5°	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1	250.3	300.5	263.0
95°	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0	793.9	772.1	582.6
97.5°	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2	997.4	813.3	545.3
100°	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6	1004.2	761.7	494.6
102.5°	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3	947.4	697.2	460.4
105°	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0	844.1	621.5	431.0
107.5°	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8	760.8	579.0	425.7
110°	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7	719.1	564.7	427.3



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9	695.5	557.8	431.8
115°	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0	673.6	554.2	440.5
117.5°	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5	663.7	553.3	449.8
120°	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9	658.4	553.3	456.6
122.5°	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8	652.4	552.5	463.5
125°	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3	642.3	551.4	473.7
127.5°	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3	628.8	549.3	481.8
130°	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2	620.5	548.5	487.9
132.5°	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2	612.9	547.8	493.2
135°	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3	601.6	546.7	501.2
137.5°	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4	591.7	546.4	505.9
140°	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0	586.4	545.7	509.7
142.5°	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4	581.9	545.7	512.7
145°	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5	574.1	543.8	514.5
147.5°	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2	567.1	540.4	515.4
150°	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6	561.8	538.1	515.4
152.5°	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2	555.7	534.3	513.9
155°	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7	546.7	528.6	511.6
157.5°	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2	537.4	522.8	509.2
160°	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9	530.5	518.2	506.9
162.5°	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5	524.5	513.6	504.6
165°	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0	514.5	506.9	500.2
167.5°	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9	505.3	500.0	495.7
170°	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0	499.3	495.5	492.6
172.5°	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9	494.0	490.9	489.6
175°	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8	487.9	486.0	486.0
177.5°	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5	483.7	483.0	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1108.8	1104.0	1101.6	1096.0	1089.4	1085.9	1082.8	1078.3	1072.4	1066.2	1061.6
5°	1165.1	1154.7	1141.7	1126.1	1112.2	1098.8	1087.0	1075.4	1061.9	1048.0	1034.1
7.5°	1222.9	1202.4	1180.3	1154.7	1129.8	1107.2	1086.4	1066.4	1043.8	1023.7	1005.3
10°	1263.1	1235.3	1204.5	1172.1	1139.5	1111.3	1083.6	1058.4	1030.7	1006.0	985.1
12.5°	1295.7	1263.1	1226.0	1185.5	1146.5	1112.4	1080.4	1047.7	1016.1	989.3	961.6
15°	1349.8	1305.1	1255.3	1206.7	1156.0	1109.6	1066.7	1028.5	992.5	954.8	928.4
17.5°	1387.0	1334.0	1273.4	1215.0	1155.1	1100.4	1050.9	1005.4	963.9	925.4	893.9
20°	1409.2	1350.7	1283.4	1217.2	1149.9	1091.4	1038.0	987.7	944.9	903.2	870.7
22.5°	1421.7	1356.9	1283.4	1214.0	1144.4	1081.0	1022.5	970.0	923.3	881.7	845.7
25°	1425.7	1356.3	1281.3	1201.5	1125.2	1058.0	997.3	940.5	888.4	846.9	808.7
27.5°	1420.2	1338.5	1261.6	1179.7	1101.0	1030.1	966.5	906.8	854.7	810.0	770.9
30°	1411.9	1324.2	1241.9	1156.8	1077.1	1009.0	941.8	884.5	830.4	784.0	744.5
32.5°	1393.8	1306.9	1218.2	1131.2	1050.4	980.2	916.5	858.9	805.8	758.3	716.4
35°	1358.0	1270.1	1173.8	1084.4	1005.1	932.2	872.5	816.9	766.2	715.4	671.2
37.5°	1311.0	1221.1	1125.3	1027.4	948.0	879.3	824.3	772.3	722.8	676.5	627.5
40°	1266.6	1184.6	1085.7	988.6	907.1	840.7	790.0	742.7	692.9	646.9	597.9
42.5°	1212.8	1143.0	1043.1	945.6	865.1	801.2	754.0	707.8	662.3	617.8	566.7
45°	1123.1	1070.2	976.5	882.8	801.8	738.4	695.0	654.3	614.4	571.9	523.8
47.5°	1020.2	984.4	903.5	807.6	732.6	675.6	633.7	600.5	566.7	524.2	482.0
50°	948.8	925.8	847.7	760.1	688.6	636.1	593.2	562.0	533.8	493.0	455.3
52.5°	872.5	860.2	794.3	710.5	641.4	590.0	553.3	525.2	496.7	462.8	427.5
55°	756.2	762.7	706.8	634.4	569.3	525.9	492.6	469.1	444.9	416.3	389.0
57.5°	637.4	661.1	623.6	560.0	499.0	459.0	433.9	414.2	393.8	370.1	346.7
60°	566.3	586.2	565.0	509.1	455.8	418.4	395.0	379.8	359.5	337.8	320.0
62.5°	496.9	518.3	505.6	460.5	411.0	378.9	358.2	344.1	329.0	310.1	291.6
65°	409.8	423.6	417.6	386.4	351.2	323.9	304.8	294.4	280.5	266.7	250.2
67.5°	313.8	340.6	337.1	320.5	290.2	268.8	256.3	247.1	234.5	224.2	213.0
70°	258.0	282.7	282.3	268.8	252.3	232.4	223.7	216.0	204.6	194.7	185.6
72.5°	211.2	233.8	237.2	226.9	215.6	200.5	192.2	186.8	175.9	169.0	161.7
75°	147.9	164.4	168.7	168.7	163.5	155.6	148.3	144.8	137.1	130.9	126.6
77.5°	96.9	107.4	114.1	115.7	116.5	113.9	107.8	105.3	99.4	97.2	93.0
80°	68.5	75.4	83.2	85.9	88.1	87.2	84.5	82.8	77.2	75.0	73.3
82.5°	47.4	51.2	57.6	63.3	62.7	65.0	62.7	61.3	57.1	56.3	54.5
85°	24.7	25.1	26.0	29.9	32.1	32.9	33.4	32.5	31.2	31.2	28.2
87.5°	11.0	10.6	10.2	10.2	10.4	11.6	12.0	12.0	11.3	10.8	10.0
90°	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0	2.9	5.7	6.6
92.5°	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8	15.7	24.6	36.2
95°	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2	34.1	43.6	55.9
97.5°	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1	56.1	64.2	75.6
100°	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0	72.0	78.6	90.0
102.5°	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2	88.7	94.6	105.2
105°	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9	113.7	118.5	129.8
107.5°	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0	138.8	143.7	155.7
110°	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4	156.3	161.0	172.4



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1	173.0	178.5	189.1
115°	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2	198.0	204.6	214.1
117.5°	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1	222.8	228.7	239.1
120°	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8	238.7	245.4	255.8
122.5°	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0	253.9	260.6	270.2
125°	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9	275.7	281.4	291.8
127.5°	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5	292.5	299.4	311.3
130°	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4	303.1	310.7	325.0
132.5°	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2	312.3	322.1	335.6
135°	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0	326.9	336.3	352.5
137.5°	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9	340.5	350.9	366.2
140°	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7	349.6	360.0	376.1
142.5°	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3	360.2	369.8	385.2
145°	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3	375.2	384.7	397.9
147.5°	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1	390.1	398.4	412.1
150°	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8	400.7	408.3	419.7
152.5°	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6	409.9	417.4	428.0
155°	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5	424.4	430.1	439.6
157.5°	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9	436.9	442.2	449.6
160°	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2	445.2	449.1	455.7
162.5°	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8	452.1	455.1	461.0
165°	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4	461.4	463.3	468.0
167.5°	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9	469.0	469.9	473.5
170°	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7	472.7	473.7	476.5
172.5°	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4	476.5	476.7	478.8
175°	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3	480.3	480.3	481.3
177.5°	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0	482.2	481.4	482.2
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1056.8	1053.3	1048.8	1043.6	1037.4	1031.8	1029.4	1031.4	1032.5	1029.7	1029.4
5°	1024.6	1013.7	1005.1	992.1	981.7	973.0	966.9	964.3	965.2	958.3	956.5
7.5°	988.5	975.6	961.4	946.0	931.6	918.8	912.2	908.5	901.2	898.0	892.7
10°	965.2	947.9	934.0	915.7	899.3	884.1	876.8	870.7	863.3	859.8	852.5
12.5°	941.3	921.1	905.9	887.0	870.2	851.8	844.8	833.6	822.1	814.7	805.3
15°	907.5	883.3	864.6	842.0	822.1	801.3	782.7	761.8	754.1	737.6	728.1
17.5°	868.0	843.4	820.4	790.1	759.4	733.5	713.6	693.7	681.8	671.2	666.3
20°	842.0	819.5	787.4	752.3	718.0	689.4	673.4	660.4	647.3	640.0	634.8
22.5°	817.4	788.6	751.4	713.5	679.2	656.8	643.2	629.8	619.3	612.3	605.3
25°	776.2	738.4	699.0	655.6	632.2	612.7	597.9	587.1	580.6	571.5	568.0
27.5°	733.8	688.0	644.5	615.4	591.0	573.2	560.3	552.1	543.9	538.1	533.6
30°	701.2	654.8	615.7	588.0	563.3	548.5	538.1	528.6	522.0	517.3	513.8
32.5°	668.9	622.5	589.7	559.9	540.4	525.9	514.9	507.8	502.6	496.5	494.4
35°	622.2	581.1	552.4	525.5	505.6	492.6	483.9	476.5	472.2	470.4	469.1
37.5°	577.4	543.6	512.9	490.8	473.0	462.8	452.6	449.0	446.0	442.9	444.3
40°	548.9	517.3	490.0	466.6	452.2	441.0	434.9	430.6	428.0	428.0	428.0
42.5°	524.3	493.3	466.8	445.7	431.5	421.9	415.2	411.5	410.6	410.3	412.4
45°	486.1	457.5	430.6	413.2	401.0	391.5	387.7	384.6	384.6	386.4	386.8
47.5°	448.2	421.3	399.8	380.3	369.2	363.3	359.9	358.3	358.5	360.3	362.2
50°	424.9	398.5	377.2	359.9	349.5	343.8	340.8	340.0	340.8	340.8	343.8
52.5°	399.6	375.9	355.1	340.5	328.6	323.3	321.7	320.5	321.1	322.5	323.8
55°	362.5	341.3	321.3	307.4	298.7	295.3	291.4	291.8	291.0	291.8	291.8
57.5°	325.3	306.2	287.6	276.6	269.0	264.0	259.8	261.0	259.7	259.5	258.8
60°	301.3	280.5	265.8	255.8	247.1	242.8	238.9	239.8	238.5	237.6	235.9
62.5°	275.3	258.0	243.9	234.3	227.4	222.3	218.4	217.6	214.6	211.6	207.8
65°	237.6	223.3	210.8	201.6	195.1	191.2	188.2	185.6	179.0	172.1	168.7
67.5°	201.0	190.6	178.9	171.2	165.9	160.8	155.0	150.6	144.5	140.6	138.5
70°	177.3	167.4	157.4	150.0	144.4	139.7	133.1	130.1	125.7	124.0	121.8
72.5°	154.8	145.5	136.2	129.6	123.6	119.8	114.7	111.7	109.8	109.1	107.0
75°	120.6	113.2	106.2	100.2	95.4	92.8	90.7	88.5	87.6	83.6	81.5
77.5°	88.0	83.1	78.8	74.4	71.0	69.3	65.1	62.6	61.1	59.4	58.9
80°	68.5	65.1	60.7	58.1	53.3	51.6	49.9	49.4	49.0	48.6	48.1
82.5°	51.5	48.0	43.7	42.2	40.8	39.8	38.7	38.3	37.9	38.2	38.1
85°	26.0	24.3	24.3	23.9	23.4	23.0	22.6	22.6	22.1	22.6	22.1
87.5°	10.2	9.9	11.0	10.3	11.0	11.4	10.8	11.0	11.6	11.1	11.1
90°	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0	18.0	18.9	18.9
92.5°	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1	140.0	111.5	92.5
95°	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0	555.1	428.2	336.3
97.5°	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2	982.6	890.0	791.1
100°	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6	1161.5	1115.1	1045.0
102.5°	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3	1231.2	1244.6	1215.4
105°	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0	1225.0	1318.7	1357.6
107.5°	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8	1127.4	1259.5	1343.9
110°	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7	1051.6	1189.0	1293.1



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9	984.9	1114.7	1218.9
115°	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0	908.6	1019.4	1110.4
117.5°	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5	865.0	952.1	1029.2
120°	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9	846.0	921.8	989.0
122.5°	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8	833.9	902.9	961.8
125°	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3	814.7	880.1	932.2
127.5°	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3	792.2	857.4	906.9
130°	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2	774.0	838.5	888.7
132.5°	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2	753.6	816.4	866.7
135°	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3	722.8	780.6	828.0
137.5°	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4	693.5	742.2	785.0
140°	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0	674.5	717.1	756.9
142.5°	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4	658.6	695.2	729.7
145°	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5	636.7	665.0	691.6
147.5°	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2	617.7	640.4	661.3
150°	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6	606.3	625.3	642.3
152.5°	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2	594.9	612.4	626.4
155°	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7	578.9	593.0	604.5
157.5°	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2	563.0	574.9	584.0
160°	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9	552.3	562.7	570.3
162.5°	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5	542.5	550.7	557.4
165°	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0	527.7	534.3	539.1
167.5°	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9	515.2	520.5	523.3
170°	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0	506.9	510.6	513.5
172.5°	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9	500.0	502.3	504.3
175°	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8	490.7	492.6	492.6
177.5°	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5	485.3	485.3	486.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1027.3	1028.0	1025.6	1024.8	1025.6	1028.0	1027.3	1029.4	1029.7	1032.5	1031.4
5°	953.1	952.2	950.1	950.5	950.1	952.2	953.1	956.5	958.3	965.2	964.3
7.5°	889.6	886.2	887.1	883.7	887.1	886.2	889.6	892.7	898.0	901.2	908.5
10°	850.8	846.0	842.0	838.6	842.0	846.0	850.8	852.5	859.8	863.3	870.7
12.5°	797.7	793.6	788.3	789.4	788.3	793.6	797.7	805.3	814.7	822.1	833.6
15°	722.4	715.9	705.5	706.8	705.5	715.9	722.4	728.1	737.6	754.1	761.8
17.5°	658.7	658.8	654.0	655.1	654.0	658.8	658.7	666.3	671.2	681.8	693.7
20°	625.7	622.6	623.1	621.8	623.1	622.6	625.7	634.8	640.0	647.3	660.4
22.5°	602.8	599.1	596.1	593.4	596.1	599.1	602.8	605.3	612.3	619.3	629.8
25°	564.1	561.5	557.6	556.8	557.6	561.5	564.1	568.0	571.5	580.6	587.1
27.5°	530.1	529.6	528.1	526.0	528.1	529.6	530.1	533.6	538.1	543.9	552.1
30°	510.4	509.5	508.6	507.3	508.6	509.5	510.4	513.8	517.3	522.0	528.6
32.5°	492.7	492.1	491.3	491.4	491.3	492.1	492.7	494.4	496.5	502.6	507.8
35°	467.4	467.0	466.1	465.7	466.1	467.0	467.4	469.1	470.4	472.2	476.5
37.5°	443.8	445.0	444.4	444.3	444.4	445.0	443.8	444.3	442.9	446.0	449.0
40°	427.5	428.0	428.8	428.4	428.8	428.0	427.5	428.0	428.0	428.0	430.6
42.5°	414.0	414.1	415.3	413.8	415.3	414.1	414.0	412.4	410.3	410.6	411.5
45°	389.8	392.4	392.0	392.0	392.0	392.4	389.8	386.8	386.4	384.6	384.6
47.5°	363.4	365.6	366.2	366.2	366.2	365.6	363.4	362.2	360.3	358.5	358.3
50°	346.0	345.1	346.4	346.0	346.4	345.1	346.0	343.8	340.8	340.8	340.0
52.5°	324.9	325.1	325.0	324.5	325.0	325.1	324.9	323.8	322.5	321.1	320.5
55°	292.3	292.7	291.8	292.3	291.8	292.7	292.3	291.8	291.8	291.0	291.8
57.5°	256.9	254.8	255.7	254.6	255.7	254.8	256.9	258.8	259.5	259.7	261.0
60°	231.5	228.0	227.2	225.5	227.2	228.0	231.5	235.9	237.6	238.5	239.8
62.5°	203.1	200.6	197.7	199.1	197.7	200.6	203.1	207.8	211.6	214.6	217.6
65°	165.2	163.5	162.2	163.9	162.2	163.5	165.2	168.7	172.1	179.0	185.6
67.5°	136.7	135.8	135.8	134.9	135.8	135.8	136.7	138.5	140.6	144.5	150.6
70°	121.8	120.6	120.6	119.7	120.6	120.6	121.8	121.8	124.0	125.7	130.1
72.5°	106.6	105.3	105.7	105.1	105.7	105.3	106.6	107.0	109.1	109.8	111.7
75°	78.9	76.7	76.7	77.2	76.7	76.7	78.9	81.5	83.6	87.6	88.5
77.5°	58.9	58.5	59.0	58.3	59.0	58.5	58.9	58.9	59.4	61.1	62.6
80°	48.1	47.7	47.3	48.6	47.3	47.7	48.1	48.1	48.6	49.0	49.4
82.5°	37.3	37.3	37.2	38.9	37.2	37.3	37.3	38.1	38.2	37.9	38.3
85°	22.6	21.7	22.6	21.7	22.6	21.7	22.6	22.1	22.6	22.1	22.6
87.5°	12.0	11.8	11.3	11.6	11.3	11.8	12.0	11.1	11.1	11.6	11.0
90°	19.9	20.9	19.9	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0
92.5°	81.3	76.1	73.0	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1
95°	289.9	260.6	243.4	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0
97.5°	723.0	666.0	637.6	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2
100°	962.5	904.7	876.4	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6
102.5°	1164.9	1123.0	1093.1	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3
105°	1359.5	1351.9	1338.6	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0
107.5°	1390.7	1412.3	1421.8	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8
110°	1360.4	1400.2	1417.3	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1295.3	1343.4	1367.3	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9
115°	1185.2	1242.0	1272.4	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0
117.5°	1093.1	1140.8	1171.5	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5
120°	1043.1	1084.8	1109.4	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9
122.5°	1007.5	1043.1	1063.9	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8
125°	970.1	997.6	1015.6	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3
127.5°	944.9	969.4	984.6	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3
130°	927.5	951.1	966.3	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2
132.5°	904.7	931.5	945.8	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2
135°	865.9	892.4	907.6	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3
137.5°	820.4	846.6	859.1	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4
140°	790.1	811.0	824.2	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0
142.5°	759.0	778.4	790.1	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4
145°	715.3	731.4	740.9	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5
147.5°	678.7	692.5	699.8	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2
150°	657.5	669.8	675.5	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6
152.5°	639.3	649.3	652.7	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2
155°	613.9	621.5	624.4	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7
157.5°	591.2	596.9	598.6	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2
160°	576.0	581.7	582.6	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9
162.5°	561.6	567.3	568.3	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5
165°	542.8	546.7	545.7	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0
167.5°	525.2	527.7	527.5	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9
170°	515.4	516.3	515.4	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0
172.5°	505.5	506.5	505.5	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9
175°	492.6	494.6	492.6	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8
177.5°	485.3	486.0	484.5	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1029.4	1031.8	1037.4	1043.6	1048.8	1053.3	1056.8	1061.6	1066.2	1072.4	1078.3
5°	966.9	973.0	981.7	992.1	1005.1	1013.7	1024.6	1034.1	1048.0	1061.9	1075.4
7.5°	912.2	918.8	931.6	946.0	961.4	975.6	988.5	1005.3	1023.7	1043.8	1066.4
10°	876.8	884.1	899.3	915.7	934.0	947.9	965.2	985.1	1006.0	1030.7	1058.4
12.5°	844.8	851.8	870.2	887.0	905.9	921.1	941.3	961.6	989.3	1016.1	1047.7
15°	782.7	801.3	822.1	842.0	864.6	883.3	907.5	928.4	954.8	992.5	1028.5
17.5°	713.6	733.5	759.4	790.1	820.4	843.4	868.0	893.9	925.4	963.9	1005.4
20°	673.4	689.4	718.0	752.3	787.4	819.5	842.0	870.7	903.2	944.9	987.7
22.5°	643.2	656.8	679.2	713.5	751.4	788.6	817.4	845.7	881.7	923.3	970.0
25°	597.9	612.7	632.2	655.6	699.0	738.4	776.2	808.7	846.9	888.4	940.5
27.5°	560.3	573.2	591.0	615.4	644.5	688.0	733.8	770.9	810.0	854.7	906.8
30°	538.1	548.5	563.3	588.0	615.7	654.8	701.2	744.5	784.0	830.4	884.5
32.5°	514.9	525.9	540.4	559.9	589.7	622.5	668.9	716.4	758.3	805.8	858.9
35°	483.9	492.6	505.6	525.5	552.4	581.1	622.2	671.2	715.4	766.2	816.9
37.5°	452.6	462.8	473.0	490.8	512.9	543.6	577.4	627.5	676.5	722.8	772.3
40°	434.9	441.0	452.2	466.6	490.0	517.3	548.9	597.9	646.9	692.9	742.7
42.5°	415.2	421.9	431.5	445.7	466.8	493.3	524.3	566.7	617.8	662.3	707.8
45°	387.7	391.5	401.0	413.2	430.6	457.5	486.1	523.8	571.9	614.4	654.3
47.5°	359.9	363.3	369.2	380.3	399.8	421.3	448.2	482.0	524.2	566.7	600.5
50°	340.8	343.8	349.5	359.9	377.2	398.5	424.9	455.3	493.0	533.8	562.0
52.5°	321.7	323.3	328.6	340.5	355.1	375.9	399.6	427.5	462.8	496.7	525.2
55°	291.4	295.3	298.7	307.4	321.3	341.3	362.5	389.0	416.3	444.9	469.1
57.5°	259.8	264.0	269.0	276.6	287.6	306.2	325.3	346.7	370.1	393.8	414.2
60°	238.9	242.8	247.1	255.8	265.8	280.5	301.3	320.0	337.8	359.5	379.8
62.5°	218.4	222.3	227.4	234.3	243.9	258.0	275.3	291.6	310.1	329.0	344.1
65°	188.2	191.2	195.1	201.6	210.8	223.3	237.6	250.2	266.7	280.5	294.4
67.5°	155.0	160.8	165.9	171.2	178.9	190.6	201.0	213.0	224.2	234.5	247.1
70°	133.1	139.7	144.4	150.0	157.4	167.4	177.3	185.6	194.7	204.6	216.0
72.5°	114.7	119.8	123.6	129.6	136.2	145.5	154.8	161.7	169.0	175.9	186.8
75°	90.7	92.8	95.4	100.2	106.2	113.2	120.6	126.6	130.9	137.1	144.8
77.5°	65.1	69.3	71.0	74.4	78.8	83.1	88.0	93.0	97.2	99.4	105.3
80°	49.9	51.6	53.3	58.1	60.7	65.1	68.5	73.3	75.0	77.2	82.8
82.5°	38.7	39.8	40.8	42.2	43.7	48.0	51.5	54.5	56.3	57.1	61.3
85°	22.6	23.0	23.4	23.9	24.3	24.3	26.0	28.2	31.2	31.2	32.5
87.5°	10.8	11.4	11.0	10.3	11.0	9.9	10.2	10.0	10.8	11.3	12.0
90°	16.1	17.0	15.2	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0
92.5°	250.3	300.5	263.0	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8
95°	793.9	772.1	582.6	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2
97.5°	997.4	813.3	545.3	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1
100°	1004.2	761.7	494.6	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0
102.5°	947.4	697.2	460.4	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2
105°	844.1	621.5	431.0	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9
107.5°	760.8	579.0	425.7	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0
110°	719.1	564.7	427.3	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	695.5	557.8	431.8	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1
115°	673.6	554.2	440.5	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2
117.5°	663.7	553.3	449.8	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1
120°	658.4	553.3	456.6	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8
122.5°	652.4	552.5	463.5	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0
125°	642.3	551.4	473.7	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9
127.5°	628.8	549.3	481.8	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5
130°	620.5	548.5	487.9	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4
132.5°	612.9	547.8	493.2	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2
135°	601.6	546.7	501.2	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0
137.5°	591.7	546.4	505.9	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9
140°	586.4	545.7	509.7	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7
142.5°	581.9	545.7	512.7	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3
145°	574.1	543.8	514.5	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3
147.5°	567.1	540.4	515.4	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1
150°	561.8	538.1	515.4	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8
152.5°	555.7	534.3	513.9	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6
155°	546.7	528.6	511.6	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5
157.5°	537.4	522.8	509.2	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9
160°	530.5	518.2	506.9	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2
162.5°	524.5	513.6	504.6	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8
165°	514.5	506.9	500.2	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4
167.5°	505.3	500.0	495.7	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9
170°	499.3	495.5	492.6	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7
172.5°	494.0	490.9	489.6	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4
175°	487.9	486.0	486.0	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3
177.5°	483.7	483.0	483.0	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1082.8	1085.9	1089.4	1096.0	1101.6	1104.0	1108.8	1112.3	1111.3	1116.1	1124.5
5°	1087.0	1098.8	1112.2	1126.1	1141.7	1154.7	1165.1	1175.5	1183.7	1193.7	1208.4
7.5°	1086.4	1107.2	1129.8	1154.7	1180.3	1202.4	1222.9	1243.7	1262.2	1282.4	1308.8
10°	1083.6	1111.3	1139.5	1172.1	1204.5	1235.3	1263.1	1289.2	1313.9	1340.3	1373.7
12.5°	1080.4	1112.4	1146.5	1185.5	1226.0	1263.1	1295.7	1333.2	1364.2	1398.2	1436.8
15°	1066.7	1109.6	1156.0	1206.7	1255.3	1305.1	1349.8	1395.8	1438.7	1479.4	1528.0
17.5°	1050.9	1100.4	1155.1	1215.0	1273.4	1334.0	1387.0	1445.0	1488.8	1543.5	1588.6
20°	1038.0	1091.4	1149.9	1217.2	1283.4	1350.7	1409.2	1468.2	1517.6	1572.7	1629.9
22.5°	1022.5	1081.0	1144.4	1214.0	1283.4	1356.9	1421.7	1480.3	1541.6	1603.5	1662.6
25°	997.3	1058.0	1125.2	1201.5	1281.3	1356.3	1425.7	1498.5	1564.5	1631.7	1684.6
27.5°	966.5	1030.1	1101.0	1179.7	1261.6	1338.5	1420.2	1497.8	1564.1	1628.8	1675.0
30°	941.8	1009.0	1077.1	1156.8	1241.9	1324.2	1411.9	1489.5	1559.3	1617.4	1643.4
32.5°	916.5	980.2	1050.4	1131.2	1218.2	1306.9	1393.8	1473.2	1537.7	1572.6	1573.3
35°	872.5	932.2	1005.1	1084.4	1173.8	1270.1	1358.0	1436.1	1475.5	1478.6	1436.1
37.5°	824.3	879.3	948.0	1027.4	1125.3	1221.1	1311.0	1363.0	1376.1	1332.0	1253.4
40°	790.0	840.7	907.1	988.6	1085.7	1184.6	1266.6	1304.7	1290.9	1219.3	1131.7
42.5°	754.0	801.2	865.1	945.6	1043.1	1143.0	1212.8	1233.3	1196.5	1113.9	1011.4
45°	695.0	738.4	801.8	882.8	976.5	1070.2	1123.1	1112.6	1051.5	953.5	838.6
47.5°	633.7	675.6	732.6	807.6	903.5	984.4	1020.2	988.8	901.8	794.0	700.5
50°	593.2	636.1	688.6	760.1	847.7	925.8	948.8	901.1	804.4	700.7	614.8
52.5°	553.3	590.0	641.4	710.5	794.3	860.2	872.5	817.4	717.6	624.8	548.6
55°	492.6	525.9	569.3	634.4	706.8	762.7	756.2	685.5	594.9	515.6	455.8
57.5°	433.9	459.0	499.0	560.0	623.6	661.1	637.4	577.2	492.7	427.7	377.2
60°	395.0	418.4	455.8	509.1	565.0	586.2	566.3	500.8	434.1	374.6	332.2
62.5°	358.2	378.9	411.0	460.5	505.6	518.3	496.9	439.8	379.6	328.8	293.7
65°	304.8	323.9	351.2	386.4	417.6	423.6	409.8	351.2	305.7	263.2	238.9
67.5°	256.3	268.8	290.2	320.5	337.1	340.6	313.8	277.0	236.9	210.8	192.5
70°	223.7	232.4	252.3	268.8	282.3	282.7	258.0	228.5	197.7	176.5	163.1
72.5°	192.2	200.5	215.6	226.9	237.2	233.8	211.2	187.9	163.1	147.0	137.1
75°	148.3	155.6	163.5	168.7	168.7	164.4	147.9	130.5	116.2	106.6	103.6
77.5°	107.8	113.9	116.5	115.7	114.1	107.4	96.9	85.6	80.5	76.0	73.7
80°	84.5	87.2	88.1	85.9	83.2	75.4	68.5	63.8	58.9	57.2	56.3
82.5°	62.7	65.0	62.7	63.3	57.6	51.2	47.4	45.7	43.7	43.0	42.2
85°	33.4	32.9	32.1	29.9	26.0	25.1	24.7	24.3	23.4	23.9	23.0
87.5°	12.0	11.6	10.4	10.2	10.2	10.6	11.0	11.3	11.7	11.2	12.1
90°	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0
92.5°	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1
95°	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0
97.5°	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2
100°	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6
102.5°	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3
105°	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0
107.5°	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8
110°	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9
115°	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0
117.5°	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5
120°	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9
122.5°	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8
125°	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3
127.5°	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3
130°	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2
132.5°	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2
135°	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3
137.5°	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4
140°	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0
142.5°	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4
145°	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5
147.5°	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2
150°	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6
152.5°	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2
155°	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7
157.5°	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2
160°	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9
162.5°	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5
165°	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0
167.5°	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9
170°	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0
172.5°	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9
175°	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8
177.5°	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1128.9	1130.3	1131.4	1134.8	1135.1	1138.3	1135.1
5°	1222.3	1228.4	1238.0	1247.5	1248.4	1254.4	1243.6
7.5°	1327.1	1341.2	1349.9	1365.3	1371.4	1375.2	1369.0
10°	1399.2	1412.3	1435.3	1446.5	1457.8	1459.5	1454.3
12.5°	1469.0	1489.6	1507.7	1529.1	1528.5	1543.9	1538.2
15°	1561.9	1583.1	1608.3	1632.1	1640.8	1640.8	1647.7
17.5°	1628.1	1667.0	1693.1	1711.8	1732.3	1735.8	1733.4
20°	1672.8	1714.9	1742.7	1766.9	1780.9	1784.7	1784.7
22.5°	1706.2	1742.0	1769.0	1790.9	1802.3	1806.9	1805.6
25°	1729.2	1760.0	1776.5	1783.0	1786.0	1785.2	1776.9
27.5°	1697.6	1696.2	1685.9	1665.9	1650.9	1641.8	1631.4
30°	1637.3	1614.8	1588.8	1560.1	1523.2	1495.1	1486.4
32.5°	1547.4	1496.8	1452.8	1405.1	1365.5	1337.3	1325.4
35°	1373.7	1293.5	1228.0	1170.8	1129.1	1103.1	1094.5
37.5°	1167.4	1089.8	1008.8	953.2	918.8	892.4	882.6
40°	1036.3	951.8	881.1	829.1	793.5	767.9	767.5
42.5°	916.6	835.9	769.4	731.9	693.6	676.7	676.6
45°	750.6	686.0	629.6	600.1	577.2	563.3	559.4
47.5°	621.4	568.0	530.4	507.0	488.2	479.4	473.7
50°	548.9	502.1	472.2	451.8	441.4	430.2	429.3
52.5°	488.6	450.8	427.5	410.9	397.7	390.9	391.1
55°	410.6	380.7	364.2	351.6	341.3	336.1	333.9
57.5°	345.9	323.5	311.5	299.9	295.5	291.5	290.3
60°	305.7	290.5	279.2	270.1	263.7	262.4	261.9
62.5°	272.4	256.5	248.7	241.7	236.9	234.9	234.2
65°	224.6	212.9	205.9	200.3	198.6	195.6	195.1
67.5°	181.1	174.1	169.4	165.6	163.2	163.1	163.1
70°	154.3	150.4	146.6	144.4	143.1	142.2	142.2
72.5°	131.5	128.6	125.4	124.3	124.0	123.1	122.8
75°	100.2	97.1	97.6	95.4	93.7	91.5	90.2
77.5°	71.0	68.9	68.4	68.2	66.7	66.4	67.1
80°	55.0	52.9	52.5	52.9	52.5	51.2	51.2
82.5°	41.9	40.0	39.6	39.4	39.0	39.4	38.6
85°	22.6	21.7	21.7	21.7	22.6	22.1	21.7
87.5°	11.6	11.4	11.7	11.6	11.8	11.3	11.6
90°	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P332951-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)