

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001222

Luminaire Tested: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001222
REPORT IS A COMBINATION OF REPORTS P995838 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5569.3 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001222

CATALOG NUMBER: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001222

CATALOG NUMBER: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	67	60	55	68	60	54	50	47	43	40	35	32	30	23	22	20
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15
6	59	47	40	34	52	42	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4509	4509	4509
5°	4512	4379	4384
10°	4474	4257	4227
15°	4409	4112	4050
20°	4327	3956	3867
25°	4235	3791	3671
30°	4124	3612	3454
35°	4009	3430	3245
40°	3889	3233	3023
45°	3763	3036	2815
50°	3623	2844	2585
55°	3472	2621	2356
60°	3317	2376	2118
65°	3139	2124	1849
70°	2936	1819	1563
75°	2631	1466	1251
80°	2242	1061	879
85°	1739	589	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3763 cd/sqm

TEST NUMBER: P1001222

CATALOG NUMBER: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	0.9
10°-20°	146.8	2.6
20°-30°	216.1	3.9
30°-40°	251.2	4.5
40°-50°	251.1	4.5
50°-60°	219.6	3.9
60°-70°	163.1	2.9
70°-80°	92.5	1.7
80°-90°	28.7	0.5
90°-100°	422.2	7.6
100°-110°	858.7	15.4
110°-120°	765.4	13.7
120°-130°	642.9	11.5
130°-140°	536.5	9.6
140°-150°	409.8	7.4
150°-160°	288.0	5.2
160°-170°	169.4	3.0
170°-180°	55.1	1.0
0°-30°	415.0	7.5
0°-40°	666.1	12.0
0°-60°	1136.9	20.4
0°-90°	1421.2	25.5
90°-120°	2046.3	36.7
90°-150°	3635.6	65.3
90°-180°	4148.0	74.5
0°-180°	5569.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	553	553	553	553	553	
5°	552	551	546	551	550	52
15°	526	524	517	520	519	148
25°	476	473	467	467	466	219
35°	410	407	400	397	395	256
45°	334	331	324	319	318	258
55°	253	252	245	240	237	227
65°	171	169	165	160	158	170
75°	91	89	87	85	85	97
85°	24	24	23	23	23	26
90°	1	9	20	22	24	4
95°	37	116	910	451	272	40
105°	131	189	732	1577	1571	139
115°	230	289	653	1255	1509	228
125°	320	381	650	1068	1204	286
135°	381	453	644	948	1076	294
145°	439	502	641	800	879	275
155°	499	539	623	706	736	230
165°	544	561	597	633	642	154
175°	567	568	573	581	578	54
180°	568	568	568	568	568	

TEST NUMBER: P1001222

CATALOG NUMBER: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	552.9	552.9	552.9	552.9	552.9
2.5°	554.6	553.3	548.4	552.9	552.4
5°	552.4	550.6	545.8	550.6	549.8
7.5°	548.4	546.6	541.3	545.3	544.9
10°	542.7	540.9	535.1	538.7	537.8
12.5°	535.1	533.4	527.2	531.1	529.8
15°	525.8	524.1	517.4	520.1	518.7
17.5°	515.2	513.0	506.8	508.6	507.7
20°	503.2	501.0	494.4	495.7	494.8
22.5°	490.4	487.3	480.6	483.3	481.5
25°	476.2	473.1	466.9	467.4	465.6
27.5°	460.3	457.2	451.4	450.5	448.3
30°	444.3	440.8	435.0	433.2	431.0
32.5°	427.5	424.4	418.2	416.0	413.8
35°	409.8	406.7	400.5	397.4	395.1
37.5°	391.2	388.5	381.9	378.8	375.7
40°	373.0	369.5	362.8	358.4	356.2
42.5°	353.5	351.7	344.2	338.9	337.6
45°	334.5	331.4	324.3	319.4	318.1
47.5°	314.5	312.3	305.7	300.3	296.8
50°	294.1	292.4	286.2	280.0	277.3
52.5°	274.2	272.0	265.4	260.0	256.5
55°	252.9	251.6	245.4	240.1	237.4
57.5°	233.0	231.7	225.5	220.2	217.5
60°	212.2	210.0	204.2	200.2	198.0
62.5°	191.8	190.0	183.8	180.3	178.1
65°	171.4	169.2	164.8	160.4	158.1
67.5°	150.6	148.8	144.4	140.0	139.5
70°	131.6	128.5	124.9	121.4	120.1
72.5°	111.2	108.1	105.4	102.8	101.4
75°	91.3	89.0	86.8	85.1	84.6
77.5°	71.8	70.9	68.7	68.2	66.9
80°	54.5	53.2	52.3	51.4	50.9
82.5°	37.7	37.2	37.2	36.8	36.3
85°	23.9	23.9	23.0	23.0	22.6
87.5°	11.5	11.1	10.6	10.6	10.6
90°	1.1	8.9	20.1	22.3	23.5
92.5°	15.6	86.0	437.7	144.6	101.6
95°	36.9	116.2	910.1	450.6	272.5
97.5°	61.4	128.4	973.8	920.2	654.4
100°	84.9	145.2	897.8	1273.0	1024.0
102.5°	107.2	165.2	802.9	1494.2	1345.6
105°	130.7	189.3	732.5	1577.3	1571.2
107.5°	156.3	213.8	686.8	1552.2	1678.4
110°	182.0	238.4	665.5	1462.8	1680.6

TEST NUMBER: P1001222

CATALOG NUMBER: SA4XXDIP-B350D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.6	263.0	655.5	1353.4	1614.7
115°	230.0	288.6	653.3	1255.2	1508.6
117.5°	254.6	312.6	652.1	1178.1	1404.8
120°	279.2	336.2	652.1	1126.2	1319.9
122.5°	301.5	359.0	651.0	1092.1	1252.9
125°	320.5	380.8	649.9	1068.1	1203.8
127.5°	338.4	400.9	647.7	1045.2	1172.5
130°	352.9	420.4	646.6	1017.9	1145.7
132.5°	367.4	437.2	645.4	985.5	1115.6
135°	380.8	453.4	644.3	948.1	1076.5
137.5°	394.2	467.4	644.3	907.9	1030.7
140°	408.7	480.2	643.2	868.8	980.5
142.5°	424.3	491.9	643.2	832.4	926.9
145°	438.9	502.5	641.0	799.6	878.8
147.5°	455.6	512.6	637.6	772.2	834.2
150°	471.2	522.0	634.3	747.0	797.3
152.5°	485.8	531.0	628.7	725.8	763.8
155°	499.2	538.8	623.1	705.7	735.9
157.5°	512.6	546.1	617.5	686.8	710.2
160°	524.8	552.2	610.8	667.8	686.8
162.5°	536.0	557.2	604.1	649.3	664.4
165°	543.8	560.6	597.4	632.6	642.1
167.5°	552.8	563.4	590.7	618.1	624.2
170°	558.3	565.6	584.0	603.6	607.5
172.5°	563.9	567.3	577.3	590.7	590.7
175°	567.3	568.4	572.9	580.7	578.4
177.5°	569.5	568.4	569.5	573.4	569.5
180°	568.4	568.4	568.4	568.4	568.4

(END OF REPORT)