

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001227

Luminaire Tested: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001227
REPORT IS A COMBINATION OF REPORTS P995843 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2656.1 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001227

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001227

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	96	92	87	84	89	84	81	77	71	68	66	58	56	55	47	45	44
2	87	80	73	67	80	73	68	63	61	57	54	51	48	45	41	38	36
3	79	70	62	56	73	64	57	52	54	49	45	44	41	37	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	39	35	32	32	29	26
5	66	54	46	40	61	50	43	37	42	37	32	35	31	27	28	25	22
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	22	20
7	56	44	36	30	52	41	33	28	34	29	24	29	24	21	23	20	17
8	52	40	32	26	48	37	30	25	31	26	22	26	22	19	21	18	15
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	16	14
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3327	3327	3327
5°	3336	3240	3246
10°	3314	3176	3168
15°	3283	3105	3079
20°	3238	3027	2993
25°	3186	2942	2900
30°	3130	2857	2805
35°	3066	2770	2720
40°	3015	2687	2633
45°	2940	2609	2555
50°	2877	2520	2474
55°	2810	2435	2380
60°	2707	2328	2292
65°	2593	2214	2186
70°	2456	2082	2062
75°	2265	1937	1946
80°	2048	1789	1822
85°	1761	1640	1723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2940 cd/sqm

TEST NUMBER: P1001227

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	1.5
10°-20°	110.8	4.2
20°-30°	167.5	6.3
30°-40°	202.6	7.6
40°-50°	214.2	8.1
50°-60°	201.6	7.6
60°-70°	167.3	6.3
70°-80°	117.4	4.4
80°-90°	67.2	2.5
90°-100°	69.1	2.6
100°-110°	118.1	4.4
110°-120°	170.7	6.4
120°-130°	210.3	7.9
130°-140°	228.6	8.6
140°-150°	220.9	8.3
150°-160°	185.0	7.0
160°-170°	123.1	4.6
170°-180°	43.1	1.6
0°-30°	316.9	11.9
0°-40°	519.5	19.6
0°-60°	935.3	35.2
0°-90°	1287.1	48.5
90°-120°	357.9	13.5
90°-150°	1017.7	38.3
90°-180°	1369.0	51.5
0°-180°	2656.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	408	407	404	408	407	39
15°	392	392	391	395	394	110
25°	358	361	362	367	368	165
35°	313	319	324	330	331	196
45°	261	270	279	286	289	202
55°	205	214	228	237	240	182
65°	142	156	172	183	187	140
75°	79	96	115	128	132	84
85°	24	43	64	78	82	25
90°	8	30	53	68	73	7
95°	27	45	66	80	84	28
105°	86	96	114	126	131	92
115°	156	160	174	184	187	154
125°	226	225	236	244	246	201
135°	290	292	295	301	303	224
145°	351	352	352	355	356	220
155°	402	402	401	403	401	185
165°	437	436	436	438	436	123
175°	455	453	453	455	453	43
180°	456	456	456	456	456	

TEST NUMBER: P1001227

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	408.0	408.0	408.0	408.0	408.0
2.5°	409.8	408.4	404.8	408.0	407.5
5°	408.4	407.1	403.9	407.5	407.1
7.5°	405.7	404.8	402.0	406.2	405.7
10°	402.0	401.6	399.3	403.4	403.0
12.5°	397.0	397.0	395.7	399.3	399.3
15°	391.5	392.0	390.6	394.7	394.3
17.5°	384.2	385.6	385.1	389.3	388.8
20°	376.5	377.8	378.3	382.9	382.9
22.5°	367.8	369.6	370.5	375.1	376.0
25°	358.2	360.9	362.3	367.3	367.8
27.5°	347.7	351.8	353.6	358.2	358.6
30°	337.2	340.8	344.0	349.1	350.0
32.5°	325.8	330.3	334.0	339.9	340.8
35°	313.4	318.9	323.5	329.9	331.2
37.5°	301.1	307.5	313.0	319.4	320.7
40°	289.2	295.1	301.5	308.4	310.2
42.5°	275.5	282.3	290.1	297.9	299.3
45°	261.3	270.0	278.7	286.5	288.7
47.5°	248.1	256.8	266.8	274.6	277.3
50°	233.5	243.5	253.6	262.7	265.4
52.5°	218.8	228.9	240.8	249.9	252.7
55°	204.7	214.3	228.0	237.1	239.9
57.5°	188.7	200.6	213.8	224.8	227.1
60°	173.2	185.0	200.1	210.6	214.3
62.5°	158.1	171.3	186.4	196.9	200.6
65°	141.6	156.3	171.8	183.2	186.9
67.5°	126.1	141.6	158.1	169.5	173.2
70°	110.1	125.6	143.0	155.3	158.5
72.5°	94.6	110.6	129.3	141.2	144.8
75°	78.6	95.5	114.7	127.5	131.6
77.5°	63.5	81.3	101.4	114.2	118.8
80°	49.8	68.1	88.2	101.9	105.5
82.5°	36.1	55.3	75.4	89.5	93.7
85°	24.2	43.4	64.0	77.7	82.2
87.5°	15.1	33.8	53.9	67.2	71.3
90°	8.4	30.5	53.0	68.4	72.7
92.5°	16.1	36.5	58.0	71.9	75.8
95°	27.0	45.3	66.5	79.9	84.0
97.5°	39.3	55.3	77.0	90.2	94.4
100°	54.3	67.6	88.6	101.7	104.9
102.5°	70.5	81.0	101.1	114.1	118.1
105°	86.2	95.6	114.1	126.5	131.2
107.5°	103.5	111.6	128.0	140.8	143.6
110°	120.7	127.8	143.3	153.1	157.9

TEST NUMBER: P1001227

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	138.5	144.0	158.4	168.4	172.1
115°	156.3	160.5	174.4	184.1	186.9
117.5°	173.6	176.4	189.7	198.3	200.8
120°	190.4	193.3	205.4	212.7	217.1
122.5°	208.4	208.8	220.7	228.9	230.3
125°	225.5	225.1	236.2	244.2	246.2
127.5°	241.4	242.0	250.4	257.9	260.8
130°	257.9	258.5	265.8	273.3	274.6
132.5°	275.2	275.4	280.5	287.6	290.0
135°	289.5	291.6	294.8	301.4	303.1
137.5°	306.0	306.7	309.2	314.9	317.6
140°	322.6	322.9	323.3	328.9	330.8
142.5°	337.3	338.0	337.2	342.2	344.1
145°	351.1	352.0	352.3	354.7	355.5
147.5°	365.2	366.4	366.1	366.2	367.7
150°	377.8	378.8	378.8	378.8	378.4
152.5°	389.3	390.0	390.4	391.4	390.4
155°	401.7	401.7	401.3	402.7	401.3
157.5°	412.2	411.5	411.5	412.6	411.5
160°	421.4	421.0	420.7	421.7	420.0
162.5°	429.8	428.8	428.4	430.5	428.8
165°	437.2	436.2	435.5	437.6	436.2
167.5°	443.2	441.8	441.8	443.9	441.8
170°	448.2	446.4	446.8	448.9	446.4
172.5°	451.7	450.3	450.3	452.7	450.3
175°	454.9	453.1	452.7	455.2	452.7
177.5°	456.3	454.5	454.5	457.0	454.2
180°	455.6	455.6	455.6	455.6	455.6

(END OF REPORT)