

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007932

Luminaire Tested: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007932
REPORT IS A COMBINATION OF REPORTS P983540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8323.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007932

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007932

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41		
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29		
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22		
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	18	21	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25183	23965	23795
10°	24979	22873	22420
15°	24613	21773	20971
20°	24118	20575	19601
25°	23625	19325	18232
30°	23005	18152	16796
35°	22421	16912	15385
40°	21698	15689	14051
45°	20979	14475	12743
50°	20197	13242	11386
55°	19372	11922	10101
60°	18443	10493	8766
65°	17426	9040	7360
70°	16136	7451	5944
75°	14354	5744	4590
80°	12191	3903	2954
85°	8843	1817	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20979 cd/sqm

TEST NUMBER: P1007932

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.8
10°-20°	420.6	5.1
20°-30°	618.1	7.4
30°-40°	717.9	8.6
40°-50°	717.0	8.6
50°-60°	625.2	7.5
60°-70°	462.2	5.6
70°-80°	261.5	3.1
80°-90°	71.6	0.9
90°-100°	48.1	0.6
100°-110°	179.4	2.2
110°-120°	475.9	5.7
120°-130°	789.3	9.5
130°-140°	838.4	10.1
140°-150°	779.2	9.4
150°-160°	626.5	7.5
160°-170°	403.7	4.9
170°-180°	138.9	1.7
0°-30°	1188.2	14.3
0°-40°	1906.1	22.9
0°-60°	3248.3	39.0
0°-90°	4043.6	48.6
90°-120°	703.5	8.5
90°-150°	3110.3	37.4
90°-180°	4279.0	51.4
0°-180°	8323.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	70
90°	1	13	21	26	28	8
95°	69	34	41	46	45	81
105°	321	353	64	76	80	343
115°	607	625	652	163	87	598
125°	859	872	892	900	903	766
135°	1063	1080	1089	1100	1097	821
145°	1233	1232	1250	1257	1252	771
155°	1357	1348	1360	1367	1358	625
165°	1430	1424	1427	1434	1427	404
175°	1463	1456	1458	1465	1454	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P1007932

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	1.1	12.7	21.1	26.4	28.5
92.5°	26.4	22.2	25.3	27.5	28.5
95°	68.7	33.8	41.2	46.5	45.4
97.5°	123.6	37.0	53.9	57.0	58.1
100°	187.0	42.2	60.2	68.7	70.8
102.5°	256.7	254.6	62.3	73.9	77.1
105°	321.1	352.8	64.4	76.0	80.3
107.5°	396.1	422.5	66.5	78.2	82.4
110°	467.9	490.1	184.8	79.2	83.4

TEST NUMBER: P1007932

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	535.5	554.5	536.6	81.3	84.5
115°	607.3	625.3	651.7	162.7	86.6
117.5°	669.7	690.8	708.7	557.7	281.0
120°	739.4	755.2	774.2	786.9	644.3
122.5°	798.5	815.4	836.5	842.9	843.9
125°	858.7	872.5	892.5	899.9	903.1
127.5°	913.7	928.4	944.3	954.8	955.9
130°	965.4	982.3	993.9	1005.5	1004.5
132.5°	1018.2	1032.0	1043.6	1053.1	1052.0
135°	1062.6	1079.5	1089.0	1099.6	1097.4
137.5°	1109.1	1121.7	1132.3	1142.9	1139.7
140°	1154.5	1162.9	1174.5	1184.1	1178.8
142.5°	1192.5	1199.9	1213.6	1222.1	1216.8
145°	1232.6	1231.6	1249.5	1256.9	1251.7
147.5°	1267.5	1264.3	1282.3	1287.6	1283.3
150°	1301.3	1293.9	1310.8	1317.1	1311.9
152.5°	1329.8	1321.4	1337.2	1343.5	1336.2
155°	1357.3	1347.8	1360.4	1366.8	1358.3
157.5°	1379.5	1371.0	1380.5	1387.9	1379.5
160°	1398.5	1392.1	1398.5	1404.8	1397.4
162.5°	1415.4	1409.0	1414.3	1421.7	1412.2
165°	1430.2	1423.8	1427.0	1434.4	1427.0
167.5°	1441.8	1435.4	1438.6	1446.0	1436.5
170°	1451.3	1444.9	1447.1	1454.5	1444.9
172.5°	1457.6	1451.3	1453.4	1460.8	1451.3
175°	1462.9	1455.5	1457.6	1465.0	1454.5
177.5°	1465.0	1457.6	1458.7	1466.1	1456.6
180°	1459.7	1459.7	1459.7	1459.7	1459.7

(END OF REPORT)