

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001248

Luminaire Tested: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001248
REPORT IS A COMBINATION OF REPORTS P995867 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2679.1 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001248

CATALOG NUMBER: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001248

CATALOG NUMBER: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	44	44	44
1	96	92	87	84	89	84	81	77	71	68	66	58	56	55	47	45	44	39	39	39
2	87	80	73	67	80	73	68	63	61	57	54	51	48	45	41	38	36	32	32	32
3	79	70	62	56	73	64	57	52	54	49	45	44	41	37	36	33	31	26	26	26
4	73	61	53	47	66	57	49	44	48	42	38	39	35	32	32	29	26	22	22	22
5	66	54	46	40	61	50	43	37	42	37	32	35	31	27	28	25	22	19	19	19
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	22	20	17	17	17
7	56	44	36	30	52	41	33	28	34	29	24	29	24	21	23	20	17	15	15	15
8	52	40	32	26	48	37	30	25	31	26	22	26	22	19	21	18	15	13	13	13
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	16	14	12	12	12
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13	11	11	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3356	3356	3356
5°	3365	3268	3274
10°	3343	3204	3194
15°	3312	3132	3105
20°	3265	3054	3018
25°	3213	2967	2925
30°	3157	2881	2829
35°	3093	2794	2744
40°	3041	2710	2656
45°	2966	2631	2577
50°	2901	2542	2495
55°	2833	2455	2400
60°	2729	2348	2311
65°	2617	2233	2205
70°	2479	2100	2080
75°	2285	1954	1962
80°	2065	1803	1838
85°	1776	1653	1738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2966 cd/sqm

TEST NUMBER: P1001248

CATALOG NUMBER: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	1.5
10°-20°	111.7	4.2
20°-30°	168.9	6.3
30°-40°	204.4	7.6
40°-50°	216.0	8.1
50°-60°	203.3	7.6
60°-70°	168.7	6.3
70°-80°	118.4	4.4
80°-90°	67.7	2.5
90°-100°	69.7	2.6
100°-110°	119.2	4.4
110°-120°	172.2	6.4
120°-130°	212.1	7.9
130°-140°	230.6	8.6
140°-150°	222.9	8.3
150°-160°	186.6	7.0
160°-170°	124.2	4.6
170°-180°	43.5	1.6
0°-30°	319.6	11.9
0°-40°	524.0	19.6
0°-60°	943.3	35.2
0°-90°	1298.2	48.5
90°-120°	361.0	13.5
90°-150°	1026.6	38.3
90°-180°	1381.0	51.5
0°-180°	2679.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	412	412	412	412	412	
5°	412	411	407	411	411	39
15°	395	395	394	398	398	111
25°	361	364	365	370	371	166
35°	316	322	326	333	334	198
45°	264	272	281	289	291	204
55°	206	216	230	239	242	184
65°	143	158	173	185	188	142
75°	79	96	116	129	133	84
85°	24	44	64	78	83	25
90°	8	31	53	69	73	7
95°	27	46	67	81	85	28
105°	87	97	115	128	132	92
115°	158	162	176	186	188	156
125°	228	227	238	246	248	203
135°	292	294	297	304	306	226
145°	354	355	355	358	359	222
155°	405	405	405	406	405	186
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1001248

CATALOG NUMBER: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	411.5	411.5	411.5	411.5	411.5
2.5°	413.4	412.0	408.3	411.5	411.0
5°	412.0	410.6	407.4	411.0	410.6
7.5°	409.2	408.3	405.5	409.7	409.2
10°	405.5	405.1	402.8	406.9	406.4
12.5°	400.4	400.4	399.1	402.8	402.8
15°	394.9	395.4	394.0	398.1	397.7
17.5°	387.5	388.9	388.5	392.6	392.2
20°	379.7	381.1	381.6	386.2	386.2
22.5°	371.0	372.8	373.7	378.3	379.3
25°	361.3	364.0	365.4	370.5	371.0
27.5°	350.7	354.8	356.7	361.3	361.7
30°	340.1	343.8	347.0	352.1	353.0
32.5°	328.6	333.2	336.9	342.8	343.8
35°	316.1	321.6	326.3	332.7	334.1
37.5°	303.7	310.1	315.7	322.1	323.5
40°	291.7	297.7	304.1	311.1	312.9
42.5°	277.9	284.8	292.6	300.5	301.8
45°	263.6	272.3	281.1	288.9	291.2
47.5°	250.2	259.0	269.1	277.0	279.7
50°	235.5	245.6	255.8	265.0	267.7
52.5°	220.7	230.9	242.8	252.1	254.8
55°	206.4	216.1	229.9	239.2	241.9
57.5°	190.3	202.3	215.7	226.7	229.0
60°	174.6	186.6	201.8	212.4	216.1
62.5°	159.4	172.8	188.0	198.6	202.3
65°	142.9	157.6	173.3	184.8	188.5
67.5°	127.2	142.9	159.4	171.0	174.6
70°	111.1	126.7	144.2	156.7	159.9
72.5°	95.4	111.5	130.4	142.4	146.1
75°	79.3	96.3	115.7	128.6	132.7
77.5°	64.1	82.0	102.3	115.2	119.8
80°	50.2	68.7	88.9	102.8	106.4
82.5°	36.4	55.8	76.0	90.3	94.5
85°	24.4	43.8	64.5	78.3	82.9
87.5°	15.2	34.1	54.4	67.7	71.9
90°	8.5	30.8	53.4	69.0	73.4
92.5°	16.1	36.9	58.5	72.5	76.5
95°	27.3	45.7	67.1	80.6	84.8
97.5°	39.6	55.9	77.6	91.0	95.1
100°	54.9	68.3	89.4	102.6	105.8
102.5°	71.2	81.7	102.0	115.1	119.1
105°	86.9	96.6	115.0	127.6	132.3
107.5°	104.3	112.6	129.0	142.0	144.9
110°	121.7	128.8	144.6	154.5	159.3

TEST NUMBER: P1001248

CATALOG NUMBER: SA4XXDIP-B350D365UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.7	145.3	159.8	169.9	173.6
115°	157.8	161.9	175.9	185.7	188.5
117.5°	175.2	177.9	191.4	199.9	202.6
120°	192.1	194.9	207.2	214.7	219.1
122.5°	210.2	210.6	222.6	230.8	232.3
125°	227.5	227.1	238.2	246.3	248.3
127.5°	243.5	244.1	252.6	260.2	263.1
130°	260.1	260.7	268.1	275.7	277.1
132.5°	277.5	277.8	283.0	290.1	292.5
135°	292.0	294.1	297.3	304.0	305.7
137.5°	308.7	309.3	311.8	317.7	320.3
140°	325.4	325.7	326.1	331.7	333.7
142.5°	340.3	341.0	340.1	345.2	347.0
145°	354.1	355.0	355.4	357.8	358.6
147.5°	368.3	369.6	369.3	369.4	370.8
150°	381.1	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)