

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001270

Luminaire Tested: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001270
REPORT IS A COMBINATION OF REPORTS P995889 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2781.6 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001270

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001270

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	46	44	42
3	82	72	65	59	75	67	61	55	57	53	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	24	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3893 cd/sqm

TEST NUMBER: P1001270

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.9
10°-20°	151.9	5.5
20°-30°	223.5	8.0
30°-40°	259.8	9.3
40°-50°	259.8	9.3
50°-60°	227.2	8.2
60°-70°	168.7	6.1
70°-80°	95.7	3.4
80°-90°	28.1	1.0
90°-100°	133.6	4.8
100°-110°	271.8	9.8
110°-120°	242.3	8.7
120°-130°	203.5	7.3
130°-140°	169.8	6.1
140°-150°	129.7	4.7
150°-160°	91.2	3.3
160°-170°	53.6	1.9
170°-180°	17.4	0.6
0°-30°	429.3	15.4
0°-40°	689.1	24.8
0°-60°	1176.2	42.3
0°-90°	1468.7	52.8
90°-120°	647.7	23.3
90°-150°	1150.7	41.4
90°-180°	1313.0	47.2
0°-180°	2781.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	0	3	6	7	7	2
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001270

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	0.4	2.8	6.4	7.1	7.4
92.5°	4.9	27.2	138.6	45.8	32.2
95°	11.7	36.8	288.1	142.6	86.2
97.5°	19.4	40.6	308.2	291.2	207.1
100°	26.9	46.0	284.2	403.0	324.1
102.5°	33.9	52.3	254.1	472.9	425.9
105°	41.4	59.9	231.9	499.2	497.3
107.5°	49.5	67.7	217.4	491.2	531.2
110°	57.6	75.4	210.7	463.0	531.9



TEST NUMBER: P1001270

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.2	207.5	428.4	511.1
115°	72.8	91.4	206.8	397.2	477.5
117.5°	80.6	99.0	206.4	372.8	444.6
120°	88.4	106.4	206.4	356.4	417.8
122.5°	95.4	113.6	206.1	345.7	396.6
125°	101.4	120.6	205.7	338.1	381.0
127.5°	107.1	126.8	205.0	330.8	371.1
130°	111.7	133.0	204.6	322.2	362.6
132.5°	116.3	138.4	204.3	312.0	353.1
135°	120.5	143.5	203.9	300.0	340.7
137.5°	124.8	147.9	203.9	287.4	326.2
140°	129.4	152.0	203.6	275.0	310.3
142.5°	134.3	155.7	203.6	263.5	293.4
145°	138.9	159.0	202.9	253.0	278.2
147.5°	144.2	162.2	201.8	244.4	264.0
150°	149.2	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)