

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007948

Luminaire Tested: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007948
REPORT IS A COMBINATION OF REPORTS P983601 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5176.0 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007948

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007948

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76		
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67	64		
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53		
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45		
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39		
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	44	40	36	34		
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	30		
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26		
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24		
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21		
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1007948

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.8
10°-20°	406.8	7.9
20°-30°	597.8	11.5
30°-40°	694.3	13.4
40°-50°	693.4	13.4
50°-60°	604.6	11.7
60°-70°	446.9	8.6
70°-80°	252.9	4.9
80°-90°	67.5	1.3
90°-100°	14.3	0.3
100°-110°	53.1	1.0
110°-120°	140.9	2.7
120°-130°	233.7	4.5
130°-140°	248.3	4.8
140°-150°	230.7	4.5
150°-160°	185.5	3.6
160°-170°	119.5	2.3
170°-180°	41.1	0.8
0°-30°	1149.1	22.2
0°-40°	1843.4	35.6
0°-60°	3141.4	60.7
0°-90°	3908.8	75.5
90°-120°	208.3	4.0
90°-150°	921.1	17.8
90°-180°	1267.0	24.5
0°-180°	5176.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	0	4	6	8	8	5
95°	20	10	12	14	13	24
105°	95	104	19	22	24	102
115°	180	185	193	48	26	177
125°	254	258	264	266	267	227
135°	315	320	322	326	325	243
145°	365	365	370	372	371	228
155°	402	399	403	405	402	185
165°	424	422	423	425	423	120
175°	433	431	432	434	431	41
180°	432	432	432	432	432	

TEST NUMBER: P1007948

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	0.3	3.8	6.3	7.8	8.4
92.5°	7.8	6.6	7.5	8.1	8.4
95°	20.3	10.0	12.2	13.8	13.4
97.5°	36.6	10.9	16.0	16.9	17.2
100°	55.4	12.5	17.8	20.3	21.0
102.5°	76.0	75.4	18.5	21.9	22.8
105°	95.1	104.5	19.1	22.5	23.8
107.5°	117.3	125.1	19.7	23.1	24.4
110°	138.6	145.1	54.7	23.5	24.7



TEST NUMBER: P1007948

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	158.6	164.2	158.9	24.1	25.0
115°	179.8	185.2	193.0	48.2	25.6
117.5°	198.3	204.6	209.9	165.1	83.2
120°	218.9	223.6	229.3	233.0	190.8
122.5°	236.5	241.5	247.7	249.6	249.9
125°	254.3	258.4	264.3	266.5	267.4
127.5°	270.6	274.9	279.6	282.8	283.1
130°	285.9	290.9	294.3	297.8	297.5
132.5°	301.5	305.6	309.0	311.8	311.5
135°	314.7	319.7	322.5	325.6	325.0
137.5°	328.4	332.2	335.3	338.4	337.5
140°	341.9	344.4	347.8	350.6	349.1
142.5°	353.1	355.3	359.4	361.9	360.3
145°	365.0	364.7	370.0	372.2	370.6
147.5°	375.3	374.4	379.7	381.3	380.0
150°	385.3	383.2	388.2	390.0	388.5
152.5°	393.8	391.3	396.0	397.9	395.7
155°	401.9	399.1	402.9	404.7	402.2
157.5°	408.5	406.0	408.8	411.0	408.5
160°	414.1	412.2	414.1	416.0	413.8
162.5°	419.1	417.2	418.8	421.0	418.2
165°	423.5	421.6	422.6	424.8	422.6
167.5°	426.9	425.1	426.0	428.2	425.4
170°	429.8	427.9	428.5	430.7	427.9
172.5°	431.6	429.8	430.4	432.6	429.8
175°	433.2	431.0	431.6	433.8	430.7
177.5°	433.8	431.6	431.9	434.1	431.3
180°	432.3	432.3	432.3	432.3	432.3

(END OF REPORT)