

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007957

Luminaire Tested: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007957
REPORT IS A COMBINATION OF REPORTS P983655 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6129.0 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007957

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007957

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	98	93	88	84	91	86	82	79	75	71	69	64	61	59	54	52	50
2	88	80	73	67	82	75	68	63	64	60	55	55	51	48	46	43	41
3	80	70	62	55	74	65	58	52	56	51	46	48	44	40	40	37	34
4	73	61	53	46	68	57	50	44	50	43	39	42	38	34	36	32	29
5	67	55	46	39	62	51	43	37	44	38	33	38	33	29	32	28	25
6	62	49	40	34	57	46	38	32	40	33	29	34	29	25	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	29	23	46	34	27	22	30	24	20	26	21	18	22	18	15
10	46	33	26	21	43	31	24	20	28	22	18	24	19	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16681	16681	16681
5°	16757	15969	15880
10°	16645	15416	15191
15°	16409	14845	14486
20°	16112	14243	13816
25°	15821	13668	13209
30°	15411	13083	12607
35°	14996	12520	12166
40°	14558	12033	11726
45°	14144	11591	11345
50°	13695	11183	10966
55°	13227	10751	10583
60°	12651	10300	10179
65°	12055	9782	9714
70°	11377	9225	9213
75°	10511	8668	8741
80°	9141	8090	8252
85°	7769	7544	7828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14144 cd/sqm

TEST NUMBER: P1007957

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.6
10°-20°	286.5	4.7
20°-30°	434.1	7.1
30°-40°	528.7	8.6
40°-50°	568.8	9.3
50°-60°	552.4	9.0
60°-70°	482.4	7.9
70°-80°	371.3	6.1
80°-90°	249.9	4.1
90°-100°	195.3	3.2
100°-110°	213.6	3.5
110°-120°	317.0	5.2
120°-130°	434.7	7.1
130°-140°	432.1	7.0
140°-150°	386.9	6.3
150°-160°	308.4	5.0
160°-170°	198.7	3.2
170°-180°	68.4	1.1
0°-30°	820.6	13.4
0°-40°	1349.2	22.0
0°-60°	2470.4	40.3
0°-90°	3574.0	58.3
90°-120°	725.9	11.8
90°-150°	1979.5	32.3
90°-180°	2555.0	41.7
0°-180°	6129.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1052	1043	1052	1051	100
15°	1008	1011	1011	1025	1023	284
25°	916	927	941	959	964	421
35°	790	816	845	878	889	494
45°	648	689	742	790	805	500
55°	496	551	631	686	706	444
65°	339	414	504	567	586	337
75°	188	273	371	437	457	199
85°	55	150	247	312	333	58
90°	16	110	212	276	295	13
95°	46	101	196	257	274	50
105°	166	226	163	222	241	178
115°	305	331	412	218	197	300
125°	426	433	491	536	552	380
135°	525	533	553	590	601	406
145°	607	606	615	628	633	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P1007957

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1053.8	1053.8	1053.8	1053.8	1053.8
2.5°	1061.5	1056.9	1046.2	1053.8	1050.8
5°	1056.9	1052.3	1043.1	1052.3	1050.8
7.5°	1049.2	1046.2	1038.5	1049.2	1047.7
10°	1040.1	1037.0	1032.4	1044.7	1043.1
12.5°	1024.8	1026.3	1023.3	1035.5	1034.0
15°	1008.0	1011.1	1011.1	1024.8	1023.3
17.5°	986.6	992.7	997.3	1011.1	1011.1
20°	965.2	972.9	979.0	995.8	995.8
22.5°	942.3	951.5	960.7	977.5	980.5
25°	916.4	927.1	940.8	959.1	963.7
27.5°	885.8	902.6	917.9	940.8	943.9
30°	855.3	875.1	895.0	919.4	924.0
32.5°	821.7	844.6	869.0	898.0	907.2
35°	789.6	815.6	844.6	878.2	888.9
37.5°	754.5	783.5	820.1	856.8	867.5
40°	719.3	752.9	794.2	833.9	847.6
42.5°	685.7	719.3	768.2	812.5	826.3
45°	647.6	688.8	742.3	789.6	804.9
47.5°	610.9	655.2	716.3	765.2	782.0
50°	572.7	620.1	688.8	740.7	757.5
52.5°	536.1	586.5	659.8	713.2	731.6
55°	496.4	551.3	630.8	685.7	705.6
57.5°	458.2	519.3	598.7	658.3	678.1
60°	416.9	482.6	569.7	627.7	649.1
62.5°	380.3	449.0	536.1	598.7	618.5
65°	339.1	413.9	504.0	566.6	586.5
67.5°	302.4	380.3	471.9	534.5	555.9
70°	262.7	342.1	436.8	502.5	520.8
72.5°	226.0	308.5	404.7	468.9	491.8
75°	187.9	273.4	371.1	436.8	456.7
77.5°	151.2	239.8	339.1	404.7	426.1
80°	114.5	207.7	307.0	371.1	392.5
82.5°	84.0	175.6	276.4	340.6	360.4
85°	55.0	149.7	247.4	311.6	332.9
87.5°	33.6	125.2	223.0	285.6	305.5
90°	15.8	110.1	212.0	275.7	295.0
92.5°	26.7	105.6	200.4	260.9	279.7
95°	46.0	100.6	195.9	256.6	274.4
97.5°	71.5	94.6	191.4	249.6	268.4
100°	102.7	88.0	182.3	243.0	260.8
102.5°	135.6	184.9	172.7	233.4	251.8
105°	165.7	225.6	163.0	222.2	241.1
107.5°	202.6	252.3	153.5	211.1	230.0
110°	236.5	278.0	202.5	199.4	218.3

TEST NUMBER: P1007957

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.7	303.5	365.0	189.7	208.1
115°	305.1	330.7	412.4	217.6	196.9
117.5°	334.3	356.9	429.8	401.4	280.3
120°	368.6	382.5	452.9	501.9	448.5
122.5°	397.7	407.5	474.4	518.8	533.1
125°	425.8	432.6	491.3	536.2	551.5
127.5°	452.9	458.6	507.7	551.0	565.3
130°	478.4	485.1	522.9	565.3	577.0
132.5°	504.4	509.5	538.1	578.0	589.7
135°	524.6	532.9	552.9	590.2	601.4
137.5°	547.5	553.7	566.6	600.8	610.0
140°	569.8	572.5	581.3	610.4	617.0
142.5°	588.6	590.7	597.5	619.9	625.0
145°	606.8	606.3	615.1	628.0	633.0
147.5°	624.0	622.4	631.3	635.4	637.9
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

(END OF REPORT)