

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001277

Luminaire Tested: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001277
REPORT IS A COMBINATION OF REPORTS P995896 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2834.0 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001277

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1001277

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	52	45	40	45	39	35	38	34	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4509	4509	4509
5°	4512	4379	4384
10°	4474	4257	4227
15°	4409	4112	4050
20°	4327	3956	3867
25°	4235	3791	3671
30°	4124	3612	3454
35°	4009	3430	3245
40°	3889	3233	3023
45°	3763	3036	2815
50°	3623	2844	2585
55°	3472	2621	2356
60°	3317	2376	2118
65°	3139	2124	1849
70°	2936	1819	1563
75°	2631	1466	1251
80°	2242	1061	879
85°	1739	589	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3763 cd/sqm

TEST NUMBER: P1001277

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.8
10°-20°	146.8	5.2
20°-30°	216.1	7.6
30°-40°	251.2	8.9
40°-50°	251.1	8.9
50°-60°	219.6	7.8
60°-70°	163.1	5.8
70°-80°	92.5	3.3
80°-90°	27.4	1.0
90°-100°	15.2	0.5
100°-110°	99.9	3.5
110°-120°	190.8	6.7
120°-130°	242.2	8.5
130°-140°	259.1	9.1
140°-150°	242.2	8.5
150°-160°	195.4	6.9
160°-170°	126.0	4.4
170°-180°	43.4	1.5
0°-30°	415.0	14.6
0°-40°	666.1	23.5
0°-60°	1136.9	40.1
0°-90°	1420.0	50.1
90°-120°	305.8	10.8
90°-150°	1049.3	37.0
90°-180°	1414.0	49.9
0°-180°	2834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	553	553	553	553	553	
5°	552	551	546	551	550	52
15°	526	524	517	520	519	148
25°	476	473	467	467	466	219
35°	410	407	400	397	395	256
45°	334	331	324	319	318	258
55°	253	252	245	240	237	227
65°	171	169	165	160	158	170
75°	91	89	87	85	85	97
85°	24	24	23	23	23	26
90°	1	5	8	10	10	3
95°	19	7	8	10	10	23
105°	103	105	107	110	97	108
115°	192	193	193	194	194	189
125°	270	271	271	272	272	241
135°	335	335	336	337	337	258
145°	386	387	387	388	388	241
155°	424	424	423	424	423	195
165°	447	445	445	448	445	126
175°	457	455	455	458	454	44
180°	457	457	457	457	457	

TEST NUMBER: P1001277

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	552.9	552.9	552.9	552.9	552.9
2.5°	554.6	553.3	548.4	552.9	552.4
5°	552.4	550.6	545.8	550.6	549.8
7.5°	548.4	546.6	541.3	545.3	544.9
10°	542.7	540.9	535.1	538.7	537.8
12.5°	535.1	533.4	527.2	531.1	529.8
15°	525.8	524.1	517.4	520.1	518.7
17.5°	515.2	513.0	506.8	508.6	507.7
20°	503.2	501.0	494.4	495.7	494.8
22.5°	490.4	487.3	480.6	483.3	481.5
25°	476.2	473.1	466.9	467.4	465.6
27.5°	460.3	457.2	451.4	450.5	448.3
30°	444.3	440.8	435.0	433.2	431.0
32.5°	427.5	424.4	418.2	416.0	413.8
35°	409.8	406.7	400.5	397.4	395.1
37.5°	391.2	388.5	381.9	378.8	375.7
40°	373.0	369.5	362.8	358.4	356.2
42.5°	353.5	351.7	344.2	338.9	337.6
45°	334.5	331.4	324.3	319.4	318.1
47.5°	314.5	312.3	305.7	300.3	296.8
50°	294.1	292.4	286.2	280.0	277.3
52.5°	274.2	272.0	265.4	260.0	256.5
55°	252.9	251.6	245.4	240.1	237.4
57.5°	233.0	231.7	225.5	220.2	217.5
60°	212.2	210.0	204.2	200.2	198.0
62.5°	191.8	190.0	183.8	180.3	178.1
65°	171.4	169.2	164.8	160.4	158.1
67.5°	150.6	148.8	144.4	140.0	139.5
70°	131.6	128.5	124.9	121.4	120.1
72.5°	111.2	108.1	105.4	102.8	101.4
75°	91.3	89.0	86.8	85.1	84.6
77.5°	71.8	70.9	68.7	68.2	66.9
80°	54.5	53.2	52.3	51.4	50.9
82.5°	37.7	37.2	37.2	36.8	36.3
85°	23.9	23.9	23.0	23.0	22.6
87.5°	11.5	11.1	10.6	10.6	10.6
90°	1.0	4.8	7.5	9.6	10.3
92.5°	5.1	4.4	7.2	9.2	9.2
95°	18.8	7.2	7.5	9.6	9.9
97.5°	35.9	43.4	7.5	9.2	9.6
100°	56.1	62.2	15.0	9.2	9.6
102.5°	78.6	82.7	86.8	9.9	9.9
105°	102.9	104.9	106.6	109.7	97.4
107.5°	125.1	126.1	128.5	130.2	131.6
110°	147.7	148.7	150.7	151.4	152.4



TEST NUMBER: P1001277

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.5	171.6	172.3	171.9	173.3
115°	192.1	193.1	192.8	193.5	193.5
117.5°	212.3	213.6	214.6	214.3	214.3
120°	232.8	234.1	233.8	234.5	233.8
122.5°	251.9	252.6	253.3	253.6	252.9
125°	270.0	271.4	270.7	271.7	272.1
127.5°	287.4	287.8	289.5	289.2	288.8
130°	304.2	304.5	305.6	305.9	305.9
132.5°	319.6	320.3	321.6	322.0	321.6
135°	335.0	334.6	336.0	336.7	337.4
137.5°	348.6	348.6	350.3	351.0	350.7
140°	362.0	362.6	363.3	364.4	364.7
142.5°	373.9	375.3	375.6	376.3	376.3
145°	386.2	387.3	387.3	387.6	388.3
147.5°	395.8	397.8	397.5	397.8	398.2
150°	406.4	407.8	407.4	407.4	407.8
152.5°	415.3	416.3	415.6	416.3	416.0
155°	423.5	423.8	422.8	424.2	423.1
157.5°	430.7	430.7	429.3	431.0	429.3
160°	436.8	435.8	435.4	437.5	435.4
162.5°	442.3	440.9	440.6	442.6	440.2
165°	446.7	445.0	445.0	447.8	444.7
167.5°	450.5	448.8	448.4	451.5	448.1
170°	453.6	451.5	451.9	454.6	451.2
172.5°	455.6	453.6	453.9	456.6	452.9
175°	457.0	454.9	455.3	458.3	454.2
177.5°	458.0	455.6	456.3	459.0	454.9
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)