

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007958

Luminaire Tested: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007958
REPORT IS A COMBINATION OF REPORTS P983656 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5926.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007958

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007958

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	98	93	88	84	91	86	82	79	75	71	69	64	61	59	54	52	50
2	88	80	73	67	82	75	68	63	64	60	55	55	51	48	46	43	41
3	80	70	62	55	74	65	58	52	56	51	46	48	44	40	40	37	34
4	73	61	53	46	68	57	50	44	50	43	39	42	38	34	36	32	29
5	67	55	46	39	62	51	43	37	44	38	33	38	33	29	32	28	25
6	62	49	40	34	57	46	38	32	40	33	29	34	29	25	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	29	23	46	34	27	22	30	24	20	26	21	18	22	18	15
10	46	33	26	21	43	31	24	20	28	22	18	24	19	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16130	16130	16130
5°	16202	15441	15354
10°	16094	14906	14688
15°	15867	14353	14006
20°	15580	13772	13358
25°	15298	13216	12771
30°	14901	12651	12190
35°	14500	12105	11764
40°	14078	11634	11339
45°	13674	11207	10970
50°	13243	10813	10604
55°	12787	10395	10233
60°	12235	9958	9842
65°	11653	9457	9392
70°	11000	8921	8909
75°	10159	8383	8452
80°	8846	7821	7978
85°	7515	7294	7570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13674 cd/sqm

TEST NUMBER: P1007958

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.6
10°-20°	277.0	4.7
20°-30°	419.8	7.1
30°-40°	511.2	8.6
40°-50°	550.0	9.3
50°-60°	534.1	9.0
60°-70°	466.4	7.9
70°-80°	359.0	6.1
80°-90°	241.7	4.1
90°-100°	188.8	3.2
100°-110°	206.6	3.5
110°-120°	306.5	5.2
120°-130°	420.2	7.1
130°-140°	417.8	7.0
140°-150°	374.0	6.3
150°-160°	298.2	5.0
160°-170°	192.1	3.2
170°-180°	66.1	1.1
0°-30°	793.4	13.4
0°-40°	1304.6	22.0
0°-60°	2388.7	40.3
0°-90°	3455.8	58.3
90°-120°	701.8	11.8
90°-150°	1913.8	32.3
90°-180°	2470.0	41.7
0°-180°	5926.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1019	1019	1019	1019	1019	
5°	1022	1018	1009	1018	1016	97
15°	975	978	978	991	989	275
25°	886	896	910	927	932	407
35°	764	789	817	849	860	477
45°	626	666	718	764	778	483
55°	480	533	610	663	682	429
65°	328	400	487	548	567	326
75°	182	264	359	422	442	192
85°	53	145	239	301	322	56
90°	15	106	205	267	285	12
95°	44	97	189	248	265	48
105°	160	218	158	215	233	172
115°	295	320	399	210	190	290
125°	412	418	475	518	533	368
135°	507	515	534	571	581	392
145°	587	586	595	607	612	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P1007958

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1019.0	1019.0	1019.0	1019.0	1019.0
2.5°	1026.3	1021.9	1011.6	1019.0	1016.0
5°	1021.9	1017.5	1008.6	1017.5	1016.0
7.5°	1014.5	1011.6	1004.2	1014.5	1013.1
10°	1005.7	1002.7	998.3	1010.1	1008.6
12.5°	990.9	992.4	989.4	1001.2	999.8
15°	974.7	977.6	977.6	990.9	989.4
17.5°	954.0	959.9	964.3	977.6	977.6
20°	933.3	940.7	946.6	962.8	962.8
22.5°	911.2	920.0	928.9	945.1	948.1
25°	886.1	896.4	909.7	927.4	931.8
27.5°	856.5	872.8	887.5	909.7	912.6
30°	827.0	846.2	865.4	889.0	893.4
32.5°	794.5	816.6	840.3	868.3	877.2
35°	763.5	788.6	816.6	849.1	859.5
37.5°	729.5	757.6	793.0	828.5	838.8
40°	695.6	728.0	767.9	806.3	819.6
42.5°	663.1	695.6	742.8	785.6	798.9
45°	626.1	666.0	717.7	763.5	778.3
47.5°	590.7	633.5	692.6	739.9	756.1
50°	553.8	599.6	666.0	716.2	732.5
52.5°	518.3	567.1	638.0	689.6	707.4
55°	479.9	533.1	609.9	663.1	682.3
57.5°	443.0	502.1	578.9	636.5	655.7
60°	403.2	466.7	550.8	606.9	627.6
62.5°	367.7	434.2	518.3	578.9	598.1
65°	327.8	400.2	487.3	547.9	567.1
67.5°	292.4	367.7	456.3	516.9	537.5
70°	254.0	330.8	422.4	485.9	503.6
72.5°	218.6	298.3	391.3	453.4	475.5
75°	181.6	264.3	358.9	422.4	441.6
77.5°	146.2	231.9	327.8	391.3	412.0
80°	110.8	200.8	296.8	358.9	379.5
82.5°	81.2	169.8	267.3	329.3	348.5
85°	53.2	144.7	239.2	301.3	321.9
87.5°	32.5	121.1	215.6	276.2	295.4
90°	15.3	106.4	205.0	266.6	285.3
92.5°	25.9	102.2	193.7	252.3	270.6
95°	44.5	97.3	189.4	248.0	265.3
97.5°	69.1	91.4	185.1	241.2	259.5
100°	99.3	85.1	176.4	235.0	252.3
102.5°	131.1	178.8	167.0	225.7	243.4
105°	160.2	218.1	157.7	214.9	233.1
107.5°	195.9	243.9	148.4	204.1	222.3
110°	228.6	268.7	195.8	192.8	211.0

TEST NUMBER: P1007958

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.8	293.4	352.9	183.4	201.2
115°	295.0	319.8	398.8	210.3	190.4
117.5°	323.1	345.0	415.6	388.0	271.0
120°	356.3	369.7	437.9	485.3	433.7
122.5°	384.5	394.0	458.7	501.6	515.4
125°	411.7	418.2	475.0	518.4	533.2
127.5°	437.9	443.4	490.7	532.8	546.6
130°	462.5	469.0	505.6	546.5	557.8
132.5°	487.6	492.7	520.3	558.8	570.1
135°	507.2	515.3	534.5	570.6	581.4
137.5°	529.4	535.4	547.8	580.8	589.7
140°	551.0	553.5	562.0	590.1	596.4
142.5°	569.1	571.1	577.6	599.3	604.2
145°	586.7	586.2	594.7	607.1	611.9
147.5°	603.3	601.8	610.3	614.3	616.7
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)