

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001278

Luminaire Tested: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001278
REPORT IS A COMBINATION OF REPORTS P995897 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2646.0 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001278

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001278

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50
2	90	82	76	71	83	76	71	66	66	61	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	36	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4509	4509	4509
5°	4512	4379	4384
10°	4474	4257	4227
15°	4409	4112	4050
20°	4327	3956	3867
25°	4235	3791	3671
30°	4124	3612	3454
35°	4009	3430	3245
40°	3889	3233	3023
45°	3763	3036	2815
50°	3623	2844	2585
55°	3472	2621	2356
60°	3317	2376	2118
65°	3139	2124	1849
70°	2936	1819	1563
75°	2631	1466	1251
80°	2242	1061	879
85°	1739	589	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3763 cd/sqm

TEST NUMBER: P1001278

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	2.0
10°-20°	146.8	5.5
20°-30°	216.1	8.2
30°-40°	251.2	9.5
40°-50°	251.1	9.5
50°-60°	219.6	8.3
60°-70°	163.1	6.2
70°-80°	92.5	3.5
80°-90°	27.4	1.0
90°-100°	28.8	1.1
100°-110°	86.3	3.3
110°-120°	146.5	5.5
120°-130°	193.3	7.3
130°-140°	217.1	8.2
140°-150°	213.4	8.1
150°-160°	179.5	6.8
160°-170°	119.4	4.5
170°-180°	41.8	1.6
0°-30°	415.0	15.7
0°-40°	666.1	25.2
0°-60°	1136.9	43.0
0°-90°	1420.0	53.7
90°-120°	261.6	9.9
90°-150°	885.4	33.5
90°-180°	1226.0	46.3
0°-180°	2646.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	553	553	553	553	553	
5°	552	551	546	551	550	52
15°	526	524	517	520	519	148
25°	476	473	467	467	466	219
35°	410	407	400	397	395	256
45°	334	331	324	319	318	258
55°	253	252	245	240	237	227
65°	171	169	165	160	158	170
75°	91	89	87	85	85	97
85°	24	24	23	23	23	26
90°	1	5	8	10	10	3
95°	20	24	26	27	27	22
105°	80	80	81	82	83	84
115°	149	149	148	148	148	147
125°	217	217	217	216	215	193
135°	280	282	282	281	280	217
145°	340	341	342	341	340	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1001278

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	552.9	552.9	552.9	552.9	552.9
2.5°	554.6	553.3	548.4	552.9	552.4
5°	552.4	550.6	545.8	550.6	549.8
7.5°	548.4	546.6	541.3	545.3	544.9
10°	542.7	540.9	535.1	538.7	537.8
12.5°	535.1	533.4	527.2	531.1	529.8
15°	525.8	524.1	517.4	520.1	518.7
17.5°	515.2	513.0	506.8	508.6	507.7
20°	503.2	501.0	494.4	495.7	494.8
22.5°	490.4	487.3	480.6	483.3	481.5
25°	476.2	473.1	466.9	467.4	465.6
27.5°	460.3	457.2	451.4	450.5	448.3
30°	444.3	440.8	435.0	433.2	431.0
32.5°	427.5	424.4	418.2	416.0	413.8
35°	409.8	406.7	400.5	397.4	395.1
37.5°	391.2	388.5	381.9	378.8	375.7
40°	373.0	369.5	362.8	358.4	356.2
42.5°	353.5	351.7	344.2	338.9	337.6
45°	334.5	331.4	324.3	319.4	318.1
47.5°	314.5	312.3	305.7	300.3	296.8
50°	294.1	292.4	286.2	280.0	277.3
52.5°	274.2	272.0	265.4	260.0	256.5
55°	252.9	251.6	245.4	240.1	237.4
57.5°	233.0	231.7	225.5	220.2	217.5
60°	212.2	210.0	204.2	200.2	198.0
62.5°	191.8	190.0	183.8	180.3	178.1
65°	171.4	169.2	164.8	160.4	158.1
67.5°	150.6	148.8	144.4	140.0	139.5
70°	131.6	128.5	124.9	121.4	120.1
72.5°	111.2	108.1	105.4	102.8	101.4
75°	91.3	89.0	86.8	85.1	84.6
77.5°	71.8	70.9	68.7	68.2	66.9
80°	54.5	53.2	52.3	51.4	50.9
82.5°	37.7	37.2	37.2	36.8	36.3
85°	23.9	23.9	23.0	23.0	22.6
87.5°	11.5	11.1	10.6	10.6	10.6
90°	1.0	4.8	7.5	9.6	10.3
92.5°	8.9	13.3	15.0	16.1	16.4
95°	20.5	23.6	26.0	27.0	27.0
97.5°	32.8	35.5	38.3	39.6	39.6
100°	47.8	49.2	52.3	53.0	53.0
102.5°	63.6	63.9	66.6	67.7	68.0
105°	79.6	80.0	81.3	82.4	83.4
107.5°	96.4	96.7	97.1	98.4	98.1
110°	113.5	114.1	113.8	113.1	114.1



TEST NUMBER: P1001278

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.2	131.2	130.5	130.5	130.5
115°	149.0	149.0	148.3	148.0	147.6
117.5°	165.7	165.7	165.4	164.4	163.4
120°	182.5	183.9	182.8	181.1	181.8
122.5°	199.9	200.3	199.9	198.9	197.2
125°	217.0	217.0	216.7	216.0	215.3
127.5°	232.4	233.4	232.7	232.0	231.7
130°	248.8	249.8	249.8	249.1	247.8
132.5°	265.5	266.2	265.9	265.2	264.9
135°	279.9	281.9	281.9	281.3	280.2
137.5°	296.0	297.0	297.7	296.6	297.0
140°	312.0	312.7	312.7	312.4	312.0
142.5°	326.7	327.4	327.1	327.1	327.1
145°	340.0	341.4	341.7	341.4	340.4
147.5°	353.7	355.4	355.1	354.7	354.4
150°	366.0	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)