

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007972

Luminaire Tested: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007972
REPORT IS A COMBINATION OF REPORTS P983715 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6837.1 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007972

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007972

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46
2	87	79	72	67	80	73	67	62	62	58	54	52	48	45	42	40	38
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31
4	72	61	52	46	66	56	49	43	48	42	37	40	36	32	33	29	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16681	16681	16681
5°	16757	15969	15880
10°	16645	15416	15191
15°	16409	14845	14486
20°	16112	14243	13816
25°	15821	13668	13209
30°	15411	13083	12607
35°	14996	12520	12166
40°	14558	12033	11726
45°	14144	11591	11345
50°	13695	11183	10966
55°	13227	10751	10583
60°	12651	10300	10179
65°	12055	9782	9714
70°	11377	9225	9213
75°	10511	8668	8741
80°	9141	8090	8252
85°	7769	7544	7828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14144 cd/sqm

TEST NUMBER: P1007972

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.5
10°-20°	286.5	4.2
20°-30°	434.1	6.3
30°-40°	528.7	7.7
40°-50°	568.8	8.3
50°-60°	552.4	8.1
60°-70°	482.4	7.1
70°-80°	371.3	5.4
80°-90°	250.4	3.7
90°-100°	203.2	3.0
100°-110°	243.3	3.6
110°-120°	395.7	5.8
120°-130°	565.2	8.3
130°-140°	570.7	8.3
140°-150°	515.7	7.5
150°-160°	412.0	6.0
160°-170°	265.5	3.9
170°-180°	91.4	1.3
0°-30°	820.6	12.0
0°-40°	1349.2	19.7
0°-60°	2470.4	36.1
0°-90°	3574.4	52.3
90°-120°	842.2	12.3
90°-150°	2493.8	36.5
90°-180°	3263.0	47.7
0°-180°	6837.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1052	1043	1052	1051	100
15°	1008	1011	1011	1025	1023	284
25°	916	927	941	959	964	421
35°	790	816	845	878	889	494
45°	648	689	742	790	805	500
55°	496	551	631	686	706	444
65°	339	414	504	567	586	337
75°	188	273	371	437	457	199
85°	55	150	247	312	333	58
90°	16	112	216	280	300	13
95°	57	106	203	264	282	63
105°	219	284	174	235	254	234
115°	406	434	520	244	211	399
125°	568	577	639	685	701	507
135°	700	711	733	772	783	541
145°	811	810	822	836	840	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P1007972

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1053.8	1053.8	1053.8	1053.8	1053.8
2.5°	1061.5	1056.9	1046.2	1053.8	1050.8
5°	1056.9	1052.3	1043.1	1052.3	1050.8
7.5°	1049.2	1046.2	1038.5	1049.2	1047.7
10°	1040.1	1037.0	1032.4	1044.7	1043.1
12.5°	1024.8	1026.3	1023.3	1035.5	1034.0
15°	1008.0	1011.1	1011.1	1024.8	1023.3
17.5°	986.6	992.7	997.3	1011.1	1011.1
20°	965.2	972.9	979.0	995.8	995.8
22.5°	942.3	951.5	960.7	977.5	980.5
25°	916.4	927.1	940.8	959.1	963.7
27.5°	885.8	902.6	917.9	940.8	943.9
30°	855.3	875.1	895.0	919.4	924.0
32.5°	821.7	844.6	869.0	898.0	907.2
35°	789.6	815.6	844.6	878.2	888.9
37.5°	754.5	783.5	820.1	856.8	867.5
40°	719.3	752.9	794.2	833.9	847.6
42.5°	685.7	719.3	768.2	812.5	826.3
45°	647.6	688.8	742.3	789.6	804.9
47.5°	610.9	655.2	716.3	765.2	782.0
50°	572.7	620.1	688.8	740.7	757.5
52.5°	536.1	586.5	659.8	713.2	731.6
55°	496.4	551.3	630.8	685.7	705.6
57.5°	458.2	519.3	598.7	658.3	678.1
60°	416.9	482.6	569.7	627.7	649.1
62.5°	380.3	449.0	536.1	598.7	618.5
65°	339.1	413.9	504.0	566.6	586.5
67.5°	302.4	380.3	471.9	534.5	555.9
70°	262.7	342.1	436.8	502.5	520.8
72.5°	226.0	308.5	404.7	468.9	491.8
75°	187.9	273.4	371.1	436.8	456.7
77.5°	151.2	239.8	339.1	404.7	426.1
80°	114.5	207.7	307.0	371.1	392.5
82.5°	84.0	175.6	276.4	340.6	360.4
85°	55.0	149.7	247.4	311.6	332.9
87.5°	33.6	125.2	223.0	285.6	305.5
90°	16.0	112.2	215.5	280.1	299.8
92.5°	31.1	109.3	204.6	265.5	284.5
95°	57.4	106.2	202.7	264.3	281.9
97.5°	92.0	100.7	200.3	259.0	278.0
100°	133.6	95.0	192.3	254.4	272.5
102.5°	178.0	227.0	183.0	245.6	264.5
105°	218.8	283.9	173.7	234.8	254.4
107.5°	268.1	322.2	164.5	224.0	243.6
110°	313.8	359.0	233.1	212.5	232.1

TEST NUMBER: P1007972

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	358.3	395.2	453.7	203.2	222.1
115°	405.5	434.1	520.2	244.5	211.3
117.5°	445.0	471.1	547.0	493.6	326.8
120°	490.8	507.4	581.0	632.0	555.0
122.5°	529.7	542.4	612.7	658.2	672.6
125°	567.8	576.9	638.9	685.0	700.8
127.5°	604.0	612.1	663.8	708.8	723.3
130°	638.0	647.5	687.2	731.6	743.1
132.5°	672.7	680.2	710.7	752.1	763.6
135°	700.3	711.4	733.0	772.0	782.8
137.5°	730.9	739.2	753.8	789.8	798.4
140°	760.7	764.8	775.5	806.2	811.9
142.5°	785.7	789.1	798.1	822.0	826.2
145°	810.6	809.9	821.7	835.8	839.9
147.5°	833.6	831.5	843.3	848.3	850.1
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)