

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007973

Luminaire Tested: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007973
REPORT IS A COMBINATION OF REPORTS P983716 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6611.0 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007973

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007973

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46
2	87	79	72	67	80	73	67	62	62	58	54	52	48	45	42	40	38
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31
4	72	61	52	46	66	56	49	43	48	42	37	40	36	32	33	29	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16130	16130	16130
5°	16202	15441	15354
10°	16094	14906	14688
15°	15867	14353	14006
20°	15580	13772	13358
25°	15298	13216	12771
30°	14901	12651	12190
35°	14500	12105	11764
40°	14078	11634	11339
45°	13674	11207	10970
50°	13243	10813	10604
55°	12787	10395	10233
60°	12235	9958	9842
65°	11653	9457	9392
70°	11000	8921	8909
75°	10159	8383	8452
80°	8846	7821	7978
85°	7515	7294	7570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13674 cd/sqm

TEST NUMBER: P1007973

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.5
10°-20°	277.0	4.2
20°-30°	419.8	6.3
30°-40°	511.2	7.7
40°-50°	550.0	8.3
50°-60°	534.1	8.1
60°-70°	466.4	7.1
70°-80°	359.0	5.4
80°-90°	242.1	3.7
90°-100°	196.5	3.0
100°-110°	235.2	3.6
110°-120°	382.6	5.8
120°-130°	546.5	8.3
130°-140°	551.9	8.3
140°-150°	498.7	7.5
150°-160°	398.4	6.0
160°-170°	256.7	3.9
170°-180°	88.4	1.3
0°-30°	793.4	12.0
0°-40°	1304.6	19.7
0°-60°	2388.7	36.1
0°-90°	3456.2	52.3
90°-120°	814.3	12.3
90°-150°	2411.4	36.5
90°-180°	3155.0	47.7
0°-180°	6611.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1019	1019	1019	1019	1019	
5°	1022	1018	1009	1018	1016	97
15°	975	978	978	991	989	275
25°	886	896	910	927	932	407
35°	764	789	817	849	860	477
45°	626	666	718	764	778	483
55°	480	533	610	663	682	429
65°	328	400	487	548	567	326
75°	182	264	359	422	442	192
85°	53	145	239	301	322	56
90°	16	108	208	271	290	13
95°	56	103	196	256	273	61
105°	212	274	168	227	246	227
115°	392	420	503	236	204	385
125°	549	558	618	662	678	490
135°	677	688	709	746	757	524
145°	784	783	795	808	812	491
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P1007973

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1019.0	1019.0	1019.0	1019.0	1019.0
2.5°	1026.3	1021.9	1011.6	1019.0	1016.0
5°	1021.9	1017.5	1008.6	1017.5	1016.0
7.5°	1014.5	1011.6	1004.2	1014.5	1013.1
10°	1005.7	1002.7	998.3	1010.1	1008.6
12.5°	990.9	992.4	989.4	1001.2	999.8
15°	974.7	977.6	977.6	990.9	989.4
17.5°	954.0	959.9	964.3	977.6	977.6
20°	933.3	940.7	946.6	962.8	962.8
22.5°	911.2	920.0	928.9	945.1	948.1
25°	886.1	896.4	909.7	927.4	931.8
27.5°	856.5	872.8	887.5	909.7	912.6
30°	827.0	846.2	865.4	889.0	893.4
32.5°	794.5	816.6	840.3	868.3	877.2
35°	763.5	788.6	816.6	849.1	859.5
37.5°	729.5	757.6	793.0	828.5	838.8
40°	695.6	728.0	767.9	806.3	819.6
42.5°	663.1	695.6	742.8	785.6	798.9
45°	626.1	666.0	717.7	763.5	778.3
47.5°	590.7	633.5	692.6	739.9	756.1
50°	553.8	599.6	666.0	716.2	732.5
52.5°	518.3	567.1	638.0	689.6	707.4
55°	479.9	533.1	609.9	663.1	682.3
57.5°	443.0	502.1	578.9	636.5	655.7
60°	403.2	466.7	550.8	606.9	627.6
62.5°	367.7	434.2	518.3	578.9	598.1
65°	327.8	400.2	487.3	547.9	567.1
67.5°	292.4	367.7	456.3	516.9	537.5
70°	254.0	330.8	422.4	485.9	503.6
72.5°	218.6	298.3	391.3	453.4	475.5
75°	181.6	264.3	358.9	422.4	441.6
77.5°	146.2	231.9	327.8	391.3	412.0
80°	110.8	200.8	296.8	358.9	379.5
82.5°	81.2	169.8	267.3	329.3	348.5
85°	53.2	144.7	239.2	301.3	321.9
87.5°	32.5	121.1	215.6	276.2	295.4
90°	15.5	108.5	208.3	270.8	289.8
92.5°	30.1	105.7	197.7	256.7	275.1
95°	55.5	102.7	196.0	255.5	272.6
97.5°	88.9	97.3	193.8	250.4	268.8
100°	129.2	91.9	186.0	246.0	263.6
102.5°	172.1	219.5	176.9	237.5	255.7
105°	211.6	274.5	168.0	227.1	245.9
107.5°	259.3	311.5	159.0	216.6	235.5
110°	303.5	347.1	225.3	205.5	224.4

TEST NUMBER: P1007973

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.4	382.1	438.7	196.4	214.7
115°	392.1	419.8	503.0	236.3	204.3
117.5°	430.2	455.5	529.0	477.3	316.0
120°	474.6	490.6	561.7	611.2	536.7
122.5°	512.2	524.4	592.5	636.4	650.4
125°	549.1	557.8	617.8	662.4	677.7
127.5°	584.0	591.9	641.8	685.5	699.5
130°	616.9	626.2	664.6	707.3	718.5
132.5°	650.5	657.7	687.2	727.3	738.4
135°	677.2	688.0	708.7	746.5	757.0
137.5°	706.8	714.8	728.9	763.7	772.1
140°	735.7	739.5	749.9	779.6	785.0
142.5°	759.8	763.0	771.8	794.8	798.9
145°	783.9	783.2	794.6	808.2	812.1
147.5°	806.0	804.0	815.4	820.3	822.0
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)