

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007976

Luminaire Tested: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007976
REPORT IS A COMBINATION OF REPORTS P983719 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6925.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007976

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007976

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25392	25392	25392
5°	25433	24202	24031
10°	25225	23099	22641
15°	24856	21987	21179
20°	24357	20779	19795
25°	23859	19517	18413
30°	23232	18330	16963
35°	22644	17079	15537
40°	21913	15843	14190
45°	21189	14619	12870
50°	20396	13372	11499
55°	19564	12039	10202
60°	18629	10597	8852
65°	17601	9129	7433
70°	16296	7525	6002
75°	14494	5800	4636
80°	12311	3942	2983
85°	8927	1836	1270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21189 cd/sqm

TEST NUMBER: P1007976

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	2.2
10°-20°	424.8	6.1
20°-30°	624.2	9.0
30°-40°	725.0	10.5
40°-50°	724.1	10.5
50°-60°	631.4	9.1
60°-70°	466.7	6.7
70°-80°	264.1	3.8
80°-90°	71.4	1.0
90°-100°	32.0	0.5
100°-110°	119.2	1.7
110°-120°	316.1	4.6
120°-130°	524.2	7.6
130°-140°	556.8	8.0
140°-150°	517.5	7.5
150°-160°	416.1	6.0
160°-170°	268.1	3.9
170°-180°	92.3	1.3
0°-30°	1200.0	17.3
0°-40°	1925.0	27.8
0°-60°	3280.5	47.4
0°-90°	4082.7	59.0
90°-120°	467.2	6.7
90°-150°	2065.8	29.8
90°-180°	2842.0	41.0
0°-180°	6925.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1581	1593	1590	152
15°	1527	1518	1498	1504	1496	430
25°	1382	1370	1343	1346	1343	636
35°	1192	1177	1152	1143	1135	745
45°	970	959	936	919	913	749
55°	734	725	706	688	680	656
65°	495	486	470	456	449	490
75°	259	256	248	239	242	277
85°	63	62	60	56	54	70
90°	1	8	14	18	19	6
95°	46	22	27	31	30	54
105°	213	234	43	50	53	228
115°	403	415	433	108	58	397
125°	570	580	593	598	600	509
135°	706	717	723	730	729	545
145°	819	818	830	835	831	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P1007976

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1613.3	1605.6	1588.6	1604.1	1601.0
5°	1604.1	1597.9	1580.9	1593.3	1590.2
7.5°	1593.3	1584.0	1567.0	1579.4	1576.3
10°	1576.3	1565.5	1547.0	1559.3	1554.7
12.5°	1553.2	1543.9	1525.4	1533.1	1530.0
15°	1526.9	1517.7	1497.6	1503.8	1496.1
17.5°	1494.6	1485.3	1465.3	1473.0	1465.3
20°	1459.1	1449.8	1428.2	1432.9	1426.7
22.5°	1423.6	1409.7	1389.7	1389.7	1386.6
25°	1382.0	1369.6	1343.4	1346.5	1343.4
27.5°	1335.7	1324.9	1304.8	1300.2	1292.5
30°	1289.4	1277.1	1253.9	1249.3	1243.2
32.5°	1240.1	1230.8	1206.1	1196.9	1190.7
35°	1192.3	1176.8	1152.2	1142.9	1135.2
37.5°	1138.3	1124.4	1099.7	1088.9	1081.2
40°	1082.7	1070.4	1045.7	1031.8	1025.7
42.5°	1028.8	1016.4	991.7	976.3	967.1
45°	970.2	959.4	936.2	919.3	913.1
47.5°	913.1	902.3	877.6	860.6	851.4
50°	852.9	845.2	823.6	802.0	794.3
52.5°	794.3	783.5	763.5	746.5	735.7
55°	734.2	724.9	706.4	687.9	680.2
57.5°	674.0	666.3	646.3	627.7	621.6
60°	613.9	607.7	586.1	569.1	564.5
62.5°	555.3	544.5	529.0	513.6	507.4
65°	495.1	485.8	470.4	456.5	448.8
67.5°	433.4	425.7	411.8	401.0	394.8
70°	376.3	370.2	356.3	345.5	339.3
72.5°	317.7	311.6	303.8	293.1	288.4
75°	259.1	256.0	248.3	239.1	242.2
77.5°	206.7	200.5	197.4	192.8	188.2
80°	154.2	152.7	149.6	145.0	141.9
82.5°	104.9	104.9	103.3	97.2	97.2
85°	63.2	61.7	60.2	55.5	54.0
87.5°	27.8	24.7	21.6	17.0	15.4
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.6	22.4	27.4	30.9	30.2
97.5°	82.1	24.6	35.8	37.9	38.6
100°	124.2	28.1	40.0	45.6	47.0
102.5°	170.5	169.1	41.4	49.1	51.2
105°	213.3	234.3	42.8	50.5	53.3
107.5°	263.1	280.6	44.2	51.9	54.7
110°	310.8	325.5	122.8	52.6	55.4



TEST NUMBER: P1007976

CATALOG NUMBER: S122DIP-B1005D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.7	368.3	356.4	54.0	56.1
115°	403.4	415.3	432.8	108.0	57.5
117.5°	444.8	458.8	470.7	370.4	186.6
120°	491.1	501.6	514.2	522.6	427.9
122.5°	530.4	541.6	555.6	559.8	560.5
125°	570.3	579.5	592.8	597.7	599.8
127.5°	606.8	616.6	627.2	634.2	634.9
130°	641.2	652.4	660.1	667.9	667.2
132.5°	676.3	685.4	693.1	699.4	698.7
135°	705.7	717.0	723.3	730.3	728.9
137.5°	736.6	745.0	752.0	759.1	757.0
140°	766.8	772.4	780.1	786.4	782.9
142.5°	792.0	796.9	806.1	811.7	808.2
145°	818.7	818.0	829.9	834.8	831.3
147.5°	841.8	839.7	851.7	855.2	852.4
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

(END OF REPORT)