

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007984

Luminaire Tested: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007984
REPORT IS A COMBINATION OF REPORTS P983772 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7643.0 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007984

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007984

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	96	91	86	82	87	83	79	76	69	67	64	56	54	53	45	43	42			36
2	86	78	72	66	79	72	66	61	60	56	52	49	46	43	38	36	34			29
3	79	68	61	54	72	63	56	51	52	47	43	43	39	36	34	31	29			24
4	72	60	52	46	65	55	48	42	46	41	36	38	34	30	30	27	24			20
5	66	53	45	39	60	49	42	36	41	35	31	34	29	26	27	23	21			17
6	60	48	39	33	55	44	37	31	37	31	27	30	26	22	24	21	18			15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	19	16			13
8	52	39	31	26	47	36	29	24	30	25	21	25	21	17	20	17	14			12
9	48	35	28	23	44	33	26	21	28	22	18	23	19	16	19	15	13			11
10	45	32	25	20	41	30	23	19	26	20	16	21	17	14	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P1007984

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.3
10°-20°	285.7	3.7
20°-30°	432.8	5.7
30°-40°	527.1	6.9
40°-50°	567.1	7.4
50°-60°	550.7	7.2
60°-70°	481.0	6.3
70°-80°	370.2	4.8
80°-90°	250.1	3.3
90°-100°	211.9	2.8
100°-110°	277.2	3.6
110°-120°	486.3	6.4
120°-130°	715.8	9.4
130°-140°	730.8	9.6
140°-150°	664.5	8.7
150°-160°	531.6	7.0
160°-170°	342.6	4.5
170°-180°	117.9	1.5
0°-30°	818.1	10.7
0°-40°	1345.2	17.6
0°-60°	2463.0	32.2
0°-90°	3564.3	46.6
90°-120°	975.4	12.8
90°-150°	3086.6	40.4
90°-180°	4079.0	53.4
0°-180°	7643.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	114	219	284	304	14
95°	70	112	210	272	290	79
105°	280	351	186	249	269	300
115°	522	554	644	275	227	513
125°	732	743	809	857	873	653
135°	903	918	941	982	992	698
145°	1046	1045	1060	1076	1079	655
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1007984

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	16.1	114.3	218.9	284.3	304.4
92.5°	36.1	113.2	208.8	270.0	289.2
95°	70.5	112.4	210.1	272.4	289.7
97.5°	115.6	107.5	210.2	269.2	288.4
100°	169.4	102.9	203.4	266.9	285.5
102.5°	226.9	275.4	194.5	259.1	278.6
105°	280.1	351.2	185.7	248.7	269.1
107.5°	343.8	402.8	176.8	238.4	258.7
110°	403.2	452.4	268.1	227.1	247.4

TEST NUMBER: P1007984

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.6	501.1	555.9	218.2	237.7
115°	521.5	553.5	644.5	275.0	227.3
117.5°	572.9	602.9	682.2	599.7	380.0
120°	632.1	651.6	728.7	782.0	677.8
122.5°	682.3	698.1	772.4	818.8	833.4
125°	731.8	743.4	809.3	856.6	873.0
127.5°	778.4	789.4	844.0	891.1	905.6
130°	822.3	835.2	877.0	923.4	934.7
132.5°	867.1	877.3	910.0	953.1	964.4
135°	903.3	917.6	940.9	981.9	992.3
137.5°	942.7	953.5	970.0	1008.0	1015.9
140°	981.3	986.9	999.8	1032.3	1036.9
142.5°	1013.5	1018.3	1030.0	1055.4	1058.6
145°	1046.1	1045.2	1060.4	1075.8	1078.9
147.5°	1075.7	1073.0	1088.2	1094.2	1095.2
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)