

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008047

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008047
REPORT IS A COMBINATION OF REPORTS P984015 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3974.1 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008047

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008047

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	87	83	79	81	78	74	71	60	58	56	44	42	41	29	28	27
2	83	76	69	64	74	67	62	58	52	48	45	38	36	34	25	23	22
3	76	66	59	53	67	59	53	48	46	41	38	33	30	28	22	20	19
4	69	58	50	44	61	52	45	40	40	36	32	29	26	24	19	17	16
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	14
6	58	46	38	32	51	41	34	29	32	27	23	24	20	18	16	13	12
7	53	41	34	28	47	37	30	25	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	33	27	22	26	21	18	19	16	14	13	11	9
9	46	34	27	22	41	30	24	20	24	19	16	18	14	12	12	10	8
10	43	31	24	19	38	28	22	17	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4804	4804	4804
5°	4826	4599	4573
10°	4793	4439	4375
15°	4726	4275	4172
20°	4641	4101	3979
25°	4556	3936	3803
30°	4438	3767	3631
35°	4319	3605	3504
40°	4194	3465	3377
45°	4073	3338	3267
50°	3943	3221	3159
55°	3808	3097	3048
60°	3644	2967	2931
65°	3470	2816	2797
70°	3278	2657	2654
75°	3026	2497	2517
80°	2635	2330	2376
85°	2232	2174	2255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4073 cd/sqm

TEST NUMBER: P1008047

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	0.7
10°-20°	82.5	2.1
20°-30°	125.0	3.1
30°-40°	152.2	3.8
40°-50°	163.8	4.1
50°-60°	159.1	4.0
60°-70°	138.9	3.5
70°-80°	106.9	2.7
80°-90°	73.3	1.8
90°-100°	81.1	2.0
100°-110°	154.1	3.9
110°-120°	336.8	8.5
120°-130°	532.3	13.4
130°-140°	556.9	14.0
140°-150°	513.4	12.9
150°-160°	412.0	10.4
160°-170°	265.5	6.7
170°-180°	91.4	2.3
0°-30°	236.3	5.9
0°-40°	388.5	9.8
0°-60°	711.5	17.9
0°-90°	1030.6	25.9
90°-120°	572.0	14.4
90°-150°	2174.6	54.7
90°-180°	2943.0	74.1
0°-180°	3974.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	304	304	304	304	304	
5°	304	303	300	303	303	29
15°	290	291	291	295	295	82
25°	264	267	271	276	278	121
35°	227	235	243	253	256	142
45°	186	198	214	227	232	144
55°	143	159	182	198	203	128
65°	98	119	145	163	169	97
75°	54	79	107	126	132	57
85°	16	43	71	90	96	17
90°	5	38	72	93	100	6
95°	49	46	78	98	102	56
105°	213	247	80	103	111	228
115°	401	418	455	147	101	395
125°	566	575	602	619	625	505
135°	699	710	721	737	739	540
145°	811	810	822	829	828	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P1008047

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	303.5	303.5	303.5	303.5	303.5
2.5°	305.7	304.4	301.3	303.5	302.6
5°	304.4	303.0	300.4	303.0	302.6
7.5°	302.2	301.3	299.1	302.2	301.7
10°	299.5	298.6	297.3	300.8	300.4
12.5°	295.1	295.6	294.7	298.2	297.8
15°	290.3	291.2	291.2	295.1	294.7
17.5°	284.1	285.9	287.2	291.2	291.2
20°	278.0	280.2	281.9	286.8	286.8
22.5°	271.4	274.0	276.7	281.5	282.4
25°	263.9	267.0	270.9	276.2	277.5
27.5°	255.1	259.9	264.3	270.9	271.8
30°	246.3	252.0	257.7	264.8	266.1
32.5°	236.6	243.2	250.3	258.6	261.3
35°	227.4	234.9	243.2	252.9	256.0
37.5°	217.3	225.6	236.2	246.7	249.8
40°	207.2	216.8	228.7	240.2	244.1
42.5°	197.5	207.2	221.2	234.0	238.0
45°	186.5	198.4	213.8	227.4	231.8
47.5°	175.9	188.7	206.3	220.4	225.2
50°	164.9	178.6	198.4	213.3	218.2
52.5°	154.4	168.9	190.0	205.4	210.7
55°	142.9	158.8	181.7	197.5	203.2
57.5°	132.0	149.5	172.4	189.6	195.3
60°	120.1	139.0	164.1	180.8	186.9
62.5°	109.5	129.3	154.4	172.4	178.1
65°	97.6	119.2	145.1	163.2	168.9
67.5°	87.1	109.5	135.9	153.9	160.1
70°	75.7	98.5	125.8	144.7	150.0
72.5°	65.1	88.8	116.6	135.0	141.6
75°	54.1	78.7	106.9	125.8	131.5
77.5°	43.5	69.1	97.6	116.6	122.7
80°	33.0	59.8	88.4	106.9	113.0
82.5°	24.2	50.6	79.6	98.1	103.8
85°	15.8	43.1	71.3	89.7	95.9
87.5°	9.7	36.1	64.2	82.2	88.0
90°	5.1	38.2	72.0	93.1	99.7
92.5°	21.4	41.9	70.8	89.4	95.3
95°	48.7	46.4	77.7	97.9	102.5
97.5°	84.4	46.3	82.9	101.3	107.3
100°	126.0	47.2	83.6	105.5	111.6
102.5°	171.4	184.6	81.9	105.3	112.3
105°	213.4	247.0	80.2	103.2	110.9
107.5°	262.7	290.7	78.5	101.1	108.7
110°	309.5	332.9	153.7	98.3	105.9

TEST NUMBER: P1008047

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.0	373.5	381.9	96.6	103.5
115°	401.2	417.8	455.0	146.6	101.4
117.5°	441.7	459.1	489.4	403.3	225.7
120°	487.5	499.8	529.9	550.5	461.5
122.5°	526.4	538.1	568.1	584.2	588.9
125°	565.6	574.7	602.0	618.6	624.7
127.5°	601.8	611.0	633.3	651.2	655.9
130°	635.8	646.4	663.3	681.5	684.4
132.5°	670.5	679.1	693.3	709.7	712.5
135°	699.2	710.3	721.0	737.2	739.3
137.5°	729.8	738.1	747.2	762.6	763.6
140°	759.6	764.8	773.3	786.6	785.8
142.5°	784.6	789.1	798.1	809.0	807.7
145°	810.6	809.9	821.7	829.2	827.9
147.5°	833.6	831.5	843.3	847.2	845.8
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)