

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008050

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008050
REPORT IS A COMBINATION OF REPORTS P984018 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4002.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008050

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008050

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	77	68	61	56	69	61	55	51	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	54	46	40	58	48	42	36	38	33	30	29	26	23	20	18	17
6	60	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7280	7280	7280
5°	7292	6938	6890
10°	7232	6622	6491
15°	7127	6304	6072
20°	6983	5958	5675
25°	6840	5595	5278
30°	6661	5255	4863
35°	6491	4896	4455
40°	6282	4542	4069
45°	6074	4191	3690
50°	5847	3833	3296
55°	5609	3451	2925
60°	5341	3037	2537
65°	5044	2618	2132
70°	4673	2156	1721
75°	4156	1663	1328
80°	3529	1131	856
85°	2557	524	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6074 cd/sqm

TEST NUMBER: P1008050

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	1.1
10°-20°	121.8	3.0
20°-30°	179.0	4.5
30°-40°	207.9	5.2
40°-50°	207.6	5.2
50°-60°	181.0	4.5
60°-70°	133.8	3.3
70°-80°	75.7	1.9
80°-90°	21.7	0.5
90°-100°	31.8	0.8
100°-110°	118.7	3.0
110°-120°	314.7	7.9
120°-130°	522.0	13.0
130°-140°	554.5	13.9
140°-150°	515.4	12.9
150°-160°	414.3	10.4
160°-170°	267.0	6.7
170°-180°	91.9	2.3
0°-30°	344.0	8.6
0°-40°	551.9	13.8
0°-60°	940.5	23.5
0°-90°	1171.7	29.3
90°-120°	465.3	11.6
90°-150°	2057.1	51.4
90°-180°	2830.0	70.7
0°-180°	4002.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	460	458	453	457	456	44
15°	438	435	429	431	429	123
25°	396	393	385	386	385	182
35°	342	337	330	328	326	213
45°	278	275	268	264	262	215
55°	210	208	202	197	195	188
65°	142	139	135	131	129	140
75°	74	73	71	68	69	79
85°	18	18	17	16	16	20
90°	1	8	14	18	19	4
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008050

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.9	459.9	459.9	459.9	459.9
2.5°	462.5	460.3	455.5	459.9	459.0
5°	459.9	458.1	453.2	456.8	455.9
7.5°	456.8	454.1	449.3	452.8	451.9
10°	451.9	448.8	443.5	447.1	445.7
12.5°	445.3	442.6	437.3	439.5	438.7
15°	437.8	435.1	429.4	431.1	428.9
17.5°	428.5	425.8	420.1	422.3	420.1
20°	418.3	415.7	409.5	410.8	409.0
22.5°	408.1	404.2	398.4	398.4	397.5
25°	396.2	392.7	385.1	386.0	385.1
27.5°	382.9	379.8	374.1	372.8	370.6
30°	369.7	366.1	359.5	358.2	356.4
32.5°	355.5	352.9	345.8	343.1	341.4
35°	341.8	337.4	330.3	327.7	325.5
37.5°	326.3	322.4	315.3	312.2	310.0
40°	310.4	306.9	299.8	295.8	294.1
42.5°	294.9	291.4	284.3	279.9	277.3
45°	278.1	275.0	268.4	263.5	261.8
47.5°	261.8	258.7	251.6	246.7	244.1
50°	244.5	242.3	236.1	229.9	227.7
52.5°	227.7	224.6	218.9	214.0	210.9
55°	210.5	207.8	202.5	197.2	195.0
57.5°	193.2	191.0	185.3	180.0	178.2
60°	176.0	174.2	168.0	163.2	161.8
62.5°	159.2	156.1	151.7	147.2	145.5
65°	141.9	139.3	134.9	130.9	128.7
67.5°	124.3	122.0	118.1	115.0	113.2
70°	107.9	106.1	102.1	99.1	97.3
72.5°	91.1	89.3	87.1	84.0	82.7
75°	74.3	73.4	71.2	68.5	69.4
77.5°	59.3	57.5	56.6	55.3	53.9
80°	44.2	43.8	42.9	41.6	40.7
82.5°	30.1	30.1	29.6	27.9	27.9
85°	18.1	17.7	17.2	15.9	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P1008050

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)