

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001432

Luminaire Tested: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001432
REPORT IS A COMBINATION OF REPORTS P996051 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6155.3 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001432

CATALOG NUMBER: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001432

CATALOG NUMBER: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	34	34	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	29	29	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	25	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	27	24	24	21	19	19	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1001432

CATALOG NUMBER: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.5
10°-20°	256.8	4.2
20°-30°	377.9	6.1
30°-40°	439.3	7.1
40°-50°	439.3	7.1
50°-60°	384.2	6.2
60°-70°	285.2	4.6
70°-80°	161.8	2.6
80°-90°	48.3	0.8
90°-100°	373.7	6.1
100°-110°	760.0	12.3
110°-120°	677.5	11.0
120°-130°	569.1	9.2
130°-140°	474.9	7.7
140°-150°	362.7	5.9
150°-160°	254.9	4.1
160°-170°	149.9	2.4
170°-180°	48.8	0.8
0°-30°	725.8	11.8
0°-40°	1165.1	18.9
0°-60°	1988.6	32.3
0°-90°	2483.9	40.4
90°-120°	1811.2	29.4
90°-150°	3217.8	52.3
90°-180°	3671.0	59.6
0°-180°	6155.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	1	8	18	20	21	5
95°	33	103	806	399	241	36
105°	116	168	648	1396	1391	123
115°	204	255	578	1111	1335	202
125°	284	337	575	945	1066	253
135°	337	401	570	839	953	260
145°	388	445	567	708	778	244
155°	442	477	552	625	651	204
165°	481	496	529	560	568	136
175°	502	503	507	514	512	48
180°	503	503	503	503	503	

TEST NUMBER: P1001432

CATALOG NUMBER: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	1.0	7.9	17.8	19.8	20.8
92.5°	13.8	76.2	387.4	128.0	89.9
95°	32.6	102.8	805.5	398.8	241.2
97.5°	54.4	113.7	861.8	814.4	579.2
100°	75.1	128.5	794.6	1126.8	906.3
102.5°	94.9	146.3	710.6	1322.4	1191.0
105°	115.6	167.6	648.4	1396.0	1390.6
107.5°	138.4	189.2	607.8	1373.8	1485.5
110°	161.1	211.0	589.1	1294.8	1487.5

TEST NUMBER: P1001432

CATALOG NUMBER: SA4XXDIP-B575D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.8	232.8	580.2	1197.9	1429.2
115°	203.6	255.4	578.2	1111.0	1335.3
117.5°	225.3	276.8	577.2	1042.7	1243.4
120°	247.1	297.5	577.2	996.8	1168.2
122.5°	266.9	317.8	576.2	966.6	1108.9
125°	283.7	337.0	575.2	945.4	1065.5
127.5°	299.5	354.8	573.2	925.1	1037.8
130°	312.3	372.1	572.3	900.9	1014.1
132.5°	325.2	387.0	571.3	872.2	987.4
135°	337.0	401.2	570.3	839.1	952.8
137.5°	348.9	413.6	570.3	803.6	912.3
140°	361.7	425.0	569.3	769.0	867.8
142.5°	375.6	435.4	569.3	736.8	820.3
145°	388.4	444.8	567.3	707.6	777.8
147.5°	403.3	453.6	564.4	683.4	738.3
150°	417.1	462.0	561.4	661.2	705.7
152.5°	429.9	470.0	556.4	642.4	676.0
155°	441.8	476.9	551.5	624.7	651.3
157.5°	453.7	483.3	546.6	607.8	628.6
160°	464.5	488.8	540.6	591.0	607.8
162.5°	474.4	493.2	534.7	574.8	588.1
165°	481.3	496.2	528.8	559.9	568.3
167.5°	489.2	498.6	522.8	547.0	552.5
170°	494.2	500.6	516.9	534.2	537.7
172.5°	499.1	502.1	511.0	522.8	522.8
175°	502.1	503.1	507.0	513.9	512.0
177.5°	504.1	503.1	504.1	507.5	504.1
180°	503.1	503.1	503.1	503.1	503.1

(END OF REPORT)