

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008053

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008053
REPORT IS A COMBINATION OF REPORTS P984021 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3848.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008053

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008053

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	77	68	61	56	69	61	55	51	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	54	46	40	58	48	42	36	38	33	30	29	26	23	20	18	17
6	60	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7000	7000	7000
5°	7011	6672	6625
10°	6953	6368	6242
15°	6852	6062	5838
20°	6714	5728	5457
25°	6578	5380	5075
30°	6405	5054	4676
35°	6243	4708	4283
40°	6041	4368	3911
45°	5840	4030	3548
50°	5622	3686	3170
55°	5393	3318	2812
60°	5134	2922	2440
65°	4852	2517	2049
70°	4491	2074	1654
75°	3994	1600	1279
80°	3393	1086	822
85°	2458	506	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5840 cd/sqm

TEST NUMBER: P1008053

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.1
10°-20°	117.1	3.0
20°-30°	172.1	4.5
30°-40°	199.9	5.2
40°-50°	199.6	5.2
50°-60°	174.1	4.5
60°-70°	128.7	3.3
70°-80°	72.8	1.9
80°-90°	20.9	0.5
90°-100°	30.6	0.8
100°-110°	114.1	3.0
110°-120°	302.6	7.9
120°-130°	501.9	13.0
130°-140°	533.2	13.9
140°-150°	495.5	12.9
150°-160°	398.4	10.4
160°-170°	256.7	6.7
170°-180°	88.4	2.3
0°-30°	330.8	8.6
0°-40°	530.7	13.8
0°-60°	904.3	23.5
0°-90°	1126.6	29.3
90°-120°	447.3	11.6
90°-150°	1977.9	51.4
90°-180°	2721.0	70.7
0°-180°	3848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	439	438	42
15°	421	418	413	415	412	119
25°	381	378	370	371	370	175
35°	329	324	318	315	313	205
45°	267	264	258	253	252	206
55°	202	200	195	190	188	181
65°	136	134	130	126	124	135
75°	71	71	68	66	67	76
85°	17	17	17	15	15	19
90°	1	8	13	17	18	4
95°	44	22	26	30	29	52
105°	204	224	41	48	51	218
115°	386	398	414	103	55	380
125°	546	555	568	572	574	487
135°	676	686	692	699	698	522
145°	784	783	795	799	796	490
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P1008053

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	442.2	442.2	442.2	442.2	442.2
2.5°	444.7	442.6	437.9	442.2	441.3
5°	442.2	440.5	435.8	439.2	438.4
7.5°	439.2	436.7	432.0	435.4	434.5
10°	434.5	431.6	426.5	429.9	428.6
12.5°	428.2	425.6	420.5	422.6	421.8
15°	420.9	418.4	412.9	414.6	412.4
17.5°	412.0	409.5	403.9	406.0	403.9
20°	402.2	399.7	393.7	395.0	393.3
22.5°	392.4	388.6	383.1	383.1	382.2
25°	381.0	377.6	370.3	371.2	370.3
27.5°	368.2	365.2	359.7	358.4	356.3
30°	355.5	352.1	345.7	344.4	342.7
32.5°	341.8	339.3	332.5	329.9	328.2
35°	328.7	324.4	317.6	315.1	312.9
37.5°	313.8	310.0	303.2	300.2	298.1
40°	298.5	295.1	288.3	284.4	282.7
42.5°	283.6	280.2	273.4	269.1	266.6
45°	267.4	264.5	258.1	253.4	251.7
47.5°	251.7	248.7	241.9	237.3	234.7
50°	235.1	233.0	227.0	221.1	219.0
52.5°	219.0	216.0	210.5	205.8	202.8
55°	202.4	199.8	194.7	189.6	187.5
57.5°	185.8	183.7	178.2	173.0	171.3
60°	169.2	167.5	161.6	156.9	155.6
62.5°	153.1	150.1	145.8	141.6	139.9
65°	136.5	133.9	129.7	125.9	123.7
67.5°	119.5	117.4	113.5	110.5	108.8
70°	103.7	102.0	98.2	95.2	93.5
72.5°	87.6	85.9	83.8	80.8	79.5
75°	71.4	70.6	68.5	65.9	66.8
77.5°	57.0	55.3	54.4	53.1	51.9
80°	42.5	42.1	41.2	40.0	39.1
82.5°	28.9	28.9	28.5	26.8	26.8
85°	17.4	17.0	16.6	15.3	14.9
87.5°	7.7	6.8	6.0	4.7	4.3
90°	0.7	8.1	13.4	16.8	18.1
92.5°	16.8	14.1	16.1	17.5	18.1
95°	43.7	21.5	26.2	29.6	28.9
97.5°	78.6	23.5	34.3	36.3	36.9
100°	118.9	26.9	38.3	43.7	45.0
102.5°	163.2	161.9	39.6	47.0	49.0
105°	204.2	224.3	41.0	48.4	51.0
107.5°	251.9	268.7	42.3	49.7	52.4
110°	297.6	311.7	117.5	50.4	53.1



TEST NUMBER: P1008053

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	340.5	352.6	341.2	51.7	53.7
115°	386.2	397.6	414.4	103.4	55.1
117.5°	425.8	439.3	450.7	354.7	178.7
120°	470.2	480.3	492.3	500.4	409.7
122.5°	507.8	518.5	532.0	536.0	536.7
125°	546.1	554.8	567.6	572.3	574.3
127.5°	581.0	590.4	600.5	607.2	607.9
130°	613.9	624.7	632.1	639.4	638.8
132.5°	647.5	656.2	663.6	669.7	669.0
135°	675.7	686.5	692.5	699.2	697.9
137.5°	705.3	713.3	720.0	726.8	724.8
140°	734.2	739.5	746.9	753.0	749.6
142.5°	758.3	763.0	771.8	777.1	773.8
145°	783.9	783.2	794.6	799.3	795.9
147.5°	806.0	804.0	815.4	818.8	816.1
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)