

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001458

Luminaire Tested: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001458
REPORT IS A COMBINATION OF REPORTS P996077 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5798.0 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001458

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001458

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15
9	49	37	29	24	45	34	27	23	29	23	20	23	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1001458

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.5
10°-20°	247.0	4.3
20°-30°	363.4	6.3
30°-40°	422.5	7.3
40°-50°	422.5	7.3
50°-60°	369.5	6.4
60°-70°	274.3	4.7
70°-80°	155.6	2.7
80°-90°	47.2	0.8
90°-100°	80.1	1.4
100°-110°	239.8	4.1
110°-120°	407.4	7.0
120°-130°	537.3	9.3
130°-140°	603.5	10.4
140°-150°	593.2	10.2
150°-160°	498.9	8.6
160°-170°	332.0	5.7
170°-180°	116.2	2.0
0°-30°	698.1	12.0
0°-40°	1120.5	19.3
0°-60°	1912.5	33.0
0°-90°	2389.6	41.2
90°-120°	727.4	12.5
90°-150°	2461.3	42.5
90°-180°	3408.0	58.8
0°-180°	5798.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	3	13	21	27	28	7
95°	57	66	72	75	75	62
105°	221	222	226	229	232	235
115°	414	414	412	411	410	409
125°	603	603	602	600	598	538
135°	778	784	784	782	779	602
145°	945	949	950	949	946	592
155°	1083	1083	1082	1086	1082	498
165°	1179	1176	1174	1180	1176	332
175°	1226	1222	1221	1228	1221	116
180°	1228	1228	1228	1228	1228	

TEST NUMBER: P1001458

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	2.9	13.3	20.9	26.6	28.5
92.5°	24.7	37.1	41.8	44.7	45.6
95°	57.0	65.6	72.2	75.1	75.1
97.5°	91.2	98.8	106.4	110.2	110.2
100°	133.0	136.8	145.4	147.3	147.3
102.5°	176.7	177.7	185.3	188.1	189.1
105°	221.4	222.3	226.1	229.0	231.8
107.5°	267.9	268.9	269.8	273.6	272.7
110°	315.4	317.3	316.4	314.5	317.3

TEST NUMBER: P1001458

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.8	364.8	362.9	362.9	362.9
115°	414.2	414.2	412.3	411.4	410.4
117.5°	460.8	460.8	459.8	457.0	454.1
120°	507.3	511.1	508.3	503.5	505.4
122.5°	555.8	556.7	555.8	552.9	548.2
125°	603.3	603.3	602.3	600.4	598.5
127.5°	646.0	648.9	647.0	645.1	644.1
130°	691.6	694.5	694.5	692.6	688.8
132.5°	738.2	740.1	739.1	737.2	736.3
135°	778.1	783.8	783.8	781.9	779.0
137.5°	822.7	825.6	827.5	824.6	825.6
140°	867.4	869.3	869.3	868.3	867.4
142.5°	908.2	910.1	909.2	909.2	909.2
145°	945.3	949.1	950.0	949.1	946.2
147.5°	983.3	988.0	987.1	986.1	985.2
150°	1017.5	1021.3	1021.3	1021.3	1020.3
152.5°	1049.8	1051.7	1052.6	1055.5	1052.6
155°	1083.0	1083.0	1082.1	1085.9	1082.1
157.5°	1111.6	1109.7	1109.7	1112.5	1109.7
160°	1136.3	1135.3	1134.4	1137.2	1132.5
162.5°	1159.1	1156.2	1155.3	1161.0	1156.2
165°	1179.0	1176.2	1174.3	1180.0	1176.2
167.5°	1195.2	1191.4	1191.4	1197.1	1191.4
170°	1208.5	1203.7	1204.7	1210.4	1203.7
172.5°	1218.0	1214.2	1214.2	1220.8	1214.2
175°	1226.5	1221.8	1220.8	1227.5	1220.8
177.5°	1230.3	1225.6	1225.6	1232.2	1224.6
180°	1228.4	1228.4	1228.4	1228.4	1228.4

(END OF REPORT)