

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001459

Luminaire Tested: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001459
REPORT IS A COMBINATION OF REPORTS P996078 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5919.0 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001459

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001459

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	34	34	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	30	29	29	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	25	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	27	24	24	21	19	19	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1001459

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.5
10°-20°	247.0	4.2
20°-30°	363.4	6.1
30°-40°	422.5	7.1
40°-50°	422.5	7.1
50°-60°	369.5	6.2
60°-70°	274.3	4.6
70°-80°	155.6	2.6
80°-90°	46.4	0.8
90°-100°	359.3	6.1
100°-110°	730.8	12.3
110°-120°	651.4	11.0
120°-130°	547.2	9.2
130°-140°	456.6	7.7
140°-150°	348.7	5.9
150°-160°	245.1	4.1
160°-170°	144.2	2.4
170°-180°	46.9	0.8
0°-30°	698.1	11.8
0°-40°	1120.5	18.9
0°-60°	1912.5	32.3
0°-90°	2388.9	40.4
90°-120°	1741.5	29.4
90°-150°	3094.0	52.3
90°-180°	3530.0	59.6
0°-180°	5919.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	1	8	17	19	20	5
95°	31	99	774	384	232	34
105°	111	161	623	1342	1337	118
115°	196	246	556	1068	1284	194
125°	273	324	553	909	1024	243
135°	324	386	548	807	916	250
145°	374	428	546	680	748	234
155°	425	459	530	601	626	196
165°	463	477	508	538	546	131
175°	483	484	488	494	492	46
180°	484	484	484	484	484	

TEST NUMBER: P1001459

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	1.0	7.6	17.1	19.0	20.0
92.5°	13.3	73.2	372.5	123.0	86.5
95°	31.4	98.8	774.5	383.5	231.9
97.5°	52.3	109.3	828.7	783.1	556.9
100°	72.2	123.6	764.1	1083.4	871.5
102.5°	91.2	140.6	683.3	1271.6	1145.2
105°	111.2	161.1	623.4	1342.4	1337.1
107.5°	133.0	182.0	584.5	1321.0	1428.4
110°	154.9	202.9	566.4	1245.0	1430.3

TEST NUMBER: P1001459

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.8	223.8	557.9	1151.8	1374.2
115°	195.8	245.6	556.0	1068.2	1283.9
117.5°	216.7	266.1	555.0	1002.6	1195.5
120°	237.6	286.0	555.0	958.4	1123.3
122.5°	256.6	305.5	554.1	929.4	1066.3
125°	272.7	324.1	553.1	909.0	1024.5
127.5°	288.0	341.2	551.2	889.5	997.9
130°	300.3	357.8	550.2	866.2	975.1
132.5°	312.7	372.0	549.3	838.7	949.4
135°	324.1	385.8	548.3	806.8	916.1
137.5°	335.5	397.7	548.3	772.6	877.2
140°	347.8	408.6	547.4	739.3	834.4
142.5°	361.1	418.6	547.4	708.5	788.8
145°	373.5	427.6	545.5	680.4	747.9
147.5°	387.7	436.2	542.6	657.2	709.9
150°	401.0	444.3	539.8	635.8	678.5
152.5°	413.4	451.9	535.0	617.8	650.0
155°	424.8	458.6	530.3	600.6	626.3
157.5°	436.2	464.7	525.5	584.4	604.4
160°	446.7	470.0	519.8	568.3	584.5
162.5°	456.2	474.2	514.1	552.6	565.5
165°	462.8	477.0	508.4	538.4	546.4
167.5°	470.4	479.4	502.7	526.0	531.2
170°	475.2	481.4	497.0	513.7	517.0
172.5°	479.9	482.8	491.3	502.8	502.7
175°	482.8	483.7	487.5	494.2	492.3
177.5°	484.7	483.7	484.7	488.0	484.7
180°	483.7	483.7	483.7	483.7	483.7

(END OF REPORT)