

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008061

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008061
REPORT IS A COMBINATION OF REPORTS P984074 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4850.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008061

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008061

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	21
1	91	86	82	79	80	76	73	70	58	56	54	41	40	38	25	25	24	24	24	17
2	82	75	69	64	73	66	61	57	50	47	44	36	33	31	22	21	20	20	20	13
3	75	66	58	53	66	58	52	47	44	40	37	31	29	26	19	18	16	16	16	11
4	68	58	50	44	60	51	45	40	39	34	31	28	25	22	17	15	14	14	14	9
5	62	51	43	37	55	45	39	34	35	30	26	25	21	19	15	13	12	12	12	8
6	57	46	38	32	50	41	34	29	31	26	23	22	19	16	14	12	10	10	10	7
7	53	41	33	28	47	36	30	25	28	23	20	20	17	14	12	11	9	9	9	6
8	49	37	29	24	43	33	26	22	25	21	17	18	15	13	11	10	8	8	8	5
9	45	34	26	21	40	30	24	19	23	18	15	17	13	11	10	9	7	7	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	7	7	7	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4850	4850	4850
5°	4872	4643	4617
10°	4839	4483	4417
15°	4770	4315	4212
20°	4684	4141	4017
25°	4599	3973	3840
30°	4479	3804	3665
35°	4360	3639	3537
40°	4232	3498	3409
45°	4112	3370	3298
50°	3982	3252	3188
55°	3845	3126	3076
60°	3678	2994	2959
65°	3505	2843	2824
70°	3309	2682	2678
75°	3054	2520	2542
80°	2659	2351	2399
85°	2260	2192	2276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4112 cd/sqm

TEST NUMBER: P1008061

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	0.6
10°-20°	83.3	1.7
20°-30°	126.2	2.6
30°-40°	153.7	3.2
40°-50°	165.4	3.4
50°-60°	160.6	3.3
60°-70°	140.2	2.9
70°-80°	108.0	2.2
80°-90°	74.5	1.5
90°-100°	91.3	1.9
100°-110°	190.7	3.9
110°-120°	433.1	8.9
120°-130°	691.9	14.3
130°-140°	726.3	15.0
140°-150°	670.8	13.8
150°-160°	538.5	11.1
160°-170°	347.0	7.2
170°-180°	119.4	2.5
0°-30°	238.5	4.9
0°-40°	392.2	8.1
0°-60°	718.2	14.8
0°-90°	1040.9	21.5
90°-120°	715.1	14.7
90°-150°	2804.1	57.8
90°-180°	3809.0	78.5
0°-180°	4850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	306	306	306	306	306	
5°	307	306	303	306	306	29
15°	293	294	294	298	298	83
25°	266	270	274	279	280	123
35°	230	237	246	255	258	143
45°	188	200	216	230	234	145
55°	144	160	183	199	205	129
65°	99	120	146	165	170	98
75°	55	80	108	127	133	58
85°	16	44	72	91	97	17
90°	5	41	77	99	106	6
95°	63	54	86	108	112	73
105°	278	318	94	119	128	297
115°	524	544	587	180	119	516
125°	739	751	782	801	807	659
135°	914	928	941	959	961	706
145°	1060	1059	1074	1083	1081	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008061

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	306.4	306.4	306.4	306.4	306.4
2.5°	308.6	307.3	304.1	306.4	305.5
5°	307.3	305.9	303.3	305.9	305.5
7.5°	305.0	304.1	301.9	305.0	304.6
10°	302.4	301.5	300.2	303.7	303.3
12.5°	297.9	298.4	297.5	301.0	300.6
15°	293.0	293.9	293.9	297.9	297.5
17.5°	286.8	288.6	289.9	293.9	293.9
20°	280.6	282.8	284.6	289.5	289.5
22.5°	274.0	276.6	279.3	284.2	285.1
25°	266.4	269.5	273.5	278.8	280.2
27.5°	257.5	262.4	266.9	273.5	274.4
30°	248.6	254.4	260.2	267.3	268.6
32.5°	238.9	245.5	252.6	261.1	263.7
35°	229.6	237.1	245.5	255.3	258.4
37.5°	219.3	227.8	238.4	249.1	252.2
40°	209.1	218.9	230.9	242.4	246.4
42.5°	199.4	209.1	223.3	236.2	240.2
45°	188.3	200.3	215.8	229.6	234.0
47.5°	177.6	190.5	208.2	222.5	227.3
50°	166.5	180.3	200.3	215.3	220.2
52.5°	155.8	170.5	191.8	207.4	212.7
55°	144.3	160.3	183.4	199.4	205.1
57.5°	133.2	151.0	174.1	191.4	197.1
60°	121.2	140.3	165.6	182.5	188.7
62.5°	110.6	130.5	155.8	174.1	179.8
65°	98.6	120.3	146.5	164.7	170.5
67.5°	87.9	110.6	137.2	155.4	161.6
70°	76.4	99.5	127.0	146.1	151.4
72.5°	65.7	89.7	117.7	136.3	143.0
75°	54.6	79.5	107.9	127.0	132.8
77.5°	44.0	69.7	98.6	117.7	123.9
80°	33.3	60.4	89.2	107.9	114.1
82.5°	24.4	51.1	80.4	99.0	104.8
85°	16.0	43.5	71.9	90.6	96.8
87.5°	9.8	36.4	64.8	83.0	88.8
90°	5.3	41.1	76.8	99.1	106.2
92.5°	26.7	46.6	76.4	95.5	101.8
95°	62.6	53.5	86.5	107.9	112.3
97.5°	109.3	54.0	94.3	113.4	119.6
100°	163.8	55.8	96.2	119.8	126.5
102.5°	223.3	236.1	94.9	120.9	128.5
105°	278.2	318.4	93.6	119.1	127.6
107.5°	342.7	376.1	92.3	117.4	125.9
110°	404.0	432.0	191.3	114.7	123.2

TEST NUMBER: P1008061

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	462.2	485.6	490.6	113.4	121.0
115°	523.9	544.2	586.8	179.8	119.3
117.5°	577.0	598.7	632.8	516.3	282.8
120°	636.9	652.3	686.5	709.8	592.1
122.5°	687.7	702.8	737.3	754.8	759.7
125°	739.1	750.9	782.4	800.7	807.4
127.5°	786.3	798.5	824.2	844.3	849.2
130°	830.8	844.8	864.2	884.8	887.5
132.5°	876.2	887.5	904.2	922.6	925.3
135°	913.8	928.4	941.0	959.4	961.2
137.5°	953.8	964.7	976.1	993.6	993.9
140°	992.8	999.7	1010.6	1025.9	1024.0
142.5°	1025.5	1031.5	1043.3	1055.9	1053.5
145°	1059.6	1058.7	1074.2	1083.2	1080.9
147.5°	1089.6	1086.9	1102.3	1107.3	1105.0
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)