

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001465

Luminaire Tested: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001465
REPORT IS A COMBINATION OF REPORTS P996084 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6617.5 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001465

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001465

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	93	89	85	81	84	80	77	73	64	61	59	48	47	45	34	34	33
2	85	77	71	66	76	69	64	60	55	51	48	42	40	37	30	28	27
3	77	67	60	54	69	61	55	49	48	44	40	37	34	31	26	24	23
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19
5	64	53	45	39	58	48	41	35	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	26	23	20	19	16	14
7	54	42	34	29	49	38	31	27	31	26	22	24	20	17	17	15	13
8	50	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	14	12	10
10	44	32	25	20	39	29	23	18	23	19	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4944 cd/sqm

TEST NUMBER: P1001465

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.0
10°-20°	186.2	2.8
20°-30°	281.6	4.3
30°-40°	340.7	5.1
40°-50°	360.2	5.4
50°-60°	339.0	5.1
60°-70°	281.3	4.3
70°-80°	197.4	3.0
80°-90°	113.5	1.7
90°-100°	501.5	7.6
100°-110°	934.3	14.1
110°-120°	822.0	12.4
120°-130°	681.4	10.3
130°-140°	561.1	8.5
140°-150°	424.0	6.4
150°-160°	296.9	4.5
160°-170°	174.6	2.6
170°-180°	56.8	0.9
0°-30°	532.8	8.1
0°-40°	873.5	13.2
0°-60°	1572.7	23.8
0°-90°	2164.9	32.7
90°-120°	2257.8	34.1
90°-150°	3924.3	59.3
90°-180°	4453.0	67.3
0°-180°	6617.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	14	52	97	121	129	11
95°	48	155	1005	552	375	50
105°	142	217	806	1696	1696	151
115°	242	309	710	1347	1614	240
125°	334	395	692	1137	1282	297
135°	394	469	671	997	1134	305
145°	453	518	661	829	914	285
155°	515	555	642	728	759	237
165°	561	578	616	652	662	158
175°	585	586	591	599	596	56
180°	586	586	586	586	586	

TEST NUMBER: P1001465

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	13.5	52.2	96.8	121.3	128.7
92.5°	27.6	127.0	522.7	242.1	203.9
95°	48.0	155.0	1005.0	552.1	375.4
97.5°	72.5	163.9	1066.8	1031.6	764.5
100°	96.0	178.0	984.0	1391.5	1140.1
102.5°	119.0	195.8	882.2	1614.8	1467.9
105°	141.6	217.4	805.9	1696.0	1695.8
107.5°	168.1	240.4	754.9	1666.2	1801.7
110°	193.7	262.6	729.9	1569.6	1800.2

TEST NUMBER: P1001465

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.4	285.7	715.7	1452.2	1727.6
115°	241.7	309.0	709.6	1347.0	1613.7
117.5°	267.1	331.6	704.6	1263.0	1502.7
120°	291.6	352.6	700.7	1204.8	1410.6
122.5°	314.6	374.0	695.7	1165.8	1336.9
125°	333.5	394.8	691.5	1137.2	1281.7
127.5°	351.9	415.6	685.4	1109.0	1245.7
130°	366.1	434.9	680.3	1077.0	1213.4
132.5°	381.0	452.2	676.2	1039.7	1178.4
135°	394.1	468.9	671.1	996.6	1133.6
137.5°	407.9	482.6	668.0	951.3	1081.8
140°	422.8	495.8	664.6	907.2	1026.2
142.5°	438.3	507.9	663.1	866.8	967.0
145°	453.2	518.0	660.8	828.8	913.7
147.5°	470.5	528.4	657.3	796.8	863.7
150°	486.6	538.2	653.9	770.2	822.0
152.5°	500.8	547.4	648.1	748.2	787.4
155°	514.6	555.4	642.4	727.6	758.6
157.5°	528.4	562.9	636.6	708.0	732.2
160°	541.1	569.2	629.7	688.4	708.0
162.5°	552.6	574.4	622.8	669.4	685.0
165°	560.6	577.9	615.9	652.2	661.9
167.5°	569.8	580.8	609.0	637.2	643.5
170°	575.6	583.1	602.1	622.2	626.3
172.5°	581.4	584.8	595.2	609.0	609.0
175°	584.8	586.0	590.6	598.6	596.3
177.5°	587.1	586.0	587.1	591.2	587.1
180°	586.0	586.0	586.0	586.0	586.0

(END OF REPORT)