

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008066

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008066
REPORT IS A COMBINATION OF REPORTS P984079 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4856.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008066

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008066

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32			24
1	92	88	84	81	82	78	75	72	60	58	56	44	43	41	29	28	27			20
2	84	77	71	66	74	68	63	59	53	49	47	38	36	35	25	24	23			17
3	76	67	60	55	68	60	54	49	47	42	39	34	31	29	22	21	20			14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17			12
5	64	53	45	39	57	47	41	36	37	32	28	27	24	21	18	16	15			11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13			9
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11			8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10			8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9			7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6100 cd/sqm

TEST NUMBER: P1008066

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	0.9
10°-20°	122.3	2.5
20°-30°	179.7	3.7
30°-40°	208.7	4.3
40°-50°	208.5	4.3
50°-60°	181.8	3.7
60°-70°	134.4	2.8
70°-80°	76.0	1.6
80°-90°	22.3	0.5
90°-100°	41.4	0.9
100°-110°	154.2	3.2
110°-120°	409.1	8.4
120°-130°	678.5	14.0
130°-140°	720.7	14.8
140°-150°	669.9	13.8
150°-160°	538.5	11.1
160°-170°	347.0	7.1
170°-180°	119.4	2.5
0°-30°	345.5	7.1
0°-40°	554.2	11.4
0°-60°	944.5	19.5
0°-90°	1177.2	24.2
90°-120°	604.7	12.5
90°-150°	2673.8	55.1
90°-180°	3679.0	75.8
0°-180°	4856.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	1	11	18	23	24	4
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008066

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7

TEST NUMBER: P1008066

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)