

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008067

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008067
REPORT IS A COMBINATION OF REPORTS P984080 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4808.0 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008067

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008067

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24		
1	92	88	84	81	82	78	75	72	60	58	56	44	43	41	29	28	27	20		
2	84	77	71	66	74	68	63	59	53	49	47	38	36	35	25	24	23	17		
3	76	67	60	55	68	60	54	49	47	42	39	34	31	29	22	21	20	14		
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12		
5	64	53	45	39	57	47	41	36	37	32	28	27	24	21	18	16	15	11		
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9		
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8		
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8		
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9	7		
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7236	7236	7236
5°	7247	6897	6849
10°	7189	6583	6453
15°	7083	6266	6036
20°	6941	5921	5641
25°	6799	5561	5247
30°	6622	5223	4834
35°	6453	4866	4428
40°	6246	4515	4044
45°	6039	4166	3667
50°	5813	3811	3278
55°	5574	3431	2907
60°	5307	3019	2523
65°	5016	2603	2118
70°	4643	2144	1711
75°	4128	1654	1321
80°	3513	1123	849
85°	2543	521	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6039 cd/sqm

TEST NUMBER: P1008067

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	0.9
10°-20°	121.1	2.5
20°-30°	177.9	3.7
30°-40°	206.6	4.3
40°-50°	206.4	4.3
50°-60°	179.9	3.7
60°-70°	133.0	2.8
70°-80°	75.3	1.6
80°-90°	22.0	0.5
90°-100°	41.0	0.9
100°-110°	152.7	3.2
110°-120°	405.1	8.4
120°-130°	671.9	14.0
130°-140°	713.7	14.8
140°-150°	663.3	13.8
150°-160°	533.3	11.1
160°-170°	343.6	7.1
170°-180°	118.3	2.5
0°-30°	342.0	7.1
0°-40°	548.6	11.4
0°-60°	934.9	19.4
0°-90°	1165.2	24.2
90°-120°	598.8	12.5
90°-150°	2647.7	55.1
90°-180°	3643.0	75.8
0°-180°	4808.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	457	457	457	457	457	
5°	457	455	450	454	453	43
15°	435	432	427	429	426	123
25°	394	390	383	384	383	181
35°	340	335	328	326	324	212
45°	276	273	267	262	260	213
55°	209	207	201	196	194	187
65°	141	138	134	130	128	139
75°	74	73	71	68	69	79
85°	18	18	17	16	15	20
90°	1	11	18	22	24	4
95°	58	29	35	40	39	69
105°	273	300	55	65	68	292
115°	517	532	555	138	74	509
125°	731	743	760	766	769	652
135°	904	919	927	936	934	699
145°	1049	1048	1064	1070	1066	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008067

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	457.1	457.1	457.1	457.1	457.1
2.5°	459.8	457.6	452.7	457.1	456.2
5°	457.1	455.4	450.5	454.0	453.2
7.5°	454.0	451.4	446.6	450.1	449.2
10°	449.2	446.1	440.9	444.4	443.1
12.5°	442.6	440.0	434.7	436.9	436.0
15°	435.1	432.5	426.8	428.6	426.4
17.5°	425.9	423.3	417.6	419.8	417.6
20°	415.8	413.2	407.0	408.3	406.6
22.5°	405.7	401.7	396.0	396.0	395.1
25°	393.8	390.3	382.8	383.7	382.8
27.5°	380.6	377.6	371.9	370.5	368.3
30°	367.5	363.9	357.3	356.0	354.3
32.5°	353.4	350.8	343.7	341.1	339.3
35°	339.8	335.4	328.3	325.7	323.5
37.5°	324.4	320.4	313.4	310.3	308.1
40°	308.6	305.0	298.0	294.1	292.3
42.5°	293.2	289.7	282.6	278.2	275.6
45°	276.5	273.4	266.8	262.0	260.2
47.5°	260.2	257.1	250.1	245.3	242.6
50°	243.1	240.9	234.7	228.6	226.4
52.5°	226.4	223.3	217.6	212.7	209.7
55°	209.2	206.6	201.3	196.0	193.8
57.5°	192.1	189.9	184.2	178.9	177.1
60°	174.9	173.2	167.0	162.2	160.9
62.5°	158.2	155.2	150.8	146.4	144.6
65°	141.1	138.5	134.1	130.1	127.9
67.5°	123.5	121.3	117.4	114.3	112.5
70°	107.2	105.5	101.5	98.5	96.7
72.5°	90.5	88.8	86.6	83.5	82.2
75°	73.8	73.0	70.8	68.1	69.0
77.5°	58.9	57.1	56.3	54.9	53.6
80°	44.0	43.5	42.6	41.3	40.4
82.5°	29.9	29.9	29.4	27.7	27.7
85°	18.0	17.6	17.1	15.8	15.4
87.5°	7.9	7.0	6.2	4.8	4.4
90°	0.9	10.8	18.0	22.5	24.3
92.5°	22.5	18.9	21.6	23.4	24.3
95°	58.4	28.8	35.1	39.6	38.7
97.5°	105.2	31.5	45.9	48.6	49.5
100°	159.1	36.0	51.2	58.4	60.2
102.5°	218.5	216.7	53.0	62.9	65.6
105°	273.3	300.3	54.8	64.7	68.3
107.5°	337.2	359.6	56.6	66.5	70.1
110°	398.3	417.2	157.3	67.4	71.0

TEST NUMBER: P1008067

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	455.9	472.0	456.8	69.2	71.9
115°	517.0	532.3	554.8	138.5	73.7
117.5°	570.0	588.0	603.3	474.7	239.2
120°	629.4	642.9	659.1	669.8	548.5
122.5°	679.7	694.1	712.1	717.5	718.4
125°	731.0	742.7	759.8	766.0	768.7
127.5°	777.7	790.3	803.8	812.8	813.7
130°	821.8	836.2	846.1	856.0	855.1
132.5°	866.8	878.4	888.3	896.4	895.5
135°	904.5	918.9	927.0	936.0	934.2
137.5°	944.1	954.9	963.9	972.8	970.1
140°	982.7	989.9	999.8	1007.9	1003.4
142.5°	1015.1	1021.4	1033.1	1040.3	1035.8
145°	1049.3	1048.4	1063.7	1070.0	1065.5
147.5°	1078.9	1076.2	1091.5	1096.0	1092.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)