

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001501

Luminaire Tested: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001501
REPORT IS A COMBINATION OF REPORTS P996120 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6827.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001501

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001501

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1001501

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.3
10°-20°	257.9	3.8
20°-30°	379.6	5.6
30°-40°	441.2	6.5
40°-50°	441.2	6.5
50°-60°	385.9	5.7
60°-70°	286.5	4.2
70°-80°	162.5	2.4
80°-90°	48.8	0.7
90°-100°	441.0	6.5
100°-110°	896.9	13.1
110°-120°	799.4	11.7
120°-130°	671.5	9.8
130°-140°	560.4	8.2
140°-150°	428.0	6.3
150°-160°	300.8	4.4
160°-170°	176.9	2.6
170°-180°	57.5	0.8
0°-30°	729.1	10.7
0°-40°	1170.3	17.1
0°-60°	1997.4	29.3
0°-90°	2495.3	36.5
90°-120°	2137.3	31.3
90°-150°	3797.1	55.6
90°-180°	4332.0	63.4
0°-180°	6827.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	9	21	23	24	5
95°	38	121	950	471	285	42
105°	136	198	765	1647	1641	145
115°	240	301	682	1311	1576	238
125°	335	398	679	1116	1257	298
135°	398	474	673	990	1124	307
145°	458	525	670	835	918	288
155°	521	563	651	737	769	240
165°	568	586	624	661	671	160
175°	592	594	598	606	604	56
180°	594	594	594	594	594	

TEST NUMBER: P1001501

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.2	9.3	21.0	23.3	24.5
92.5°	16.3	89.8	457.2	151.0	106.1
95°	38.5	121.3	950.5	470.6	284.6
97.5°	64.1	134.1	1017.0	961.0	683.4
100°	88.6	151.6	937.7	1329.6	1069.5
102.5°	112.0	172.6	838.6	1560.5	1405.4
105°	136.5	197.7	765.1	1647.4	1641.0
107.5°	163.3	223.4	717.3	1621.2	1752.9
110°	190.1	249.0	695.1	1527.8	1755.3

TEST NUMBER: P1001501

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.8	274.6	684.6	1413.6	1686.5
115°	240.3	301.4	682.3	1310.9	1575.7
117.5°	265.9	326.5	681.1	1230.4	1467.2
120°	291.6	351.0	681.1	1176.2	1378.6
122.5°	314.9	375.0	680.0	1140.6	1308.6
125°	334.7	397.7	678.8	1115.6	1257.3
127.5°	353.4	418.7	676.5	1091.6	1224.6
130°	368.5	439.1	675.3	1063.1	1196.6
132.5°	383.7	456.6	674.1	1029.2	1165.1
135°	397.7	473.6	673.0	990.2	1124.3
137.5°	411.7	488.1	673.0	948.2	1076.5
140°	426.9	501.5	671.8	907.4	1024.0
142.5°	443.2	513.8	671.8	869.5	968.0
145°	458.4	524.8	669.5	835.0	917.9
147.5°	475.8	535.4	666.0	806.5	871.2
150°	492.2	545.2	662.5	780.2	832.7
152.5°	507.3	554.6	656.6	758.1	797.7
155°	521.3	562.8	650.8	737.1	768.6
157.5°	535.3	570.3	645.0	717.2	741.8
160°	548.2	576.7	638.0	697.4	717.3
162.5°	559.8	582.0	631.0	678.2	693.9
165°	568.0	585.5	624.0	660.7	670.6
167.5°	577.3	588.4	617.0	645.6	652.0
170°	583.1	590.8	610.0	630.4	634.5
172.5°	589.0	592.4	603.0	617.0	617.0
175°	592.5	593.6	598.3	606.5	604.1
177.5°	594.8	593.6	594.8	598.9	594.8
180°	593.6	593.6	593.6	593.6	593.6

(END OF REPORT)