

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008068

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008068
REPORT IS A COMBINATION OF REPORTS P984081 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4649.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008068

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008068

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	43	41	29	28	27
2	84	77	71	66	74	68	63	59	53	49	47	38	36	35	25	24	23
3	76	67	60	55	68	60	54	49	47	42	39	34	31	29	22	21	20
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	39	57	47	41	36	37	32	28	27	24	21	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7000	7000	7000
5°	7011	6672	6625
10°	6953	6368	6242
15°	6852	6062	5838
20°	6714	5728	5457
25°	6578	5380	5075
30°	6405	5054	4676
35°	6243	4708	4283
40°	6041	4368	3911
45°	5840	4030	3548
50°	5622	3686	3170
55°	5393	3318	2812
60°	5134	2922	2440
65°	4852	2517	2049
70°	4491	2074	1654
75°	3994	1600	1279
80°	3393	1086	822
85°	2458	506	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5840 cd/sqm

TEST NUMBER: P1008068

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	0.9
10°-20°	117.1	2.5
20°-30°	172.1	3.7
30°-40°	199.9	4.3
40°-50°	199.6	4.3
50°-60°	174.1	3.7
60°-70°	128.7	2.8
70°-80°	72.8	1.6
80°-90°	21.3	0.5
90°-100°	39.6	0.9
100°-110°	147.7	3.2
110°-120°	391.6	8.4
120°-130°	649.6	14.0
130°-140°	690.0	14.8
140°-150°	641.3	13.8
150°-160°	515.6	11.1
160°-170°	332.2	7.1
170°-180°	114.3	2.5
0°-30°	330.8	7.1
0°-40°	530.7	11.4
0°-60°	904.3	19.5
0°-90°	1127.1	24.2
90°-120°	578.9	12.5
90°-150°	2559.8	55.1
90°-180°	3522.0	75.8
0°-180°	4649.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	439	438	42
15°	421	418	413	415	412	119
25°	381	378	370	371	370	175
35°	329	324	318	315	313	205
45°	267	264	258	253	252	206
55°	202	200	195	190	188	181
65°	136	134	130	126	124	135
75°	71	71	68	66	67	76
85°	17	17	17	15	15	19
90°	1	10	17	22	24	4
95°	56	28	34	38	37	67
105°	264	290	53	63	66	282
115°	500	515	536	134	71	492
125°	707	718	734	741	743	630
135°	874	888	896	905	903	676
145°	1014	1014	1028	1034	1030	634
155°	1117	1109	1120	1125	1118	515
165°	1177	1172	1174	1180	1174	333
175°	1204	1198	1200	1206	1197	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P1008068

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	442.2	442.2	442.2	442.2	442.2
2.5°	444.7	442.6	437.9	442.2	441.3
5°	442.2	440.5	435.8	439.2	438.4
7.5°	439.2	436.7	432.0	435.4	434.5
10°	434.5	431.6	426.5	429.9	428.6
12.5°	428.2	425.6	420.5	422.6	421.8
15°	420.9	418.4	412.9	414.6	412.4
17.5°	412.0	409.5	403.9	406.0	403.9
20°	402.2	399.7	393.7	395.0	393.3
22.5°	392.4	388.6	383.1	383.1	382.2
25°	381.0	377.6	370.3	371.2	370.3
27.5°	368.2	365.2	359.7	358.4	356.3
30°	355.5	352.1	345.7	344.4	342.7
32.5°	341.8	339.3	332.5	329.9	328.2
35°	328.7	324.4	317.6	315.1	312.9
37.5°	313.8	310.0	303.2	300.2	298.1
40°	298.5	295.1	288.3	284.4	282.7
42.5°	283.6	280.2	273.4	269.1	266.6
45°	267.4	264.5	258.1	253.4	251.7
47.5°	251.7	248.7	241.9	237.3	234.7
50°	235.1	233.0	227.0	221.1	219.0
52.5°	219.0	216.0	210.5	205.8	202.8
55°	202.4	199.8	194.7	189.6	187.5
57.5°	185.8	183.7	178.2	173.0	171.3
60°	169.2	167.5	161.6	156.9	155.6
62.5°	153.1	150.1	145.8	141.6	139.9
65°	136.5	133.9	129.7	125.9	123.7
67.5°	119.5	117.4	113.5	110.5	108.8
70°	103.7	102.0	98.2	95.2	93.5
72.5°	87.6	85.9	83.8	80.8	79.5
75°	71.4	70.6	68.5	65.9	66.8
77.5°	57.0	55.3	54.4	53.1	51.9
80°	42.5	42.1	41.2	40.0	39.1
82.5°	28.9	28.9	28.5	26.8	26.8
85°	17.4	17.0	16.6	15.3	14.9
87.5°	7.7	6.8	6.0	4.7	4.3
90°	0.9	10.4	17.4	21.7	23.5
92.5°	21.7	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.2	37.4
97.5°	101.7	30.4	44.3	46.9	47.8
100°	153.9	34.8	49.5	56.5	58.2
102.5°	211.2	209.5	51.3	60.8	63.5
105°	264.3	290.3	53.0	62.6	66.1
107.5°	326.0	347.7	54.8	64.3	67.8
110°	385.1	403.3	152.1	65.2	68.7

TEST NUMBER: P1008068

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	440.7	456.4	441.6	66.9	69.5
115°	499.8	514.6	536.3	133.9	71.3
117.5°	551.1	568.5	583.3	459.0	231.2
120°	608.5	621.5	637.2	647.6	530.3
122.5°	657.2	671.1	688.5	693.7	694.5
125°	706.7	718.0	734.5	740.6	743.2
127.5°	751.9	764.1	777.1	785.8	786.7
130°	794.5	808.4	818.0	827.5	826.7
132.5°	838.0	849.3	858.8	866.7	865.8
135°	874.5	888.4	896.2	904.9	903.2
137.5°	912.7	923.2	931.9	940.6	937.9
140°	950.1	957.1	966.6	974.5	970.1
142.5°	981.4	987.5	998.8	1005.7	1001.4
145°	1014.4	1013.6	1028.3	1034.4	1030.1
147.5°	1043.1	1040.5	1055.3	1059.6	1056.2
150°	1070.9	1064.9	1078.8	1084.0	1079.6
152.5°	1094.4	1087.5	1100.5	1105.7	1099.6
155°	1117.0	1109.2	1119.6	1124.8	1117.9
157.5°	1135.3	1128.3	1136.1	1142.2	1135.3
160°	1150.9	1145.7	1150.9	1156.1	1150.0
162.5°	1164.8	1159.6	1164.0	1170.0	1162.2
165°	1177.0	1171.8	1174.4	1180.5	1174.4
167.5°	1186.6	1181.3	1183.9	1190.0	1182.2
170°	1194.4	1189.2	1190.9	1197.0	1189.2
172.5°	1199.6	1194.4	1196.1	1202.2	1194.4
175°	1203.9	1197.9	1199.6	1205.7	1197.0
177.5°	1205.7	1199.6	1200.5	1206.5	1198.7
180°	1201.3	1201.3	1201.3	1201.3	1201.3

(END OF REPORT)