

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008083

Luminaire Tested: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008083
REPORT IS A COMBINATION OF REPORTS P984141 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6033.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008083

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008083

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	34	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11772	11772	11772
5°	11791	11220	11141
10°	11695	10709	10497
15°	11524	10194	9819
20°	11291	9633	9177
25°	11061	9048	8536
30°	10771	8498	7863
35°	10497	7919	7203
40°	10160	7345	6579
45°	9824	6777	5966
50°	9455	6199	5332
55°	9070	5582	4729
60°	8636	4912	4104
65°	8159	4233	3447
70°	7557	3489	2783
75°	6718	2689	2149
80°	5708	1829	1383
85°	4139	851	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9824 cd/sqm

TEST NUMBER: P1008083

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.2
10°-20°	196.9	3.3
20°-30°	289.4	4.8
30°-40°	336.1	5.6
40°-50°	335.7	5.6
50°-60°	292.7	4.9
60°-70°	216.4	3.6
70°-80°	122.4	2.0
80°-90°	34.8	0.6
90°-100°	46.6	0.8
100°-110°	173.5	2.9
110°-120°	460.2	7.6
120°-130°	763.3	12.7
130°-140°	810.8	13.4
140°-150°	753.6	12.5
150°-160°	605.8	10.0
160°-170°	390.4	6.5
170°-180°	134.4	2.2
0°-30°	556.3	9.2
0°-40°	892.4	14.8
0°-60°	1520.9	25.2
0°-90°	1894.5	31.4
90°-120°	680.3	11.3
90°-150°	3007.9	49.9
90°-180°	4139.0	68.6
0°-180°	6033.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	741	733	739	737	71
15°	708	704	694	697	694	199
25°	641	635	623	624	623	295
35°	553	546	534	530	526	345
45°	450	445	434	426	423	347
55°	340	336	328	319	315	304
65°	230	225	218	212	208	227
75°	120	119	115	111	112	128
85°	29	29	28	26	25	33
90°	1	12	20	26	28	6
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1008083

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	743.7	743.7	743.7	743.7	743.7
2.5°	748.0	744.4	736.5	743.7	742.2
5°	743.7	740.8	732.9	738.7	737.2
7.5°	738.7	734.4	726.5	732.2	730.8
10°	730.8	725.8	717.2	722.9	720.8
12.5°	720.1	715.8	707.2	710.8	709.3
15°	707.9	703.6	694.3	697.2	693.6
17.5°	692.9	688.6	679.3	682.9	679.3
20°	676.4	672.2	662.1	664.3	661.4
22.5°	660.0	653.6	644.3	644.3	642.8
25°	640.7	635.0	622.8	624.2	622.8
27.5°	619.2	614.2	604.9	602.8	599.2
30°	597.8	592.1	581.3	579.2	576.3
32.5°	574.9	570.6	559.2	554.9	552.0
35°	552.7	545.6	534.2	529.9	526.3
37.5°	527.7	521.3	509.8	504.8	501.3
40°	502.0	496.3	484.8	478.4	475.5
42.5°	476.9	471.2	459.8	452.6	448.3
45°	449.8	444.8	434.0	426.2	423.3
47.5°	423.3	418.3	406.9	399.0	394.7
50°	395.4	391.9	381.8	371.8	368.3
52.5°	368.3	363.3	354.0	346.1	341.1
55°	340.4	336.1	327.5	318.9	315.3
57.5°	312.5	308.9	299.6	291.0	288.2
60°	284.6	281.7	271.7	263.9	261.7
62.5°	257.4	252.4	245.3	238.1	235.3
65°	229.5	225.2	218.1	211.7	208.1
67.5°	200.9	197.4	190.9	185.9	183.1
70°	174.5	171.6	165.2	160.2	157.3
72.5°	147.3	144.4	140.9	135.9	133.7
75°	120.1	118.7	115.1	110.8	112.3
77.5°	95.8	93.0	91.5	89.4	87.2
80°	71.5	70.8	69.4	67.2	65.8
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.3	28.6	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P1008083

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)