

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001507

Luminaire Tested: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001507
REPORT IS A COMBINATION OF REPORTS P996126 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6637.5 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001507

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001507

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	93	89	85	81	84	80	77	73	64	61	59	48	47	45	34	34	33
2	85	77	71	66	76	69	64	60	55	51	48	42	40	37	30	28	27
3	77	67	60	54	69	61	55	49	48	44	40	37	34	31	26	24	23
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19
5	64	53	45	39	58	48	41	35	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	26	23	20	19	16	14
7	54	42	34	29	49	38	31	27	31	26	22	24	20	17	17	15	13
8	50	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	14	12	10
10	44	32	25	20	39	29	23	18	23	19	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5611	5611	5611
5°	5627	5465	5475
10°	5590	5358	5342
15°	5538	5236	5192
20°	5460	5105	5047
25°	5373	4961	4890
30°	5279	4818	4730
35°	5172	4672	4587
40°	5086	4532	4440
45°	4959	4400	4310
50°	4850	4251	4173
55°	4738	4106	4014
60°	4565	3927	3865
65°	4375	3733	3686
70°	4143	3512	3479
75°	3818	3266	3281
80°	3455	3016	3075
85°	2969	2765	2907

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4959 cd/sqm

TEST NUMBER: P1001507

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	1.0
10°-20°	186.8	2.8
20°-30°	282.4	4.3
30°-40°	341.7	5.1
40°-50°	361.2	5.4
50°-60°	340.0	5.1
60°-70°	282.1	4.3
70°-80°	198.0	3.0
80°-90°	113.9	1.7
90°-100°	503.0	7.6
100°-110°	937.2	14.1
110°-120°	824.5	12.4
120°-130°	683.4	10.3
130°-140°	562.8	8.5
140°-150°	425.3	6.4
150°-160°	297.8	4.5
160°-170°	175.2	2.6
170°-180°	57.0	0.9
0°-30°	534.4	8.1
0°-40°	876.2	13.2
0°-60°	1577.4	23.8
0°-90°	2171.3	32.7
90°-120°	2264.7	34.1
90°-150°	3936.2	59.3
90°-180°	4466.0	67.3
0°-180°	6637.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	688	688	688	688	688	
5°	689	687	681	687	687	65
15°	660	661	659	666	665	186
25°	604	609	611	620	620	278
35°	529	538	546	556	559	331
45°	441	455	470	483	487	341
55°	345	361	384	400	404	308
65°	239	264	290	309	315	237
75°	132	161	193	215	222	141
85°	41	73	108	131	139	43
90°	14	52	97	122	129	11
95°	48	156	1008	554	376	50
105°	142	218	808	1701	1701	152
115°	242	310	712	1351	1619	241
125°	334	396	694	1141	1286	298
135°	395	470	673	1000	1137	306
145°	455	520	663	831	916	285
155°	516	557	644	730	761	238
165°	562	580	618	654	664	159
175°	587	588	592	600	598	56
180°	588	588	588	588	588	

TEST NUMBER: P1001507

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	688.1	688.1	688.1	688.1	688.1
2.5°	691.2	688.9	682.7	688.1	687.3
5°	688.9	686.6	681.2	687.3	686.6
7.5°	684.2	682.7	678.1	685.0	684.2
10°	678.1	677.3	673.5	680.4	679.6
12.5°	669.6	669.6	667.3	673.5	673.5
15°	660.4	661.1	658.8	665.7	665.0
17.5°	648.0	650.3	649.6	656.5	655.7
20°	634.9	637.2	638.0	645.7	645.7
22.5°	620.3	623.4	624.9	632.6	634.2
25°	604.1	608.7	611.0	619.5	620.3
27.5°	586.4	593.3	596.4	604.1	604.9
30°	568.7	574.8	580.2	588.7	590.2
32.5°	549.4	557.1	563.3	573.3	574.8
35°	528.6	537.8	545.5	556.3	558.6
37.5°	507.8	518.6	527.8	538.6	540.9
40°	487.8	497.8	508.6	520.1	523.2
42.5°	464.6	476.2	489.3	502.4	504.7
45°	440.8	455.4	470.0	483.1	487.0
47.5°	418.4	433.0	450.0	463.1	467.7
50°	393.7	410.7	427.7	443.1	447.7
52.5°	369.1	386.0	406.1	421.5	426.1
55°	345.2	361.4	384.5	399.9	404.5
57.5°	318.2	338.3	360.6	379.1	383.0
60°	292.0	312.1	337.5	355.2	361.4
62.5°	266.6	289.0	314.4	332.1	338.3
65°	238.9	263.5	289.7	309.0	315.2
67.5°	212.7	238.9	266.6	285.9	292.0
70°	185.7	211.9	241.2	262.0	267.4
72.5°	159.5	186.5	218.1	238.1	244.3
75°	132.5	161.0	193.4	215.0	221.9
77.5°	107.1	137.2	171.1	192.6	200.3
80°	84.0	114.8	148.7	171.8	178.0
82.5°	60.9	93.2	127.1	151.0	158.0
85°	40.8	73.2	107.9	131.0	138.7
87.5°	25.4	57.0	90.9	113.3	120.2
90°	13.5	52.4	97.1	121.7	129.0
92.5°	27.8	127.4	524.3	242.8	204.5
95°	48.1	155.5	1008.1	553.7	376.5
97.5°	72.7	164.4	1070.1	1034.6	766.9
100°	96.3	178.6	987.0	1395.8	1143.7
102.5°	119.4	196.3	884.9	1619.6	1472.3
105°	142.0	218.0	808.4	1701.1	1701.0
107.5°	168.6	241.2	757.1	1671.3	1807.2
110°	194.4	263.5	732.1	1574.3	1805.6

TEST NUMBER: P1001507

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.0	286.5	717.9	1456.5	1732.9
115°	242.5	310.1	711.7	1351.1	1618.6
117.5°	267.9	332.6	706.7	1266.7	1507.3
120°	292.6	353.7	702.8	1208.4	1415.0
122.5°	315.7	375.1	697.9	1169.4	1341.1
125°	334.5	396.0	693.6	1140.6	1285.6
127.5°	353.0	416.8	687.4	1112.4	1249.4
130°	367.2	436.2	682.5	1080.2	1217.1
132.5°	382.2	453.6	678.2	1042.9	1182.0
135°	395.3	470.3	673.2	999.6	1137.0
137.5°	409.1	484.0	670.2	954.2	1085.1
140°	424.1	497.4	666.6	910.0	1029.2
142.5°	439.6	509.4	665.1	869.3	970.0
145°	454.6	519.6	662.8	831.4	916.5
147.5°	471.9	530.0	659.3	799.3	866.5
150°	488.1	539.8	655.9	772.5	824.5
152.5°	502.3	549.0	650.1	750.6	789.8
155°	516.2	557.2	644.3	729.8	760.9
157.5°	530.0	564.7	638.6	710.2	734.4
160°	542.7	571.0	631.6	690.5	710.1
162.5°	554.3	576.2	624.7	671.4	687.0
165°	562.3	579.7	617.8	654.2	664.0
167.5°	571.6	582.6	610.8	639.2	645.5
170°	577.4	584.8	603.9	624.1	628.2
172.5°	583.1	586.6	597.0	610.8	610.8
175°	586.6	587.7	592.4	600.4	598.1
177.5°	588.9	587.7	588.9	593.0	588.9
180°	587.7	587.7	587.7	587.7	587.7

(END OF REPORT)