

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001509

Luminaire Tested: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001509
REPORT IS A COMBINATION OF REPORTS P996128 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6613.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001509

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001509

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	104	104	104	104		94	94	94	94		76	76	76		60	60	60		45	45	45
1	95	91	87	83		86	82	79	76		67	65	62		52	51	50		39	38	37
2	86	79	73	68		78	72	67	62		58	55	52		46	44	41		35	33	32
3	79	70	62	57		71	63	57	52		52	47	43		41	38	35		31	29	27
4	72	61	54	48		65	56	49	44		46	41	37		36	33	30		27	25	23
5	66	55	47	41		60	50	43	38		41	36	32		32	29	26		25	22	20
6	61	49	41	35		55	45	38	33		37	32	28		29	26	23		22	20	18
7	56	44	36	31		51	40	34	29		33	28	24		27	23	20		20	18	16
8	52	40	32	27		47	37	30	25		30	25	21		24	21	18		19	16	14
9	48	36	29	24		44	33	27	22		28	23	19		22	19	16		17	15	13
10	45	33	26	22		41	31	24	20		25	21	17		21	17	14		16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1001509

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.4
10°-20°	255.3	3.9
20°-30°	375.8	5.7
30°-40°	436.8	6.6
40°-50°	436.8	6.6
50°-60°	382.0	5.8
60°-70°	283.6	4.3
70°-80°	160.9	2.4
80°-90°	49.3	0.7
90°-100°	97.3	1.5
100°-110°	291.4	4.4
110°-120°	495.1	7.5
120°-130°	652.9	9.9
130°-140°	733.4	11.1
140°-150°	720.8	10.9
150°-160°	606.2	9.2
160°-170°	403.4	6.1
170°-180°	141.2	2.1
0°-30°	721.7	10.9
0°-40°	1158.6	17.5
0°-60°	1977.4	29.9
0°-90°	2471.2	37.4
90°-120°	883.8	13.4
90°-150°	2990.9	45.2
90°-180°	4142.0	62.6
0°-180°	6613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	4	16	25	32	35	8
95°	69	80	88	91	91	75
105°	269	270	275	278	282	285
115°	503	503	501	500	499	496
125°	733	733	732	730	727	653
135°	946	952	952	950	947	731
145°	1149	1153	1154	1153	1150	719
155°	1316	1316	1315	1320	1315	606
165°	1433	1429	1427	1434	1429	404
175°	1490	1485	1484	1492	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1001509

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	3.5	16.2	25.4	32.3	34.6
92.5°	30.0	45.0	50.8	54.3	55.4
95°	69.3	79.7	87.7	91.2	91.2
97.5°	110.8	120.1	129.3	133.9	133.9
100°	161.6	166.2	176.6	178.9	178.9
102.5°	214.7	215.9	225.1	228.6	229.7
105°	269.0	270.1	274.8	278.2	281.7
107.5°	325.6	326.7	327.9	332.5	331.3
110°	383.3	385.6	384.4	382.1	385.6

TEST NUMBER: P1001509

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.3	443.3	441.0	441.0	441.0
115°	503.4	503.4	501.0	499.9	498.7
117.5°	559.9	559.9	558.8	555.3	551.8
120°	616.5	621.1	617.6	611.9	614.2
122.5°	675.4	676.5	675.4	671.9	666.1
125°	733.1	733.1	731.9	729.6	727.3
127.5°	785.0	788.5	786.2	783.9	782.7
130°	840.5	843.9	843.9	841.6	837.0
132.5°	897.0	899.3	898.2	895.9	894.7
135°	945.5	952.4	952.4	950.1	946.7
137.5°	999.8	1003.2	1005.6	1002.1	1003.2
140°	1054.0	1056.3	1056.3	1055.2	1054.0
142.5°	1103.7	1106.0	1104.8	1104.8	1104.8
145°	1148.7	1153.3	1154.5	1153.3	1149.9
147.5°	1194.9	1200.7	1199.5	1198.3	1197.2
150°	1236.4	1241.1	1241.1	1241.1	1239.9
152.5°	1275.7	1278.0	1279.2	1282.6	1279.2
155°	1316.1	1316.1	1315.0	1319.6	1315.0
157.5°	1350.7	1348.4	1348.4	1351.9	1348.4
160°	1380.8	1379.6	1378.4	1381.9	1376.1
162.5°	1408.5	1405.0	1403.8	1410.8	1405.0
165°	1432.7	1429.2	1426.9	1433.9	1429.2
167.5°	1452.3	1447.7	1447.7	1454.6	1447.7
170°	1468.5	1462.7	1463.9	1470.8	1462.7
172.5°	1480.0	1475.4	1475.4	1483.5	1475.4
175°	1490.4	1484.7	1483.5	1491.6	1483.5
177.5°	1495.1	1489.3	1489.3	1497.4	1488.1
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)